



DELL 34 CURVED VIDEO CONFERENCING MONITOR | C3422WE

# Team up. Seamlessly.



## COLLABORATE ON A CURVE

Bring your meetings to life with the world's first 34" curved video conferencing monitor certified for Microsoft Teams.†



## WORK COMFORTABLY

Tilt, swivel and adjust the height of your monitor to your exact preference.



## MULTITASK MODE

Multitask efficiently with two PC sources using built-in Picture-by-Picture and Keyboard, Video and Mouse features.



## TRUSTED RELIABILITY

As the world's #1 monitor company\*, we take pride in our unyielding commitment to quality and the utmost satisfaction of our customers.

# World class video conferencing




## COLLABORATE ON A CURVE

**Join meetings faster:** Enjoy world class collaboration and efficient, fast meetings with a dedicated, one-touch Microsoft Teams button.

**Immersive collaboration:** Razor-sharp video clarity on a pop-up 5MP IR camera with FHD video resolution giving you more than twice the detail of a 2MP on a beautiful, panoramic screen.

**Clear, vibrant sound:** Dual 5W integrated speakers deliver clear, vibrant communication from any workspace quashing background chatter with a noise-canceling microphone.



## ALWAYS MEETING READY

**Ready to meet:** With the high definition 5MP IR camera, dual 5W integrated speakers and noise-canceling microphone, you are good to go for any meeting.

**Enhanced Security:** The pop-up 5MP camera hides safely out of sight when not in use and adds an intelligent layer of security with facial recognition through Windows Hello™<sup>1</sup>.

**Personalized convenience:** Say what you need and let Cortana do the rest with hands-free commands.



## MULTITASK MODE

**Multitask efficiently:** Connect two PC sources to the monitor and display the content at the same time with Picture-by-Picture (PBP) and Picture-in-Picture (PIP) features. Use the KVM (keyboard, video and mouse) feature to edit content from two different PCs using a single keyboard and mouse.

**The power of USB-C®:** Connect to productivity: With wired connectivity options like RJ45 and USB-C®, your monitor delivers reliable Ethernet<sup>2</sup>, power, audio and video — all in one clutter-free setup.

**Enhanced manageability:** Managing your monitor is easy with MAC Address pass-through<sup>3</sup>, PXE boot, and wake-on LAN conveniently built in.

**Productivity at every level:** Easy Arrange allows you to easily tile multiple applications across one or more screens with 38 pre-set window partitions and the ability to personalize up to five windows, giving you improved multitasking abilities.<sup>4</sup>



## WORK COMFORTABLY

**Flexible, all-day comfort:** Tilt, swivel and adjust the height of your monitor for a comfortable setup all day long. Or choose from a variety of mounts and stands, including VESA, for even more flexibility.

**Easy on the eyes:** Comfort meets collaboration with ComfortView Plus<sup>5</sup> — an always-on, built-in low blue light screen that optimizes eye comfort by reducing potentially harmful blue light emissions while delivering excellent color accuracy.

## THANK YOU FOR MAKING DELL MONITORS #1 WORLDWIDE\*

**Peace of mind:** Dell Premium Panel Exchange allows a free panel replacement during the Limited Hardware Warranty<sup>6</sup> period even if only one bright pixel is found.

**Minimize downtime:** Your monitor comes with a 3-year Advanced Exchange Service<sup>7</sup> so that if a replacement becomes necessary, it will be shipped to you the next business day during your 3-year Limited Hardware Warranty.

**Get a higher level of support:** Upgrade to 24 X 7, in-region technical phone support from qualified engineers with Dell ProSupport option.<sup>8</sup>

# Features & Technical Specifications

<b>Monitor</b>	Dell 34 Curved Video Conferencing Monitor – C3422WE	
Diagonal Viewing Size	867.1 mm (34.14 inches)	
Horizontal	799.8 mm (31.49 inches)	
Vertical	334.8 mm (13.18 inches)	
Maximum Preset Resolution	3440 x 1440 at 60Hz	
Aspect Ratio	21:9	
Curvature	3800R (typical)	
Pixel Pitch	0.2325 mm x 0.2325 mm	
Pixel Per Inch (PPI)	109.68	
Brightness	300 cd/m <sup>2</sup> (typical)	
Color Support	Color Gamut (typical): 99% sRGB Color Depth: 1.07 billion colors	
Contrast Ratio	1000: 1 (typical)	
Viewing Angle	178° (vertical) typical 178° (horizontal) typical	
Response Time	8 ms (Normal); 5 ms (Fast) - (gray to gray)	
Panel Type	In-Plane Switching Technology	
Backlight Technology	LED	
PbP / PiP / KVM	PbP (Yes) / PiP (Yes) / KVM (Yes), Auto KVM	
Dell Display Manager Compatibility	Yes	
Daisy Chain Availability	No	
Remote Asset Management	Yes, via Dell Command   Monitor	
Display Screen Coating	Antiglare with 3H hardness	
<b>Connectivity</b>		
Connectors	1 x DP 1.2 (HDCP2.2); 1 x HDMI 2.0 (HDCP2.2); 1 x USB Type-B (USB 3.2 Gen1 upstream port); 1 x USB Type-C® (Alternate mode with DisplayPort 1.2, USB 3.2 Gen1 upstream port, Power Delivery up to 90W); 1 x USB Type-C downstream (15W), USB 3.2 Gen1 (5Gbps); 2 x super speed USB 5Gbps (USB 3.2 Gen1); 1 x super speed USB 5Gbps (USB 3.2 Gen1) with BC 1.2 charging capability at 2 A (max); 1 x 3.5 mm headphone jack; 1 x RJ45	
<b>Video Conferencing</b>		
Webcam Specs	5 mega-pixel RGB+IR, Windows Hello™1 compatible Video Frame Rate - 1920x 1080 (Full HD) - up to 30 frames per second	
Built-in Microphone	Digital microphone x2	
Built-in Speaker	2 x 5W	
<b>Design Features</b>		
Adjustability	Height-adjustable stand (120 mm), Tilt (-5° to 21°) Swivel (-30° to 30°), Slant adjust -4° to 4°	
Security	Security lock slot (cable lock sold separately)	
Flat Panel Mount Interface	VESA (100 mm)	
<b>Power</b>		
Voltage Required	100-240 VAC / 50 or 60 Hz ± 3 Hz / 2.8 A (maximum)	
Power Delivery (via USB-C Type C)	Up to 90W	
Power Consumption (Operational)	38 W (On Mode) <sup>9</sup> / 220 W (Max) <sup>10</sup>	
Power Consumption Stand by/Sleep	0.5 W	
<b>Dimensions (with Stand)</b>		
Height (Compressed ~ Extended)	456.20 mm ~ 576.2 mm (17.96 inches ~ 22.68 inches)	
Width	815.85 mm (32.1 inches)	
Depth	234.95 mm (9.30 inches)	
<b>Weight</b>		
Weight (Panel Only - for VESA Mount)	7.3 kg (16.06 lb)	
Weight (with Packaging)	16 kg (35.2 lb)	
<b>Standard Service Plan</b>	Premium Panel Exchange, 3-Years Advanced Exchange Service <sup>7</sup> and Limited Hardware Warranty <sup>8</sup>	
<b>Optional Service Plan</b>	Dell ProSupport <sup>8</sup>	
<b>Environmental Compliance</b>	ENERGY STAR® certified monitor, EPEAT® Gold registered where applicable <sup>11</sup> , TCO Certified Display, RoHS Compliant, BFR/PVC Free monitor (excluding external cables), meets NFPA 99 leakage current requirements, arsenic-free glass and mercury-free for the panel only	
<b>What's in the box?</b>		
<b>Components</b>		<ul style="list-style-type: none"><li>• Monitor with stand</li></ul>
<b>Cables</b>		<ul style="list-style-type: none"><li>• Power cable</li><li>• 1 x DP Cable (DP to DP)</li><li>• 1 x USB Type-C cable (C to C)</li><li>• 1 x USB 3.2 Gen1 Type-A to Type-B upstream cable</li></ul>
<b>Documentation</b>		<ul style="list-style-type: none"><li>• Quick Setup Guide</li><li>• Safety and Regulatory Information</li></ul>

# Recommended Accessories

## DELL 34 CURVED VIDEO CONFERENCING MONITOR | C3422WE

### Video Conferencing Features




- 1 Microphone
- 2 IR LED
- 3 Webcam lens
- 4 IR LED
- 5 Webcam LED indicator
- 6 Microphone
- 7 Built-in speakers
- 8 Teams button and LED
- 9 Hookswitch and LED
- 10 Volume down and LED
- 11 Volume up and LED
- 12 Microphone mute and LED
- 13 Power LED indicator

### Easily adjust the panel to your preferred viewing position.



Back view - Cable management slot



Tilt and height adjustable



Quick access controls with dedicated Microsoft Teams button




Swivel



Toolless monitor installation with Quick Release

### Connectivity



- |                      |                              |  |                          |
|----------------------|------------------------------|--|--------------------------|
| 1 Security lock slot | 4 DisplayPort (in)           | 7 Super speed USB 5Gbps (USB 3.2 Gen1) | 10 Headphone jack        |
| 2 Power connector    | 5 USB-C upstream/DisplayPort | 8 RJ45 connector                       | 11 USB-C downstream port |
| 3 HDMI port          | 6 USB-B upstream port        | 9 Super speed USB 5Gbps (USB 3.2 Gen1) | 12 Stand lock            |

† Based on Dell analysis of publicly available information of competitive desktop monitors, October 2020.

\* Dell monitors are #1 Worldwide for 7 consecutive years (2013, Q2 to 2020, Q3)! Source: IDC Worldwide Quarterly PC Monitor Tracker, Q3, 2020.

\*\* Based on internal analysis, November 2019, ID#G19000453.

\*\*\* Based on Dell internal analysis of battery life usage model calculations and 3 million keystrokes per year, November 2019. Results vary depending on usage and computing conditions.

1 Windows Hello requires specialized hardware, including fingerprint reader, illuminated IR sensor or other biometric sensors.

2 Ethernet connection via the RJ45 port.

3 MAC Address pass-through functionality is tested to work with most Dell PC systems. Functionality on non-Dell systems may vary.

4 Download Dell Display Manager for free at [www.dell.com/ddm](http://www.dell.com/ddm).

5 Source: TÜV Rheinland certified – Low Blue Light Hardware Solution and Flicker Free

6 For a copy of the Limited Hardware Warranty, write to Dell USA LP, Attention: Warranties One Dell Way, Round Rock, TX 78682 or see [dell.com/warranty](http://dell.com/warranty) for details.

7 Advanced Exchange Service: Dell will send you a replacement monitor the next business day in most cases, if deemed necessary after phone/online diagnosis. Shipping times may vary by location and for monitors 55" and above. Fee charged for failure to return defective unit. See [dell.com/servicecontracts/global](http://dell.com/servicecontracts/global) for details.

8 Availability varies by region, please visit [dell.com/support](http://dell.com/support) for details.

9 As defined in EU 2019/2021 and EU 2019/2013.

10 Max brightness and contrast setting with maximum power loading on all USB ports.

11 EPEAT Gold registered where applicable. EPEAT registration varies by country. See [www.epeat.net](http://www.epeat.net) for registration status by country.

[Dell.com/monitors](http://Dell.com/monitors)

Product availability varies by country. Please contact your Dell representative for more information.

© 2021 Dell Inc. or its subsidiaries. All Rights Reserved. Dell Technologies, Dell, EMC, Dell EMC and other trademarks are trademarks of Dell Inc. or its subsidiaries. Other trademarks may be trademarks of their respective owners. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum.

