
## Key Features

165Hz Refresh Rate | Ultra-Fast Response Time | Adaptive Sync | Frameless Design



## Product **Description**

The ViewSonic\* VX2718-P-MHD is a 27″ 1080p gaming monitor built for gaming and entertainment. With a sleek frameless design, the VX2718-P-MHD provides a seamless viewing experience for multi-monitor gaming setups. Featuring a 165Hz\* refresh rate, 1ms (MPRT) response time and adaptive sync technology, this monitor virtually eliminates screen tearing and stuttering for a fluid gaming experience. The VX2718-P-MHD also comes equipped with ViewSonic exclusive ViewMode™ presets, which offer optimized screen performance for different home entertainment applications such as watching movies, editing files, or playing video games. Two HDMI (v1.4) inputs, and one DisplayPort (v1.2) input offers flexible connectivity for both general use and entertainment. \*165Hz refresh rate with DisplayPort











Display:

Display Size (in.): 27 Viewable Area (in.): 27 Panel Type: MVA Resolution: 1920 x 1080 Resolution Type: Full HD (1920x1080)

Static Contrast Ratio: 4,000:1 Dynamic Contrast Ratio: 80,000,000:1 Light Source: LED Brightness: 250 cd/m2 Colors: 16.7M

Color Space Support: 8 bit (6 bit + FRC)

Aspect Ratio: 16:9 Response Time (Typical GTG): 5ms Response Time (MPRT):

Viewing Angles: 178° horizontal, 178° vertical

Backlight Life (Hours): 30,000

Panel Surface: Anti-Glare type, Hard-coating (3H), Haze 25%

Refresh Rate (Hz): 165

Compatibility:

PC Resolution (max): 1920x1080 Mac® Resolution (max): 1920x1080

Connector:

3.5mm Audio Out(1), HDMI 1.4 In(2), DisplayPort(1)

Audio:

Internal Speakers: 2W (x2)

Power:

26W Eco Mode (Conserve): Eco Mode (optimized): 28W Consumption (typical): 32W Consumption (max): 37W

AC 100-240V (universal), 50-60Hz Voltage:

0.5W Stand-by: Power Supply: Internal

Additional Hardware:

Kensington Lock Slot:

Controls:

Physical Controls: Key 1 (favorite), Key 2, Key 3, Key 4, Key 5 (power)

Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu On Screen Display:

**Operating Conditions:** 

Temperature: 32-104° F (0 - 40° C)

Humidity (non-condensing): 20-90%

Mount:

VESA Compatible: 100 x 100 mm Video Signal:

Frequency Horizontal: HDMI (v1.4): 24 ~ 166.4 KHz, DisplayPort (v1.2): 24 ~ 183 KHz Frequency Vertical: HDMI (v1.4): 50 ~ 144 Hz, DisplayPort (v1.2): 50 ~ 165 Hz

**Ergonomics:** 

Tilt (Forward/Back): 5° / 25°

Weight (imperial):

Net (lbs): 4.4 Net Without Stand (lbs): 4.0 Gross (lbs): 6.0

Weight (metric):

9.7 Net (ka): Net Without Stand (kg): 8.8 Gross (ka): 13.2

Dimensions (imperial) (WxHxD):

Packaging (in.): 27.4 x 18.1 x 5.7 Physical (in.): 24.2 x 18.0 x 8.9 Physical Without Stand (in.): 24.2 x 14.3 x 1.8

Dimensions (metric) (WxHxD):

695.0 x 460.0 x 145.0 Packaging (mm): Physical (mm): 615.0 x 458.0 x 226.0 Physical Without Stand (mm): 615.0 x 364.0 x 46.0

General:

Regulations: cTUVus, FCC-B, ICES003, CEC, NOM, Mexico Energy

PACKAGE CONTENTS: VX2718-P-MHD, Power Cable, DisplayPort Cable, Quick Start Guide

Recycle/Disposal: Please dispose of in accordance with local, state or federal laws.

Warranty: Three-year limited warranty on parts, labor and backlight

Accessories:

CB-00008948, CB-00009950, CB-00010555, CB-00010684, CB-00010958, LCD-DMA-002, LCD-WMK-001

Copyright © ViewSonic Corporation 2000-2021. All rights reserved. (10/22/2021 09:59 AM PST)