



Extraordinary color accuracy and picture-perfect design.

Remove barriers between designer and design with the HP DreamColor Z25x G3 Monitor. Create jaw-dropping visuals with over a billion colors and hyper-realistic contrast in QHD HDR. Work flawlessly in your chosen medium with purpose-built, factory-calibrated color presets for Mac® and PC.



The right colors, right out of the box.

Create with over a billion exceptionally vibrant colors in 99% sRGB and 95% DCI-P3 coverage^[1] - all in vivid HDR and QHD resolution. This PANTONE® Validated monitor has user presets that allow creators to optimize their own color space. Choose your workflow with calibrated color presets for web design (sRGB D65), print design (sRGB D50), photography (DCI-P3 D65), HD video (BT.709), or customize one that's for exactly right for you.

Beautifully designed for all creators.

Remove barriers between design and designer with the thoughtfully crafted, frameless experience of this 25-inch diagonal screen monitor. It features a single USB-C® port that connects both video and data and powers either your Mac® or PC. And let's you work comfortably with 4-way adjustable ergonomics.

Easy adjustments for a smooth workflow.

Enjoy an uninterrupted workflow and quickly see every detail of what you're creating by adjusting your monitor's brightness with the touch of a button. Plus a simple joypad lets you switch easily between your color presets.

Featuring

Customize your colors

Need to customize your colors presets? The HP Display Center let's you create 3 additional presets.

HP Zero BrightDot Guarantee

Even if just a third of a pixel fails or is stuck in one position, HP will replace the entire display.^[5]

Optional integrated audio

Easily attach the Z Display G3 Conferencing Speaker Bar for stereo quality audio and dual microphones.^[6]

3-year limited warranty

3-year limited warranty includes technical support, diagnostic services, and hardware replacement.

Specifications

Display size (diagonal)	25"
Panel technology	IPS
Display size (diagonal)	63.5 cm (25")
Aspect ratio	16:9 ^[1]
Native resolution	QHD (2560 x 1440) ^[1]
Resolutions supported	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 1920 x 1200; 2560 x 1440
Pixel pitch	0.216 mm
Brightness	266 nits ^[1,5]
Contrast ratio	1000:1 ^[1]
Response time (typical)	14 ms gray to gray ^[1]
Minimum dimensions (W x D x H)	56.9 x 4.6 x 33.3 cm (Without stand.)
Minimum dimensions (W x D x H)	22.4 x 1.8 x 13.1 in (Without stand.)
Dimensions With Stand (W x D x H)	56.9 x 20.5 x 51.8 cm
Weight	6.2 kg (With stand.)
Weight	13.7 lb (With stand.)
Display features	Pantone® Validated; Factory Calibrated; Brightness buttons; Height Adjust/Tilt/Swivel/Pivot; VESA DisplayHDR 400 certified
Display Input Type	1 USB Type-C™ (Alternative mode DisplayPort™ 1.4, Power Delivery up to 100W); 1 HDMI 2.0 (with HDCP support); 1 DisplayPort™ 1.4-in (with HDCP support); 1 DisplayPort™ 1.4-out (with HDCP support); 1 USB Type-C™ (DisplayPort™ 1.4, Power Delivery up to 15W); 3 USB-A 3.2 Gen 1
Onscreen controls	Information; Power; Next active input; Brightness+; Color
Display scan frequency (horizontal)	30-95 KHz
Display scan frequency (vertical)	59-60 Hz
Webcam	No integrated camera
Power	100 - 240 VAC 50/60 Hz
Power consumption	205 W (maximum), 35 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% non-condensing
Sustainable impact specifications	Arsenic-free display glass; Low halogen; Mercury-free display backlights; TCO Certified; TCO Certified Edge
Certifications and compliances	BIS; BSMI; CB; CCC; CE; CECP; CEL; cTUVus; EAC; ENERGY STAR®; ErP; GS Mark; ISO 9241-307; KC/KCC; NOM; PSB; SEPA; TCO Certified; TCO Certified Edge; VCCI; WEEE; ISC; Low blue light; Ukraine Energy label; WW application; UAE
Physical security	Security lock-ready ^[2]
Management software	HP Display Center
UPC number	(A2K) 195122232160; (A2N) 195122232177; (AB0) 195122232184; (AB1) 195122232191; (AB2) 195122232207; (AB4) 195122232214; (ABA) 195122232221; (ABB) 195122232238; (ABG) 195122232245; (ABT) 195122232252; (ABU) 195122232269; (ABV) 195122232276; (ABY) 195122232283; (ACJ) 195122232290; (ACQ) 195122232306; (AKL) 195122232320; (AR6) 195122232337; (UUF) 195122232344; (UUZ) 195122232351
What's in the box	Monitor; HDMI cable; Documentation; VESA Mount adapter; Cable manager; 1 USB Type-C® to Type-C cable; 1 USB Type-C® to Type-A cable; AC power cord; DisplayPort™ 1.4 cable ^[4]

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[5] The HP Pixel Policy allows no bright sub-pixel defects for this display. For complete details, see <http://support.hp.com/us-en/document/c00288895>.

[6] Z Display Conferencing Speaker Bar Sold Separately.

Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[2] Lock sold separately.

[4] Included cables may vary by country.

[5] HP-applied uniformity compensation to each Z25xs G3 display, which brings the typical uniform peak luminance down to 266 cd/m² from a 400 cd/m² native peak brightness. Display supports luminance calibration up to 266 cd/m², reserving any luminance headroom for panel aging compensation.

© Copyright 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

USB-C® is a registered trademark of USB Implementers Forum, Pantone® is the registered trademark of Pantone LLC.

