

Country	us
Ean	0824142245255
Color	SLVR
Operating System	Windows 10 Pro
Processor	Intel® Celeron® N4000 2C/2T 1.10-2.60 GHz 4MB Cache
Chipset	SoC
Display	15.6" LED HD (1366 x 768) 16:9 Glossy Multi-Touch eDP
Display Type	Multi-Touch
Graphics	Intel® UHD
Memory	4GB DDR4 (1 x 4GB)
Memory Slots	2 x DDR4 SO-DIMM, up to 8GB
Storage	64GB M.2 SATA SSD
Optical Drive Type	N/A
LAN	1 x RJ45 (1GbE)
WLAN	Intel® Dual Band Wireless-AC 9462 1x1 802.11ac (433 Mbps)
Bluetooth	BT 5.1
Included Peripherals	USB Keyboard & Mouse
Audio	2 x 2W Speakers
VGA	N/A
Video I/O	1 x HDMI-out
USB 2.0	N/A
USB 3.1/3.2	3 x USB 3.1 Gen1 Type-A (1 x bottom, 2 x side, 1 w/SuperCharge)
Com Port	1 x adapter (RJ45 to COM)
Mic in / Headphone out	1 x Headphone-Out
Card Reader	3-in-1 (SD3.0, SD4.0, MMC)
Webcam	1.0 MP
Power Adapter	65W
Dimensions	15.02" x 10.39" x 0.98"
Weight	4.17 lbs
Warranty	1 Year