

Key Features

- Intuitive 10-point touchscreen
- Finger, stylus, and glove touch compatible
- Magnetic pen placeholder
- Adjustable back tilt up to 40-degrees
- Scratch-resistant 7H hardness screen



Product Description

The ViewSonic® TD2223 is a 22" IR touch display designed for intuitive multi-touch use. Infrared (IR) touchscreen can detect up to 10 points of contact compared to optical touchscreens and can be operated by a stylus, fingers and gloved hands. The multi-touch input is more accurate, and the display is faster. Coupled with an adjustable tilt, you can easily interact with the TD2223 at an ideal position. This monitor features Full HD resolution to give you clear images and is built with scratch-resistant 7H hardness screen to surface damage. To support your work, the TD2223 is equipped with VGA, HDMI, DVI and USB connectivity.



1. Menu Control Panel
2. USB Down Stream x 2
3. USB UP Stream
4. AC In
5. HDMI
6. VESA Compatible(Wall Mount 100 x 100mm)
7. Earphone Out
8. Audio In
9. VGA
10. DVI

Visit Us www.viewsonic.com

| DISPLAY | | CONNECTOR | | INPUT SIGNAL | | GENERAL | |
|--------------------------------|---|-----------------------------|---|--------------------------------------|-------------------------------------|-------------------|--|
| Display Size (in.): | 22 | VGA: | 1 | Frequency Horizontal: | 24 ~ 82KHz | Regulations: | cTUVus, FCC-B, ICES003, Energy Star 8.0, EPEAT Silver, CEC, MX-CoC, Mexico Energy, CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO, BSMI, RCM, GEMS, VCCI, PSE, BIS, CCC, China RoHS, China Energy Label, CECP |
| Viewable Area (in.): | 21.5 | USB 2.0 Type A: | 2 | Frequency Vertical: | 50 ~ 75Hz | | |
| Panel Type: | TN Technology | USB 2.0 Type B: | 1 | VIDEO INPUT | | | |
| Resolution: | 1920 x 1080 | 3.5mm Audio In: | 1 | Digital Sync: | TMDS - DVI-D, TMDS - HDMI (v1.4) | | |
| Resolution Type: | FHD | 3.5mm Audio Out: | 1 | Analog Sync: | Separate/Composite/SOG - RGB Analog | PACKAGE CONTENTS: | TD2223 x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v1.4; Male-Male) x1, USB A/B Cable (v2.0; Male-Male) x1, Audio Cable (Male-Male) x1, Quick Start Guide x1 |
| Static Contrast Ratio: | 1,000:1 (typ) | HDMI 1.4: | 1 | ERGONOMICS | | | |
| Dynamic Contrast Ratio: | 20M:1 | DVI-D: | 1 | Tilt (Forward/Back): | 22° / 38° | | |
| Light Source: | LED | Power in: | 3-pin Socket (IEC C14 / CEE22) | WEIGHT (IMPERIAL) | | | |
| Brightness: | 250 cd/m² (typ) | AUDIO | | Net (lbs): | 9.9 | Recycle/Disposal: | Please dispose of in accordance with local, state or federal laws. |
| Colors: | 16.7M | Internal Speakers: | 2Watts x2 | Net Without Stand (lbs): | 8.6 | Warranty: | *Warranty offered may differ from market to market |
| Color Space Support: | 8 bit (6 bit + Hi-FRC) | POWER | | Gross (lbs): | 13.2 | Power Management: | Energy Star standards, EPEAT |
| Aspect Ratio: | 16:9 | Eco Mode (Conserve): | 8.5W | WEIGHT (METRIC) | | | |
| Response Time (Typical GTG): | 5ms | Eco Mode (optimized): | 10.5W | Net (kg): | 4.5 | | |
| Response Time (GTG w/OD): | 5ms | Consumption (typical): | 12.5W | Net Without Stand (kg): | 3.9 | | |
| Response Time (Typical Tr+Tf): | 5ms | Consumption (max): | 14W | Gross (kg): | 6 | | |
| Viewing Angles: | 170° horizontal, 160° vertical | Voltage: | AC 100-240V, 50/60 Hz | DIMENSIONS (IMPERIAL) (WXHxD) | | | |
| Backlight Life (Hours): | 30000 Hrs (Min) | Stand-by: | 0.5W | Packaging (in.): | 22.8 x 15.9 x 6.5 | | |
| Curvature: | Flat | Power Supply: | Internal | Physical (in.): | 20.5 x 13.1 x 4 | | |
| Refresh Rate (Hz): | 75 | ADDITIONAL HARDWARE | | Physical Without Stand (in.): | 20.5 x 12.5 x 2.4 | | |
| Blue Light Filter: | Yes | Kensington Lock Slot: | 1 | DIMENSIONS (METRIC) (WXHxD) | | | |
| Flicker-Free: | Yes | Cable Organization: | Yes | Packaging (mm): | 580 x 405 x 164 | | |
| Color Gamut: | NTSC: 72% size (Typ), sRGB: 103% size (Typ) | CONTROLS | | Physical (mm): | 521 x 334 x 101 | | |
| Pixel Size: | 0.248 mm (H) x 0.248 mm (V) | Physical Controls: | 1, 2, Up, Down, Power | Physical Without Stand (mm): | 521 x 318 x 61 | | |
| Touch Screen: | IR, 10-point multi-touch | On Screen Display: | Auto Image Adjust, Contrast/Brightness, Input Select, Audio Adjust, Color Adjust, Information, Manual Image Adjust, Setup Menu, Memory Recall | | | | |
| Surface Treatment: | Glossy, Hard Coating (7H) | OPERATING CONDITIONS | | | | | |
| Cover Glass Thickness: | 2mm | Temperature: | 32°F to 104°F (0°C to 40°C) | | | | |
| COMPATIBILITY | | Humidity (non-condensing): | 20% to 90% | | | | |
| PC Resolution (max): | 1920x1080 | WALL MOUNT | | | | | |
| Mac® Resolution (max): | 1920x1080 | VESA Compatible: | 100 x 100 mm | | | | |
| PC Operating System: | Windows 10 certified; macOS tested | | | | | | |
| Mac® Resolution (min): | 1920x1080 | | | | | | |