



SPECIFICATIONS

CPU	Intel® Core™ i3-10110U; Core™ i5-10210U; Core™ i7-10510U
OS	Windows 10 Home - MSI recommends Windows 10 Pro for business
Chipset	Intel® SoC
Storage	2.5" SATAIII / 7200rpm with MSI HDD Rapid Upgrade Design M.2 SSD (NVMe PCIe / SATA Auto Switch)
Memory	DDR4 SO-DIMM x slots 2 / up to 32GB
Graphics	Intel® UHD Graphics
Panel Resolution	23.8" IPS Grade Panel LED Backlight (1920*1080 FHD) with MSI Anti-Flicker technology
Touch Panel	Non-touch
Optical Drive	N / A
Audio	2 x 2.5W Speakers
LAN	10/100/1000 x 2
Wireless LAN	Intel 3168AC / Intel 9462 AC (Optional)
Bluetooth	4.2 (with Intel 3168AC) / 5 (with Intel 9462AC)
USB 3.1 port	4 (Gen 1 Type A, one for Super Charger)
USB 2.0 port	2
HDMI out	1
Mic-in/Headphone-out	1/1
Keyboard / Mouse	USB Keyboard / Mouse (Optional)
AC Adapter	90W
AIO Wall Mount Kit III	VESA standard (STD 75*75mm) (Optional)
Adjustment (Tilt)	-5° ~ 15°
Dimension(WxDxH)	538.44 x 169.96 x 399.96mm / 21.20" x 6.69" x 15.75" (with Stand)
Net Weight	4.44Kg / 9.79lbs
Gross Weight	6.46Kg / 14.24lbs

FEATURES



Silent PRO Cooling

Server Grade Thermal Module handles the cooling of different components within the system.



Dual LAN

The best way to back up your file/ secure data and prevent the hacker (with MSI exclusive BIOS).



HDD Rapid Upgrade

Easy maintenance and easy upgrade design with a switchable 2.5" storage inside.



Anti-Flicker Technology

With MSI Anti-Flicker technology, a stable output current for the monitor is provided to protect your eyes.



Anti-Glare Display

An anti-glare display makes viewing the display more pleasant and reduces eyestrain for users.



VESA Mountable

VESA mountable design makes the PC completely invisible on your desk.

CONNECTIONS



- | | |
|-------------------------------|--------------------------------|
| 1. 2x USB 3.2 Gen 1 Type-A | 2. 1x Mic-in/ 1x Headphone-out |
| 3. 1x DC-in | 4. 1x Kensington Lock |
| 5. 2x RJ45 LAN | 6. 1xHDMI-out |
| 7. 2x USB 3.2 Gen 1 Type A | 8. 2x USB 2.0 Type A |
| 9. 1x switchable 2.5" Storage | |