



# Kasa Spot® Pan Tilt

# 24/7 Recording

**Indoor Security Camera** 















Motion Tracking



## Highlights


### Up, Down, All-Around

Get the full picture of any space in your apartment, dorm or home with Kasa Spot® Pan Tilt. With a 360° horizontal view and 113° vertical view, the Pan Tilt has everything covered. With Motion Tracking and Patrol Mode, track activity from beginning to end and set multiple distinct viewpoints for your camera to monitor at set intervals.




### Your Home. One App.

Turn your home into a true smart home with Kasa Smart. Automate your lights and appliances with smart plugs, bulbs, and switches. Secure your home with Kasa cameras. Control it all from the Kasa Smart app.



### Features







#### 2K HD Video

Sharp and clear 4 MP high resolution offers greater detail and colors, even when you zoom in.

#### Pan Tilt in Real Time

Swipe up, down, left, and right on your phone to rotate and set your camera's point of view.

#### **Motion Tracking**

Track and follow the subject when motion activity is detected to keep it within the camera's field of view.

#### Live View with Two-Way Talk

Watch live video and carry on a conversation from anywhere with your phone or other supported device.

#### Patrol Mode

Set multiple distinct viewpoints and program your camera to keep an eye on each region at selected intervals.

#### **Activity Zones**

Control what alerts you receive by creating up to 16 custom activity zones, at no charge, around areas that are important to you.

#### Starlight Night Vision

Capture colorful videos even in low-light environments with a highly sensitive starlight sensor.

#### Secure Local and Cloud Storage

Save your footage continuously on a microSD card<sup>†</sup> or subscribe to a Kasa Care Plan<sup>‡</sup> to store video clips to the cloud.

†microSD card not included.

<sup>‡</sup>Kasa Care Plans vary by country and region.

## **Specifications**

Camera

Image Sensor: 1/3"

**Resolution:** 4 MP HD (2560 x 1440 pixels) **Night Vison:** 50 nm IR LED, up to 30 ft **Lens:** F/NO: 1.6; Focal Length: 4 mm

View Range: 360° horizontal and 113° vertical

Storage: Supports microSD cards, up to

256 GB\*

\*microSD card required.

**Audio** 

Audio Communication: 2-way audio

Audio Input & Output:

Built-in microphone and speaker

Video

Video Compression: H.264

Frame Rate: 15 fps
Video Streaming: 4MP
Audio Compression: G.711

**Activity Notifications** 

**Input Trigger:** 

Motion detection, Audio detection

**Output Notification:** 

Push notification

Hardware

**Button:** RESET button

Indicator LED: System LED

Adapter Input: 100-240 VAC, 50/60 Hz, 0.2 A

Adapter Output: 5.0 VDC, 1.0 A

Dimensions (W x D x H):

3.2 x 3.2 x 4.4 in. (82 x 82 x 112.6 mm)

Network

Wireless Rate:

11Mbps (802.11b) 54Mbps (802.11g) 72.2Mbps (802.11n) **Frequency:** 2.4 GHz

Wireless Security: WEP, WPA/WPA2-PSK
Security: 128 bit AES encryption with SSL/TLS

System

**Regulatory Certification:** 

FCC, RoHS

**System Requirements:** 

iOS 10+, Android 5.0+

**Environment** 

**Operating Temperature:** 

0°C~40°C (32°F~104°F)

**Storage Temperature:** 

-20°C~60°C (-4°F~140°F)

**Operating Humidity:** 

10%~90% RH non-condensing

**Storage Humidity:** 

5%~90% RH non-condensing

**Package Contents** 

Kasa Spot® PanTilt

Power Adapter

10 ft USB Cable

Quick Start Guide

Mounting Screws

Mounting Plate



Specifications are subject to change without notice. All brands and product names are trademarks or registered trademarks of their respective holders.

© 2020 TP-Link