








## SPECIFICATIONS

<b>Panel Size</b>	27" (69cm)
<b>Panel Resolution</b>	2560 x 1440 (WQHD)
<b>Refresh Rate</b>	165Hz
<b>Response time</b>	1ms GTG
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	G-sync Compatible
<b>ACTIVATED RANGE</b>	48 to 165Hz
<b>Panel Type</b>	Rapid IPS
<b>Brightness (nits)</b>	300 nits
<b>Viewing Angle</b>	178° (H) / 178° (V)
<b>Aspect Ratio</b>	16:9
<b>Contrast Ratio</b>	1000:1
<b>DCR</b>	100000000:1
<b>Pixel Pitch (H x V)</b>	0.2331(H) x 0.2331(V)
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	16.7M
<b>DCI-P3 / sRGB</b>	93% / 125%
<b>Video ports</b>	1x Display Port (1.2) 2x HDMI (2.0b)
<b>Audio ports</b>	1x Earphone out
<b>Active Display Area (mm)</b>	596.736(H) x 335.664(V)
<b>Kensington Lock</b>	Yes
<b>VESA Mounting</b>	100 x 100 mm
<b>Control</b>	5-way OSD navigation joystick
<b>Power Type</b>	External Adaptor 19V 3.42A
<b>Power Input</b>	100~240V, 50~60Hz
<b>Signal Frequency</b>	90.9 to 242.4KHz (H) 30 to 165Hz (V)
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-45° ~ 45°
<b>Adjustment (Height)</b>	0 ~ 130mm
<b>Adjustment (Pivot)</b>	-90° ~ 90°
<b>Console Mode</b>	FHD @ 120Hz
<b>Power consumption</b>	32W
<b>Compatibility</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.


## FEATURES

- 
**165Hz High Refresh Rate**  
 Experience smooth gaming with a blazing fast 165Hz refresh rate, that gives you the upperhand in fast moving games
- 
**eSports Gaming**  
 MSI eSports gaming monitor will enhance your competitive gameplay to ensure you are always at your best levels.
- 
**Rapid IPS**  
 Provides 1ms GTG fast response time, optimizes screen colors and brightness.
- 
**WQHD High Resolution**  
 Game titles will even look better, displaying more details.
- 
**1ms Fast Response Time**  
 Eliminate screen tearing and choppy frame rates with 1ms response time.



<b>Carton Dimension (W X H X D)</b>	745 x 490 x 225 mm / 29.33 x 19.29 x 8.86 inch
<b>Weight (NW / GW)</b>	6.3kg / 9.4kg 13.89lbs / 20.72lbs
<b>Dimension (W x H x D)</b>	614.93 x 535.39 x 233.68 mm / 24.21 x 21.08 x 9.2 inch
<b>Frameless Design</b>	Yes
<b>Note</b>	Display Port: 2560 x 1440 (Up to 165Hz) HDMI: 2560 x 1440 (Up to 144Hz) The color gamut follows the CIE 1976 testing standard.

## CONNECTIONS



1. 5-way joystick navigator
2. 1x Display Port (1.2)
3. 2x HDMI (2.0b)
4. Earphone out
5. DC jack
6. Kensington lock