



## SPECIFICATIONS

<b>Panel Size</b>	31.5" (80 cm)
<b>Panel Resolution</b>	1920x1080 (FHD)
<b>Refresh Rate</b>	165Hz
<b>Response time</b>	1ms (MPRT)
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	FreeSync Premium
<b>ACTIVATED RANGE</b>	48Hz-165Hz
<b>Panel Type</b>	VA
<b>Brightness (nits)</b>	250
<b>Viewing Angle</b>	178°(H)/178°(V)
<b>Aspect Ratio</b>	16:9
<b>Contrast Ratio</b>	4000:1
<b>DCR</b>	100000000:1
<b>Pixel Pitch (H x V)</b>	0.36375(H) x 0.36375(V)
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	16.7M
<b>DCI-P3 / sRGB</b>	94.55% / 120.25%
<b>Video ports</b>	1x DP(1.2)□ 1x HDMI (2.0) 1x HDMI (1.4)
<b>USB ports</b>	1x USB 2.0 Type B
<b>Audio</b>	1x Earphone out
<b>Active Display Area (mm)</b>	698.4(H) x 392.85(V)
<b>Kensington Lock</b>	Yes
<b>VESA Mounting</b>	75 x 75 mm
<b>Power Type</b>	External Adaptor 19V 3.42A
<b>Power Input</b>	100~240V, 50~60Hz
<b>Signal Frequency</b>	30-200KHz(H) / 48-165Hz(V)
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-30° ~ 30°
<b>Curved</b>	1500R
<b>Adjustment (Height)</b>	0 ~ 90 mm
<b>Power consumption</b>	45W
<b>Adjustment (Pivot)</b>	-5° ~ 5°
<b>Console Mode</b>	FHD @ 120Hz

## FEATURES



### Mystic Light

Make your build look on fire or cold as ice. You are in control. Customize colors and effects with RGB LED.



### 165Hz High Refresh Rate

Experience smooth gaming with a blazing fast 165Hz refresh rate, that gives you the upperhand in fast moving games



### Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.



### Curved Gaming™

View more of your game. MSI Curved Gaming™ monitors are perfect for gamers to play their games.



### 1500R

Enjoy the most immersive gameplay with 1500R curvature rate.



### 1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



<b>Compatibility</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
<b>Carton Dimension (W X H X D)</b>	945 x 173 x 545 mm / 37.2 x 6.81 x 21.46 inch
<b>Weight (NW / GW)</b>	6.59 kg / 8.98 kg 14.53 lbs / 19.80 lbs
<b>Dimension (W x H x D)</b>	710 x 286 x 465 mm / 27.95 x 11.26 x 18.31 inch
<b>Frameless Design</b>	Yes
<b>Note</b>	Display Port: 1920 x 1080 (Up to 165Hz) HDMI 1920 x 1080 (Up to 144Hz) *sRGB and DCI-P3 follow CIE1976 standard

## CONNECTIONS



1. 5-way joystick navigator
2. 1x USB 2.0 Type B
3. 1x HDMI (2.0)
4. 1x HDMI (1.4)
5. 1x Display Port (1.2)
6. 1x Earphone out
7. 1x DC Jack