

WorkForce® WF-2850

Wireless | Print | Copy | Scan | Fax



All-in-One

Home Office

The compact, wireless all-in-one with intuitive color display.

Save time and paper — auto 2-sided printing, plus 30-page Auto Document Feeder for copying and scanning with ease

High-quality performance — pigment Black Claria® ink for crisp black text, plus professional-quality documents, proposals and reports

Fast printing — 10.3 ISO ppm (black) and 4.5 ISO ppm (color)[†]

Simple setup and navigation — 2.4" color LCD to easily print, copy, scan and fax

Affordable individual ink cartridges — replace only the cartridge that runs out

Easy wireless — print from iPad®, iPhone®, Android™ tablets and smartphones¹; includes Wi-Fi Direct®²

Hands-free voice-activated printing³ — to print a variety of projects and documents, including your to-do and shopping lists

Reliable — designed for jam-free printing

Save space on your desktop — great performance in a compact, space-saving design

Reload paper less often — 100-sheet paper feed for added productivity



Designed for use exclusively with Epson® cartridges.*

Print

Printing Technology 4-color (CMYK) drop-on-demand MicroPiezo[®] inkjet technology
Printer Language Epson ESC/P[®]-R
Maximum Print Resolution 5760 x 1440 optimized dpi
Print Speed* 10.0 ISO ppm (black), 4.5 ISO ppm (color)
Minimum Ink Droplet Size 3 picoliters

Mobile Printing and Scanning

Epson Connect™ Solutions! Epson Email Print, Epson Remote Print, Epson iPrint™ App (iOS[®], Android), Epson Print and Scan App (Windows[®]), Creative Print App (iOS, Android)
Other Apple[®] AirPrint[®], Google Cloud Print™, Android printing, Fire OS™ printing, Mopria[®] Print Service, Easy Photo Scan, Scan to Cloud†

Copy

Copy Quality Color/Black-and-white: Draft/Normal
Copy Quantity 1 – 99 (PC-free)
Maximum Copy Size 8.5" x 11", 8.5" x 14"
Copy Features Automatic 1-sided to 2-sided, fit to page, automatic reduction and enlargement (25 – 400%), copy input resolution flatbed 300 x 300, 600 x 600, copy input resolution ADF 300 x 300, 300 x 600, copy print resolution 600 x 600, 600 x 1200, ID copy, adjustable copy density, collate 100 sheets, 1-sided to 1-sided, 1-sided to 2-sided, adjustments – density, contrast, color, sharpness

Scan

Scanner Type Color flatbed
Photoelectric Device Color CIS line sensor
Optical Resolution 1200 dpi
Hardware Resolution 2400 dpi
Maximum Resolution 9600 dpi interpolated
Scanner Bit Depth 48-bit color / 24-bit output
Scan Bed Size 8.5" x 11.7" max.
Scan Features Scan to PDF, Scan to Computer (USB and network), Scan to Email (via EpsonConnect)

Fax

Black-and-white and color
 Modem: 33.6 Kbps — as fast as 3 sec per page
 Memory: Up to 100 pages
 Speed dials: 60 (max.)
 PC-Fax

Auto Document Feeder

30 sheets
 1-side to 1-side
 8.5" x 14" max. size

Connectivity

Standard Connectivity Hi-Speed USB, Wireless (802.11 b/g/n)[‡], Wi-Fi Direct[‡]
Operating Systems Windows 7/Windows 8/8.1/Windows 10 (32-bit, 64-bit), Windows XP SP3 (32-bit), Windows XP Professional x64 Edition SP2, Mac[®] OS[®] X 10.6.8 – macOS[®] 10.14.x[‡]
 Internet access is required to install OS X[®] drivers and software.

Paper Handling

Maximum Paper Size 8.5" x 44"
Paper Sizes 3.5" x 5", 4" x 6", 5" x 7", 8" x 10", Letter, Legal, A4, B5, A5, A6, half letter, executive, user definable (3.5" – 44" in length)
Borderless Photo Sizes 3.5" x 5", 4" x 6", 5" x 7", 8" x 10", Letter, A4, 16:9 wide
Paper Types Supports plain paper, Epson Bright White Paper, Brochure & Flyer Paper Matte Double-sided, Ultra Premium Presentation Paper Matte, Premium Presentation Paper Matte, Premium Presentation Paper Matte Double-sided, Presentation Paper Matte, Ultra Premium Photo Paper Luster, Ultra Premium Photo Paper Glossy, Premium Photo Paper Semi-gloss, Premium Photo Paper Glossy, Photo Paper Glossy, Photo Quality Adhesive Sheets, Iron-on Cool Peel Transfer paper
Envelope Types No. 10
PC-free Paper Support Plain (letter, A4), Photo (4" x 6", 5" x 7", Letter, A4)
Input Paper Capacity 100 sheets plain paper/20 sheets Premium Photo Paper Glossy

General

Display 2.4" color LCD
Temperature
 Operating: 50 ° to 95 °F (10 ° to 35 °C)
 Storage: -4 ° to 104 °F (-20 ° to 40 °C)
Relative Humidity
 Operating: 20 – 80%
 Storage: 5 – 85% (no condensation)
Sound Level 36 dB(A)
Rated Voltage AC 100 – 120 V/220 – 240 V
Rated Frequency 50 – 60 Hz
Rated Current 0.5 Amp

General (continued)

Power Consumption
 Standalone Copy Printing: Approx. 13 W (ISO 24712)
 Power Off: Approx. 0.3 W, ENERGY STAR[®] qualified

Safety Approvals
 Safety standards UL60950, CSA C22.2 No. 60950
 EMI FCC Part 15 subpart B class B
 CAN/CSA-CE/IEC CISPR 22 class B

Country of Origin Indonesia
Weight and Dimensions (W x D x H)

Printing: 14.8" x 22.8" x 9.5"
 Storage: 14.8" x 11.8" x 8.6"
 Weight: 11.5 lb

What's in the Box WorkForce WF-2850 printer, instruction booklets, CD-ROM with drivers, power cord, 4 Claria Ink cartridges (1x Black ink cartridge and 3x color ink cartridges: 1x Cyan, 1x Magenta, 1x Yellow)

Software Included Epson printer driver, Epson Scan[‡], Easy Photo Scan

Warranty 1-year limited warranty in the U.S. and Canada

Ink

Ink Type Claria
Ink Cartridges 4x individual ink cartridges (1x Cyan, 1x Magenta, 1x Yellow and 1x Black)
Replacement Ink Cartridges[§]
 212 Standard-capacity Black, Cyan, Magenta, Yellow (Yield, ISO pages – Black: 150, Color: 130)
 212XL High-capacity Black, Cyan, Magenta, Yellow (Yield, ISO pages – Black: 500 Color: 350)
 Printer is designed for use with Epson cartridges only, not third-party cartridges or ink*.

Eco Features

ENERGY STAR qualified
 RoHS compliant
 Save up to 50% on paper with auto 2-sided printing
 Recyclable product†
 Epson America, Inc. is a SmartWay[®] Transport Partner[®]

Ordering Information

WorkForce WF-2850 C11CG31201

*This product uses only genuine Epson-brand cartridges. Other brands of ink cartridges and ink supplies are not compatible and, even if described as compatible, may not function properly.

† Black and color print speeds are measured in accordance with ISO/IEC 24734. Actual print times will vary based on factors including system configuration, software, and page complexity. For more information, visit www.epson.com/printspeed | 1 Most features require an Internet connection to the printer, as well as an Internet- and/or email-enabled device. For a list of Epson Connect enabled printers and compatible devices and apps, visit www.epson.com/connect | 2 Wi-Fi CERTIFIED™; level of performance subject to the range of the router being used. Wi-Fi Direct may require printer software. | 3 Voice-activated printing is not available with the Epson Expression[®] EcoTank[®] ET-2500 and ET-2550 printers, and Epson printers that are 5 or more years old. Epson Connect and voice-activated device and account registration required. | 4 Requires an Internet connection, a free Epson Connect account and a destination email address or cloud storage account. For a list of supported cloud services, visit www.epson.com/connect | 5 Some applications and/or functions may not be supported under Mac OS X. | 6 Replacement cartridge yields are based on ISO/IEC 24711 tests in Default Mode printing continuously. Replacement cartridge photo yields are based on the ISO/IEC 29102 photo yield standard. Cartridge yields vary considerably for reasons including images printed, print settings, temperature and humidity. Yields may be lower when printing infrequently or predominantly with one ink color. All ink colors are used for printing and printer maintenance, and all colors have to be installed for printing. For print quality, part of the ink from the included cartridges is used for printer startup and a variable amount of ink remains in the cartridges after the "replace cartridge" signal. For details, see www.epson.com/inkinfo | 7 For convenient and reasonable recycling options, visit www.epson.com/recycle | 8 SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency.



Epson America, Inc.
 3840 Kilroy Airport Way, Long Beach, CA 90806

Epson Canada Limited
 185 Renfrew Drive, Markham, Ontario L3R 6G3

www.epson.com
www.epson.ca

Contact:



Specifications and terms are subject to change without notice. EPSON, ECOTANK, Epson ESC/P, Claria, Expression, WorkForce and MicroPiezo are registered trademarks, EPSON Exceed Your Vision is a registered logomark and Better Products for a Better Future, Epson Connect and Epson iPrint are trademarks of Seiko Epson Corporation. AirPrint, Apple, iPad, iPhone, Mac, macOS and OS X are trademarks of Apple Inc., registered in the U.S. and other countries. Android and Google Cloud Print are trademarks of Google LLC. Windows is either a registered trademark or trademark of Microsoft Corporation in the United States and/or other countries. Wi-Fi Direct[®] is a registered trademark and Wi-Fi CERTIFIED™ is a trademark of Wi-Fi Alliance[®]. SmartWay is a registered trademark of the U.S. Environmental Protection Agency. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks. Copyright 2019 Epson America, Inc. CPD-57063 Com-SS-Oct-13 4/19