



Take control of your online video with the VTWC40 Premium Full HD 1080p Autofocus Webcam which delivers full HD video at 60 FPS. Enter a new realm of realistic clarity in your office or gaming room so you can present professionally and confidently. The VTWC40 is compatible with most video conferencing apps including Microsoft Teams, Zoom, Google Meet and more. The VTWC40 is UVC compliant. You don't have to install any drivers so you can be ready for any last minute meetings or hangouts with friends. The built in dual microphones allow you to be heard clearly while speaking at a normal volume.

Key Features

- 1080p (1920x1080) High Definition camera lets you present yourself clearly and professionally in your home or office.
- Autofocus - automatically keeps the focus on you for a more consistent picture quality and perfectly sharp images and video. Precision autofocus ensures your camera will stay in focus on the subject no matter what happens in the background.
- Built in ring-light with touch control provides additional lighting for use in dark rooms. With 2 brightness and color settings (or off), the VTWC40 provides a compact solution for high quality video capture.
- Compatible with most video conferencing software including MS Teams, Zoom, Skype, Cisco Webex, Google Meet, Facebook Messenger and more.
- No Drivers Required - UVC Compliant means no setup time and ready to go as soon as you plug it in.
- Privacy cover keeps your lens protected and assures you peace of mind against spyware and other hacking tools.
- Dual built-in microphones ensure crystal clear audio so you can speak at a normal volume and still be heard.
- The camera allows for a 360 degree horizontal rotation and 30 degrees of tilt to find the best position for your setup.
- The tripod mount allows for additional setup options to find your best angle.



PN 901442 | UPC 7 84090 04602 4

Technical Specifications

- Resolution supported 1920 x 1080
- Frame Rate up to 60 FPS
- Pixels: 2 million
- View Angle: 96°
- Image Sensor: HD CMOS
- Focus: Automatic
- Built-In Ring Light: 2 Brightness and color settings
- Compatibility: Windows 10, 8, 7, XP SP3, Chromebook, MAC, Linux
- Interface: USB 2.0
- Microphone: Dual built-in microphone
- Cable Length: 1.7m / 5' 7"
- Working Temperature: -10 to 40° C
- Power Consumption: <1.25 W



All specifications are subject to change without notice. Products may not be available in all markets. The VisionTek name and design are registered trademarks of VisionTek Products, LLC. All other registered and unregistered trademarks are the property of their respective owners.

FOR MORE INFORMATION CONTACT: 1-866-883-5411 | sales@visiontek.com