

Manufacturer Part #	GS6611290
OS	Windows 10 Pro (MSI recommends Windows 11 Pro for business.)
CPU	Core i9-11900H
CPU Speed	2.5 - 4.9GHz
Chipset	HM570
Color	Core Black
Screen Size	15.6" FHD, Anti-Glare Wide View Angle 240Hz 3.5ms
Resolution	1920x1080 (16:9)
GPU	NVIDIA® GeForce RTX™ 3080 Laptop GPU Up to 1365MHz Boost Clock, 95W Maximum Graphics Power with Dynamic Boost. *May vary by scenario
Video Memory	16G GDDR6
Keyboard	Steel Series per-Key RGB with Anti-Ghost key (84 Key)
Audio	Nahimic 3 / Hi-Res Audio
Speaker	2 x Dynaudio 2W Speakers
Memory	64GB (32G*2) DDR4 3200MHz
HDD Capacity	1TB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	-
LAN	Killer E3100 2.5GbE
WLAN	Killer WiFi 6E AX1675 (2x2 )
Bluetooth	BT 5.2
Card Reader	-
Webcam	IR 720p HD Webcam
USB	3x USB 3.2 Gen2
Type-C Port	1x Thunderbolt™ 4; 1x USB 3.2 Gen2/DP
Video Port	HDMI (supports 4K @ 120Hz, 8K @ 60Hz)
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	230W Slim
Battery Pack	4 cell (99.9Whr)
Dimension	14.17"x9.65"x0.71"
Weight	4.63lbs
Manufacturer Warranty	3 year on site warranty