



The most affordable Brother INKvestment Tank printer!*

**INKVESTMENT TANK COLOR INKJET
THREE-IN-ONE WITH UP TO 1 YEAR OF
INK IN-BOX[†]**

Ideal choice for home & home offices

This revolutionary color inkjet printer features reengineered high capacity ink cartridges that provide up to 1-year of uninterrupted printing approximately 100 pages per month, using only the cartridges provided in-box.[‡]

**Put the power of
printing at your
fingertips⁵**

Go mobile with the simple to use Brother Mobile Connect⁵ App that delivers easy onscreen menu navigation for printing, copying, scanning, and device management from your mobile device.

- Up to 1-Year of Ink In-Box[†]
- Flatbed scanner
- Borderless Printing
- Wireless*, Wireless Direct, and USB connectivity
- Stay Genuine with the LC404 INKvestment Tank Ink Cartridge Series.

MFC-J1205W

Specifications:

Print Technology	4-cartridge Color Inkjet
LCD Display (type/size)	LED
Paper Size (maximum)	Paper Tray: Up to 8.5" x 11.7" (Letter size)
Print Speed (maximum)¹	Black (ISO/IEC 24734): Up to 16ppm Color (ISO/IEC 24734): Up to 9ppm
Print Resolution (maximum)²	Windows: Up to 1200 x 6000 dpi Mac: Up to 1200 x 3600 dpi
Borderless Printing Capability³	Yes (Letter, A4, A6, 4"x6", 5"x8", 3.5"x5", 5"x7" only)
Paper Input Capacity (maximum)	Up to 150 sheets
Standard Interfaces^{4,5}	Wireless (802.11 b/g/n), Wireless Direct, Hi-Speed USB 2.0
Copy Speed (maximum)⁶	Black (ISO/IEC 29183): 8ipm Color (ISO/IEC 29183): 3ipm
Copy Resolution (maximum)²	Up to 1200 x 1200 dpi
Copy Reduction/Enlargement	25% - 400% in 1% increments (Remote Copy) ⁷
Copy Options	2 in 1, 2 in 1(ID), 4 in 1 (Remote Copy) ⁷
Scanner Type	Color Flatbed (CIS)
Document Glass Size	Letter Size 8.5" x 11.7"
Scan / Copy Size (maximum)	Letter Size (8.5" x 11")
Scan Resolution (maximum)²	Optical: 2400 x 1200 (Flatbed) Interpolated: 19200 x 19200 dpi
Web Connectivity⁸	GOOGLE DRIVE™, EVERNOTE®, DROPBOX, BOX, ONEDRIVE, ONENOTE
Near Field Communication (NFC)	No
Operating Systems Compatibility⁹	Windows 7 SP1/8.1/10, Server 2008/2008, R2/2012/2012, R2/2016/2019 MAC®: OS v10.14.6/10.15.x/10.16.x
Mobile Device Compatibility⁵	Mopria®, AirPrint®, Wireless Direct, and Brother Mobile Connect
Maximum Monthly Duty Cycle¹⁰	Up to 2,500 pages
Recommended Monthly Volume¹¹	50 to 100 pages
Warranty	2-year Limited Warranty
ENERGY STAR® Qualified	Yes

Supplies & Accessories¹²:

LC404BK	Black INKvestment Tank Ink Cartridge - 750 pages ¹³
LC404C	Cyan INKvestment Tank Ink Cartridge - 750 pages ¹³
LC404M	Magenta INKvestment Tank Ink Cartridge - 750 pages ¹³
LC404Y	Yellow INKvestment Tank Ink Cartridge - 750 pages ¹³
BP71GLTR	Innobella Letter-size Glossy Inkjet Paper (20 sheets)
BP71GP20	Innobella 4" x 6" Glossy Photo Paper (20 sheets)
BP60MPLTR	Innobella Letter-size Multi-Purpose Paper (500 sheets)



At your side support. Online, call, or live chat – free support for the life of your printer. At Brother, we want to ensure that your experience with us is exceptional. Visit us at brother-usa.com where you can download the latest product drivers and software, view product manuals, learn how to get the most out of your product with how-to videos and find answers to frequently asked questions.



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. www.brotherearth.com

COMPATIBLE WITH
WINDOWS



Works with
Apple AirPrint



¹ ISO print speed based on ISO/IEC 24734 (after first set of ISO test pages). For more details, please visit www.brother-usa.com/printspeed.

² Resolutions are listed by vertical by horizontal dpi.

³ Minimum default margins .12" on all sides.

⁴ Cables not included.

⁵ Requires an Internet connection. The Brother Mobile Connect free app download is not available in all countries.

⁶ ISO copy speed is based on ISO/IEC 29183. For more details, visit www.brother-usa.com.

⁷ Feature via Brother Mobile connect Application. Brother Mobile Connect free app download is not available in all countries.

⁸ Requires Internet Connection and an account with desired service. When connected to a PC with Brother iPrint&Scan applicable software.

⁹ See system requirements on www.brother.com

¹⁰ Maximum number of printed pages per month and can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

¹¹ The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond the range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.

¹² Additional purchase required.

¹³ Approximate page yields in accordance with ISO 24711. For more page yield information see www.brother.com/pageyield.

* Based on estimated Street Price at available retailers and e-tailers; pricing may vary.

† Based on average monthly print volumes of approximately 100 pages at 60% black pages/40% color pages in accordance with ISO/IEC 24711 using 4 cartridges provided in-box. For additional page yield information, see www.brother.com/pageyield.