

Tripp Lite

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

8-Port DisplayPort/USB KVM Switch with Audio/Video and USB Peripheral Sharing, 4K 60 Hz, 1U Rack-Mount

MODEL NUMBER: B024-DPU08











Controls up to 8 DisplayPort-enabled laptop or notebook computers using one centralized DisplayPort monitor and USB keyboard/mouse.

Features

Connects 8 DisplayPort Devices to a Single DisplayPort Monitor, Keyboard and Mouse

This rack-mount KVM switch lets you access, control, boot and reboot up to eight computers or other devices with DisplayPort connectors at the same time. In addition to desktop and notebook computers, the KVM also connects up to eight media centers, gaming systems, Blu-ray and DVD players, cable and satellite boxes, DVRs and other DisplayPort-enabled devices. All eight computers share one DisplayPort and/or HDMI monitor, USB keyboard and USB mouse, which saves space on your desk or workspace.

Connect up to 128 Computers to One Original Console

You can also cascade two levels of B024-DPU08 KVM switches, allowing centralized access to as many as 128 computers using a single monitor, keyboard and mouse.

Switching Between Computers Is Fast and Easy

Use the front-panel pushbuttons, RS-232 commands, hotkeys or multi-lingual On-Screen Display (OSD) with text-based interface for quick and easy toggling between computers. Or you can use Auto Scan mode to scan all connected computers in five-second intervals automatically. Orange LEDs indicate which computer is currently selected.

Cables Are Included for Fast and Simple Setup

Connect your DisplayPort and/or HDMI monitor, keyboard, mouse, and (optional) speakers to the KVM's console ports. Then, use the included DisplayPort and USB cables to connect your computers to the KVM. The plug-and-play B024-DPU08 requires no software, so you can connect and use it immediately. It works with all major operating systems, including Windows, macOS, Sun and Linux.

USB Hub Lets You Share Peripherals between Computers

The built-in dual-port USB 3.1 Gen 1 hub allows you to share USB peripherals, such as printers, hard drives, scanners, webcams and flash drives, between all connected computers. Because the USB ports operate independently, you can print documents from one computer while working on a different computer. The hub is backward compatible with earlier USB generations. LEDs indicate which computer is using the connected USB device.

Highlights

- Supports true 4K resolutions up to 4096 x 2160 @ 60 Hz with HD audio
- Cascade up to 2 levels to control as many as 128 computers from a single console
- Built-in 2-port USB 3.1 hub lets you share USB peripherals among connected computers
- Pushbuttons, hotkeys and onscreen display allow easy toggling between computers
- Firmware-upgradable KVM works with Windows, Mac, Sun and Linux operating systems

Applications

- Share the keyboard, mouse and DisplayPort screen of a laptop or notebook computer with multiple computers
- Connect up to 8 gaming consoles, media centers and other A/V devices for a home theater system with 4K resolution
- Save money and space by sharing USB peripherals, such as a printer and external hard drive, among all connected computers
- Control up to 128 computers by cascading the B024-DPU08

System Requirements

- Console with DisplayPort and/or HDMI monitor, USB keyboard/mouse and (optional) speakers with 3.5 mm connectors
- Computer with DisplayPort, USB-A and (optional) 3.5 mm audio ports
- Windows, macOS, Sun or Linux operating system

Package Includes

- B024-DPU08 8-Port DisplayPort/USB KVM Switch
- (2) DisplayPort 1.4 cables, 5 ft. (1.5 m)
- (2) USB 3.0 A-to-B cables, 6 ft. (1.8 m)
- (2) 3.5 mm audio cables, 6 ft.





Transmits Crystal-Clear 4K Video and High-Definition Audio

The B024-DPU08 supports true 4K video ($4\overline{0}$ 96 x 2160) at 60 Hz and 2.1-channel surround sound with full bass response. With independent audio switching, you can listen to music or other audio from one computer while working on a different computer. The front-panel audio jacks have priority over the rearpanel jacks.

Stack Units to Expand Your Workstation and Enhance Your Productivity

Stack as many as eight B024-DPU08 KVM switches on a level surface to take advantage of multi-display mode. Depending on the number of stages in your stack, your installation may offer dual-display, triple-display, quad-display or multi-display scenarios, up to eight stages.

Designed for Convenient Mounting with Included Hardware

The heavy-duty metal housing comes with mounting hardware for 1U installation in an EIA-standard 19-inch rack. It also allows desktop deployment on included rubber feet that help prevent the unit from sliding. The included power supply comes with a detachable C13-to-C14 cord.

- Firmware upgrade cable, 6 ft.
- External power supply (Input: 100–240V, 50/60 Hz; Output: 12V 3.3A) with detachable C13to-C14 cord, 4 ft. (1.2 m)
- (4) Rubber feet
- Rack-mounting hardware
- · Quick Start Guide

Specifications

OVERVIEW		
UPC Code	037332263728	
Technology	DisplayPort; Stereo Audio; USB; USB 2.0 (High Speed)	
VIDEO		
Max Supported Video Resolution	4K @ 60Hz (4096 x 2160)	
Max Number of Ports (Entire Chain)	128	
AUDIO		
Audio Specification	Stereo	
INPUT		
External Power Supply Plug(s)	IEC-320-C14	
POWER		
External Power Supply Input Specs (V / Hz / A)	100-250V, 50/60Hz, 1.2A	
External Power Supply Output Specs (V / A)	12V 3.33A	
External Power Supply Cord Length (ft.)	3.93	
External Power Supply Cord Length (m.)	1.2	
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 9.5mm, Positive Pin, Negative Sleeve	
External Power Supply Certifications	CCC; CE; FCC; GS; PSE; RoHS; TUV; UL; WEEE; cUL	
USER INTERFACE, ALERTS & CONTROLS		





LED Indicators	Orange (x8) - On Line/Selected Port, Green (x1) - Power, Green (x8) - USB Link	
PHYSICAL		
Color	Black	
Material of Construction	Metal	
Rackmountable	Yes	
Shipping Dimensions (hwd / cm)	13.31 x 49.91 x 32.41	
Shipping Dimensions (hwd / in.)	5.24 x 19.65 x 12.76	
Shipping Weight (kg)	4.79	
Shipping Weight (lbs.)	10.56	
Unit Dimensions (hwd / cm)	43.24 x 21.43 x 4.40	
Unit Dimensions (hwd / in.)	17.02 x 8.44 x 1.73	
Unit Packaging Type	Вох	
Unit Weight (kg)	3.11	
Unit Weight (lbs.)	6.85	
ENVIRONMENTAL		
Operating Temperature Range	32 to 104 F (0 to 40 C)	
Storage Temperature Range	-4 to 140 F (-20 to 60 C)	
Relative Humidity	0 to 80% RH, Non-Condensing	
BTUs	136	
Power Consumption (Watts)	18.44	
COMMUNICATIONS		
IP Remote Access	No	
CONNECTIONS		
Ports	8	
PC/Server Connections	DisplayPort	
Side A - Connector 1	DISPLAYPORT (FEMALE)	
Side A - Connector 2	(2) USB A (FEMALE)	
Side A - Connector 3	3.5MM (FEMALE)	
Side B - Connector 1	(8) DISPLAYPORT (FEMALE)	
Side B - Connector 2	(8) USB B (FEMALE)	
Side B - Connector 3	(8) 3.5MM (FEMALE)	
Computer Keyboard and Mouse Interface	USB	





Computer Monitor Interface	Displayport	
Console Keyboard and Mouse Interface	USB	
Console Monitor Interface	Displayport	
Connector Plating	Nickel	
FEATURES & SPECIFICATIONS		
Number of Users	1	
NIAP-Certified Secure	No	
On-Screen Display (OSD)	Yes	
Port Selection	Hotkey; OSD; Pushbutton; Remote Selector	
Displayport Specification	1.2	
HDCP Specification	2.2	
Driver Required	No	
Cat5 KVM Switch	No	
STANDARDS & COMPLIANCE		
Certifications	RoHS, REACH, CE, FCC, NOM, WEEE	
WARRANTY		
Product Warranty Period (Worldwide)	1-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies