

## PERFORMANCE

### Processor

Intel® Xeon® W-2225 (4C / 8T, 4.1 / 4.6GHz, 8.25MB)

### Processor Sockets

1x FCLGA2066

### Discrete Graphics

NVIDIA® RTX A6000 48GB

### Chipset

Intel C422

### Memory

4x 16GB RDIMM DDR4-2933 ECC

### Memory Slots

8 DIMM sockets with 4 channels

### Max Memory

Up to 512GB (8x 64GB RDIMMs) DDR4-2933

### M.2 SSD RAID Controller

RAID 0/1

### M.2 SSD Drive

1x 1TB SSD M.2 PCIe NVMe Opal

### HDD Controller

Onboard Intel RSTe SATA

### Storage Support

Up to 6x 3.5" SATA HDD / 2.5" SATA HDD / 2.5" SATA SSD + 9x M.2 PCIe SSD + 1x PCIe AIC SSD

- 3.5" HDD up to 6TB each
- 2.5" SATA HDD up to 500GB each
- 2.5" SATA SSD up to 2TB each
- M.2 PCIe SSD up to 2TB each
- PCIe AIC SSD up to 480GB each

### Audio Chip

High Definition (HD) Audio, Realtek® ALC662 codec

### Power Supply

1000W Platinum Fixed

## DESIGN

### Keyboard

USB Traditional Keyboard, Black, English

### Mouse

USB Calliope Mouse

### Expansion Slots

- Two PCIe 3.0 x16
- Two PCIe 3.0 x4
- One PCIe 3.0 x8
- One PCI

### M.2 Slots

Up to 9x M.2 SSD:

- 2 via onboard slots
- 4 via Quad M.2 to PCIe adapter
- 3 via Single M.2 to PCIe adapter

### Bays

- 2x 3.5" disk bay (standard)
- 4x 3.5" disk bay (optional):  
2 bays come with 3rd disk or Storage Bay Upgrade Kit  
2 bays via flex bay

### Flex Bays

2x flex bays, supports the following:

- 2x half-height optical drives
- 2x 5.25" 9.0mm optical drives
- 1x 5.25" 9.0mm optical drive + 2x 3.5"/2.5" SATA SSD/HDD
- 1x 3.5"/2.5" SATA SSD/HDD with Front Access Storage Enclosure
- 1x flex module for the following options:  
Tray 1: 9.0mm optical  
Tray 2: 15-in-1 USB 3.1 Gen 1 reader, 2x Thunderbolt™, or 4-digit diagnostic display  
Port 1 and 2: Front USB 3.1 Gen 1 Type-C or eSATA
- 2x M.2 SSD with 2x Front Removable Drive Enclosures

### Dimensions (WxDxH)

165 x 460 x 440 mm (6.5 x 18.1 x 17.3 inches, with feet)

### Weight

24 kg (52.91 lbs, maximum configuration)

## CONNECTIVITY

### Onboard Ethernet

1x GbE RJ-45

### Card Reader

SD Card Reader

### Front Ports

- 3x USB 3.1 Gen 1
- 1x USB 3.1 Gen 1 (Always On and fast charge)
- 1x headphone / microphone combo jack (3.5mm)

### Rear Ports

- 4x USB 3.1 Gen 1
- 1x line-in (3.5mm)
- 1x microphone (3.5mm)
- 1x Ethernet (RJ-45)
- 2x USB 2.0
- 2x PS/2 ports (keyboard / mouse)
- 1x line-out (3.5mm)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0, TCG certified

### Physical Locks

Kensington® Security Slot

## MANAGEABILITY

### System Management

Intel® vPro with AMT 11, DASH

## SERVICE

### Base Warranty

3-year, Onsite

### Included Upgrade

3Y Premier Support Upgrade from 3Y Onsite (5WSOU26649)

## CERTIFICATIONS

### Green Certifications

- EPEAT™ Silver
- RoHS compliant
- ENERGY STAR® 8.0 (on model 30BE00B7US)
- GREENGUARD®

### ISV Certifications

Please visit [www.thinkworkstations.com/isv-certifications/](http://www.thinkworkstations.com/isv-certifications/)

## SOFTWARE

### Operating System

Windows® 10 Pro 64 for Workstations, English

## MODEL

<b>TopSeller</b>	: Yes	<b>Announce Date</b>	: 2021-06-15
<b>EAN / UPC / JAN</b>	: 196118049137	<b>End of Support</b>	: 2028-01-07



## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Kensington MicroSaver 2.0 Cable Lock from Lenovo

4X60N86662

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

## Recommended Services

BEST	5Y Lenovo Protect (Premier Support + ADP + KYD + International Upg) (5PS1D67032)
BETTER	5Y Lenovo Support (Premier Support + KYD + International Upg) (5PS1D67028)
GOOD	4Y Lenovo Support (Premier Support + KYD + International Upg) (5PS1D67027)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference