

Safe-IT 5-Outlet Surge Protector, USB-A/USB-C Ports, 5-15P Direct Plug-In, 1050 Joules, Antimicrobial Protection, Black

MODEL NUMBER: SK5BUCAM



Swivel surge protector with antimicrobial protection safeguards your valuable electronics against dangerous surges, spikes and line noise.

Features

5-Outlet Surge Protector with USB Charging Safeguards Your Sensitive Electronics

Ideal for your home, office, retail or industrial workstation, this Safe-IT™ surge protector features a surge protection rating of 1050 joules to defend your valuable electronic components against power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the SK5BUCAM protects all five, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

Rotating NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, wireless router, desk lamp and other home/office electronics into five NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. Four of the outlets rotate 90 degrees on two bars of two outlets each to allow greater flexibility in placing connected devices or accepting bulky transformers without blocking adjacent outlets.

2 USB Ports Share 3.9 Amps of Charging Power

One USB-C port and one USB-A port are available for charging your smartphone, tablet or other USB mobile devices. They share 3.9A for charging multiple devices at the same time.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

The unit plugs directly into a wall outlet, avoiding annoying cord clutter. An integrated 15A circuit breaker protects outlets and automatically cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. A green LED confirms at a glance that your connected equipment is protected.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The SK5BUCAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi,

Highlights

- 4 rotating/1 static 5-15R outlets distribute AC power to home/office equipment
- 1050 joules protect your valuable electronics against dangerous surges and spikes
- Plugs directly into the wall (no cord required) for easy installation and no cable clutter
- USB ports share 3.9A for fast charging of phones and other mobile devices
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Applications

- Protect computers, peripherals, home theater equipment and other valuable electronics against AC power surges and spikes
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges
- Charge smartphones, tablets or other USB devices via USB ports

Package Includes

- SK5BUCAM 5-Outlet Surge Protector, Black
- Owner's manual

mold and mildew.

Specifications

OVERVIEW	
UPC Code	037332263582
Product Type	Surge Protector
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(5) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Outlet Orientation	Rotatable
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LEDs confirm suppressor "protected" (green)
CHARGING	
Number of Charging Ports	2
Total Charging Watts	19.5
Charging Method	USB

Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Ports / Amps	(2) 3.9A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500, 500, 500
EMI / RFI Filtering	150 kHz to 30 MHz
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Housing Color	Black
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	29mm
Receptacle Color	Black
Unit Dimensions (hwd / in.)	4.700 x 1.500 x 4.900
Unit Dimensions (hwd / cm)	12.0 X 3.81 X 12.5
Unit Weight (lbs.)	0.73
Unit Weight (kg)	0.33
FEATURES & SPECIFICATIONS	
Rotatable Outlets	Yes
Antimicrobial	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico); UL 1449
Product Compliance	RoHS

TRIPP·LITE

by **EAT·N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

TRIPP·LITE

by **EAT·N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.