

Manufacturer Part #	Creator1711471
OS	Windows 10 Home
CPU	Core i7-11800H 8 Core
CPU Speed	2.4 - 4.6GHz
Chipset	HM570
Color	Core Black
Screen Size	17.3" UHD (3840*2160), 120Hz 100% Adobe
Resolution	3840x2160 (16:9)
GPU	NVIDIA® GeForce RTX™ 3060 Laptop GPU Up to 1747MHz Boost Clock, 95W Maximum Graphics Power with Dynamic Boost. *May vary by scenario
Video Memory	6G GDDR6
Keyboard	White backlight keyboard (102 Key)
Audio	Nahimic 3 / Hi-Res Audio
Speaker	Speakers 2W * 2
Memory	16GB (8G*2) DDR4 3200MHz
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	-
LAN	INTEL/I225-V(SLN9D)
WLAN	Killer WiFi 6E AX1675 (2x2 )
Bluetooth	BT 5.2
Card Reader	SD UHS-III
Webcam	IR 720p HD Webcam
USB	2x USB 3.2 Gen2
Type-C Port	1x Thunderbolt™ 4; 1x USB-C Gen2
Video Port	HDMI (supports 8K @ 60Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	230W Slim
Battery Pack	4 cell (99.9Whr)
Dimension	15.59"x10.21"x0.80"
Weight	5.40 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)