

## Key Features

Pantone Validated Display | Excellent Screen uniformity |

Hardware calibration ready | Amazing color accuracy |

Professional color processing

## Product Description

Perfect for designers, photographers, videographers, and other creative professionals, the ViewSonic® VP3268a-4K Ultra HD monitor delivers unmatched color accuracy and reliable long-term performance. With a SuperClear® IPS panel and a sleek frameless design, this monitor provides a near-seamless viewing experience ideal for multi-monitor setups. To ensure precise, uniform color, each of our monitors is factory calibrated to deliver an amazing Delta E<2 value for incredible color accuracy. An integrated color uniformity function ensures consistent chromaticity across the screen, while a 14-bit 3D look-up table generates a stunningly smooth palette of 4.39 trillion colors. Add to that 6-axis color adjustment functionality, and this monitor provides the ultimate color processing capability for professional applications. What’s more, productivity-boosting features include an advanced ergonomic design. Hardware calibration is also available which allows you to quickly and easily calibrate the monitor for photography, graphic design, content creation, and other color-critical applications.





32"  
DISPLAY



IPS  
PANEL



3840 x 2160  
RESOLUTION

call: 888.881.8781

email: [salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com)

visit: [viewsonic.com](http://viewsonic.com)

Contact Sales

<b>Display:</b>	
Display Size (in.):	32
Viewable Area (in.):	31.5
Panel Type:	IPS
Resolution:	3840 x 2160
Resolution Type:	4K (3840x2160)
Static Contrast Ratio:	1,300:1
Dynamic Contrast Ratio:	20,000,000:1
Light Source:	LED
Brightness:	350 cd/m2
Colors:	1.07B
Color Space Support:	10 bit (8 bit + A-FRC)
Aspect Ratio:	16:9
Response Time (Typical GTG):	5ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30,000
Panel Surface:	Anti-Glare type, Hard-coating (3H), Haze 25%
<b>Compatibility:</b>	
PC Resolution (max):	3840 x 2160
Mac® Resolution (max):	3840 x 2160
<b>Connector:</b>	
USB Type A(2), USB Type B(1), USB Type C(1), 3.5mm Audio Out(1), HDMI 2.0 In(2), DisplayPort(1)	
<b>Audio:</b>	
Internal Speakers:	5W (x2)
<b>Power:</b>	
Eco Mode (Conserve):	31W
Eco Mode (optimized):	35.2W
Consumption (typical):	46W
Consumption (max):	180W
Voltage:	100-240 VAC
Stand-by:	0.5W
Power Supply:	Internal
<b>Additional Hardware:</b>	
Kensington Lock Slot:	1
<b>Controls:</b>	
Physical Controls:	Key 1 (power), Key 2, Key 3, Key 4, Key 5 (favorite)
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu
<b>Operating Conditions:</b>	
Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	20-90%
<b>Mount:</b>	
VESA Compatible:	100 x 100 mm

<b>Video Signal:</b>	
Frequency Horizontal:	15 ~ 135 KHz
Frequency Vertical:	24 ~ 75 Hz
<b>Ergonomics:</b>	
Height Adjust:	130 mm / 5.1 in
Swivel:	120°
Pivot (Right/Left):	90° / 90°
Tilt (Forward/Back):	5° / 21°
<b>Weight (imperial):</b>	
Net (lbs):	23.5
Net Without Stand (lbs):	15.0
Gross (lbs):	36.2
<b>Weight (metric):</b>	
Net (kg):	10.7
Net Without Stand (kg):	6.8
Gross (kg):	16.4
<b>Dimensions (imperial) (WxHxD):</b>	
Packaging (in.):	32.9 x 22.6 x 12.6
Physical (in.):	28.1 x 19.9~25.0 x 10.4
Physical Without Stand (in.):	28.1 x 16.1 x 2.1
<b>Dimensions (metric) (WxHxD):</b>	
Packaging (mm):	835.0 x 575.0 x 320.0
Physical (mm):	714.0 x 506.0~636.0 x 265.0
Physical Without Stand (mm):	714.0 x 410.0 x 53.0
<b>General:</b>	
Regulations: cTUVus, FCC-B, ICES003, CEC, NOM, Mexico Energy	
PACKAGE CONTENTS: VP3268a-4K Display, Power Cable, USB-C Cable, HDMI cable, UAB-A/B Cable	
Recycle/Disposal: Please dispose of in accordance with local, state or federal laws.	
Warranty: Three-year limited warranty on parts, labor and backlight	
UPC: 766907012361	