

Planar PZN3410Q

34" Ultrawide Curved Docking Monitor

The Planar® PZN3410Q is a 34" Ultrawide 21:9 Curved QHD USB Type - C Docking monitor. The integrated docking station provides a simple and easy way to connect your PC/laptop to the monitor. A single Type C cable provides audio, video, data, network connectivity via the gigabit Ethernet port, and power delivery up to 65 watts. The Planar PZN3410Q suits nicely into education, home, office or healthcare applications.



SPECIFICATION	DETAIL
Product Name	PZN3410Q
Planar Part Number	998-2548-00
Viewable Size	34" diagonal (31.39" x 13.14")
Aspect Ratio	21:9 (Ultrawide)
Curvature	1500R
Contrast Ratio (typ)	4000:1
Viewing Angle (typ)	178° Horizontal and Vertical
Response Time (typ)	5 ms (GTG)
Brightness (Typical)	300 cd/m ²
Display Type	VA LCD Active Matrix Flat Panel Display (TFT)
Display Resolution	3440 x 1440 WQHD
Tilt Range	-5° to +21°
Palette	16.7 million colors
Pixel Pitch	0.23175 mm
Refresh Rate	24-100Hz (100Hz recommended)
Dimensions (W x H x D)	31.7" x 24.1" x 14.7" (809.34 mm x 612.35 mm x 374.16 mm)
Dimensions without Stand	31.7" x 14.4" x 4.1" (809.34 mm x 365.83 mm x 104.6mm)
Panel Depth	4.1" (104.6 mm)
Display Weight	18.1 lb/8.2 kg (14.6 lb/ 6.6kg without stand)

Shipping weight	25.0 lb (11.3 kg)
Video Inputs	USB Type C (DisplayPort Alt Mode), DisplayPort, HDMI
HDCP	Yes
Audio Output	Integrated 2W/channel stereo speakers, headphone jack
External Connections	USB Type C, HDMI 19-pin, DisplayPort 20-pin, 3.5mm headphone out, USB 3.2 Gen 1 (Type A) x 3, RJ45.
USB	USB-C x 1 (Upstream) (5Gbps), USB3.2 Gen1 x 3 (Downstream)
USB C Power Delivery	USB C (Up to 65W) (5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/3.25A)
RJ45	Ethernet LAN (10M/100M/1000M)
Compatibility	PC and Mac® (adapter may be required for Mac)
Power Supply	Internal
Power Consumption (max)	58W typical (<0.5W standby)
Power Requirements	AC 100/240 VAC
Operating Temperature	0° to +40°C (32° to 104°F)
Humidity	10 - 85% RH (non-condensing)
Mount	Built-in 100 mm VESA, back
Product Approvals	cTUVus, CE , FCC-B, RoHS
Recommended Usage	Up to 16 hours per day
Service and Support	3-Year Customer First [™] Warranty featuring FREE 2-Day Advance Replacement (US only). Please see warranty document for more details and for replacement procedures outside the US.
Options / Features	VA panel, Wide color consistent viewing angle, Discreet branding, Height adjustment:5.5" (140cmm), Swivel range 30° (15° left, 15° right), Anti-glare coating ,Multi-language display, On screen display (OSD), Kensington® Security Slot
Blue Light Reduction	Yes
Flicker Free	Yes
In the Box	PZN3410Q 34" LCD Monitor, Power Cord, HDMI & DP Cable, USB Type-C Cable, User's Guide
UPC	8 10689 00803 3

For more information, please visit www.planar.com Specifications are subject to change without notice. Specification Report Date: 7/13/2022 © Copyright 2022 Planar Systems, Inc. All rights reserved