









## SPECIFICATIONS

<b>Panel Size</b>	27" (69 cm)
<b>Panel Resolution</b>	2560 x 1440 (WQHD)
<b>Refresh Rate</b>	165Hz
<b>Response time</b>	1ms (MPRT)
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	Freesync premium
<b>ACTIVATED RANGE</b>	48Hz-165Hz
<b>Panel Type</b>	VA
<b>Video interface</b>	1x DP(1.4) 2x HDMI (2.0) 1x USB Type-C (DisplayPort Alternate)
<b>Brightness (nits)</b>	550(peak)
<b>Viewing Angle</b>	178°(H) / 178°(V)
<b>Aspect Ratio</b>	16:9
<b>Audio interface</b>	1x Earphone out
<b>Contrast Ratio</b>	3000:1
<b>Pixel Pitch (H x V)</b>	0.2331(H)X0.2331(V)
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	1.07B
<b>DCI-P3 / sRGB</b>	88.71%/111.49%
<b>Video ports</b>	1x DP(1.2a) 2x HDMI (2.0b) 1x USB Type-C Port (DP Alternate Mode)
<b>USB ports</b>	2x USB2.0 Type A 1x USB2.0 Type B
<b>Audio ports</b>	1x Earphone out
<b>Active Display Area (mm)</b>	596.736(H) x 335.664 (V)
<b>Kensington Lock</b>	Yes
<b>VESA Mounting</b>	100 x 100 mm
<b>Power Type</b>	External Adaptor 20V 4.5A
<b>Signal Frequency</b>	69.8~212.4 KHz(H) / 48~165 Hz(V)
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-30° ~ 30°
<b>Adjustment (Height)</b>	0 ~ 100 mm
<b>Curved</b>	1000R
<b>Compatibility</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners

## FEATURES

- 
**Curved Gaming™**  
View more of your game. MSI Curved Gaming™ monitors are perfect for gamers to play their games.
- 
**1000R - The Perfect Curve**  
Enjoy the most immersive gameplay with 1000R curvature rate.
- 
**Rapid Boost (165 + 1ms)**  
Experience smooth gaming with a blazing fast refresh rate and response time, that gives you the upperhand in fast moving games.
- 
**Gaming Intelligence**  
A new dawn of AI gaming, including Smart Brightness, Smart Crosshair, Night Vision AI, and Sound Tune.
- 
**KVM**  
Control multiple devices via one set of keyboard, mouse, and MSI gaming monitor.
- 
**Console Mode**  
Best solution for console users: FHD/WQHD/UWQHD@120Hz, 2K Resolution PS5™ Optimization.



# msi<sup>®</sup> MONITOR MPG ARTYMIS 273CQR

<b>Carton Dimension (W X H X D)</b>	775 x 223 x 490 mm
<b>Dimension (W x H x D)</b>	607.1 x 260.9 x 527.8mm
<b>Note</b>	Display Port: 2560 x 1440(Up to 165Hz) HDMI: 2560 x 1440 (Up to 144Hz) Type C. 2560 x 1440(Upto 165Hz) *sRGBand DCI-P3 follow CIE1976 standard

## CONNECTIONS



1. Headset Hanger
2. Marco Key
3. 5-Way joystick navigator
4. Power Jack
5. 1x Display Port (1.2a)
6. 1x HDMI w/CEC (2.0b)
7. 1x HDMI (2.0b)
8. 1x USB2.0 Type C
9. 1x Earphone out
10. 1x USB2.0 Type B Upstream Port
11. 2x USB 2.0 Type A
12. Kensington Lock