



msi

MONITOR

Optix MAG2732

ACCURATE DISPLAY. ULTIMATE VICTORY.



SPECIFICATIONS

Brightness (nits)	250 nits
DYNAMIC REFRESH RATE TECHNOLOGY	G-SYNC Compatible
ACTIVATED RANGE	48 to 165Hz
DCI-P3 / sRGB	97.5% / 140.56%
Panel Size	27" (69cm)
Aspect ratio	16:9
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.31125(H) x 0.31125(V)
Refresh Rate	165Hz
Response time	1ms
Viewing angle	178° (H) / 178° (V)
Contrast Ratio	1000:1
Power consumption	25W
Compatibility	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
Control	5-way OSD navigation joystick
Carton Dimension (W X H X D)	707 x 555 x 144 mm / 27.83 x 21.85 x 5.67 inch
Frameless Design	Yes
Dimension (W x H x D)	617 x 447 x 228 mm / 24.29 x 17.60 x 8.98 inch
Weight	5.15kg / 7.57kg 11.35lbs / 16.89lbs
Surface Treatment	Anti-glare
Panel Type	IPS
DCR	100000000:1
Active Display Area (mm)	597.6(H) x 336.15(V)
USB ports	2x USB 2.0 Type A 1x USB 2.0 Type B
Audio ports	1x Earphone out
Display Colors	1.07B (8bits + FRC)
Note	Display Port: 1920 x 1080 (Up to 165Hz) HDMI: 1920 x 1080 (Up to 165Hz) The color gamut follows the CIE 1976 testing standard.
Adjustment (Tilt)	-5° ~ 20°

FEATURES



eSports Gaming

MSI eSports gaming monitor will enhance your competitive gameplay to ensure you are always at your best levels.



165Hz High Refresh Rate

Experience smooth gaming with a blazing fast 165Hz refresh rate, that gives you the upperhand in fast moving games



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



IPS Panel

Optimize the screen colors and brightness to enhance your viewing experience.



Gaming OSD APP

Customize and set the ultimate monitor modes with keyboard & mouse in a very easy way.



HDR Ready

Provide eye-catching detail through contrast and shadows adjustment.




msi[®] MONITOR Optix MAG2732

ACCURATE DISPLAY. ULTIMATE VICTORY.

Signal Frequency	96.4 to 186.7KHz (H) 30 to 165Hz (V)
Power Input	100~240V, 50~60Hz
Power Type	External Adaptor 12V 5A
VESA Mounting	100 x 100 mm
Video ports	1x DP (Supports FHD@165Hz as specified in DisplayPort 1.2a) 2x HDMI (Supports FHD@165Hz as specified in HDMI 2.0)
Kensington Lock	Yes

CONNECTIONS



1. 5-way joystick navigator
2. DC jack
3. 1x USB 2.0 Type B
4. 2x USB 2.0 Type A
5. 1x Display Port (1.2a)
6. 2x HDMI (2.0)
7. 1x Earphone out