

# VGA to DisplayPort and USB-A Adapter Cable Kit for Tripp Lite B020-U and B022-U KVM, 6 ft. (1.8 m)

MODEL NUMBER: P778-006-DP











Connects a DisplayPort server to the VGA port on your Tripp Lite NetDirector® KVM switch.

#### **Features**

#### Connect Your Computer's DisplayPort and USB Ports to a Tripp Lite KVM Switch

This convenient cable kit saves you money by combining necessary cables into one bunch. For use with Tripp Lite B020-U and B022-U KVM switches, the P778-006-DP features male DisplayPort and USB-A connectors for your server or computer and a male HD15 connector for the KVM. The DisplayPort 1.1-compliant cable supports HD resolutions up to 1920 x 1080 (1080p) at 60 Hz with 36-bit Deep Color. The USB 2.0 cable supports 480 Mbps speeds. The bus-powered cable kit requires no software or external power adapter. A sliding switch on the back of the housing lets you decide between USB power mode or USB + DP power mode with LEDs indicating which mode you have chosen.

## **Highlights**

- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60
- LEDs indicate at a glance which power mode the cable kit is using
- Supports USB 2.0 speeds up to 480 Mbps for reliable data transfers
- Plug and play with no software or external power supply required
- Compatible only with select Tripp Lite B020-U and B022-U Series KVM switches

## **Applications**

Transfer data and video between your KVM switch and a connected server or computer

## **System Requirements**

Tripp Lite B022-U08, B022-U08-IP, B022-U16-IP, B020-U08-19-IP, B020-U16-19-IP, B020-U08-19-K or B020-U16-19-K KVM switch

## Package Includes

P778-006-DP VGA to DisplayPort and USB Adapter Cable Kit, 6 ft. (1.8 m)

# **Specifications**

•		
OVERVIEW		
UPC Code	037332263353	
Accessories Type	Cable Kit	
Technology	DVI; USB	
VIDEO		
Max Supported Video Resolution	1920 x 1080 60 Hz	
Max Supported Color Depth	36-bit Deep Color	
HDR Support	No	
USER INTERFACE, ALERTS & CONTROLS		



LED Indicators	Cross LISP & DD Dower: Orongo LISP Dower Only
LED Indicators	Green - USB & DP Power; Orange - USB Power Only
PHYSICAL	
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	USB: 3.5MM; DisplayPort: 6.0MM
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	2.32 x 6.30 x 4.69
Shipping Weight (kg)	0.25
ENVIRONMENTAL	
Operating Temperature Range	32 to 122 F (0 to 50 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	0 TO 80% RH, Non-Condensing
Storage Humidity Range	0 TO 80% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	DISPLAYPORT (MALE); USB A (MALE)
Connector Color	Black; Green
FEATURES & SPECIFICATIONS	
Displayport Specification	1.1
USB Specification	USB 2.0 (up to 480 Mbps)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <a href="https://www.tripplite.com/products/product-certification-agencies">https://www.tripplite.com/products/product-certification-agencies</a>