

SPECIFICATION SHEET

WorkForce® ST-C2100 Supertank Color MFP

Print | Copy | Scan

MICRO PIEZO HEAT+FREE



The Supertank Color MFP with wireless and auto 2-sided printing.

Up to 2 years of ink in the box $^1-$ includes enough ink to print up to 6,500 pages black/5,200 color 2

EPSON

Save up to 90 percent on ink — with low-cost replacement bottles vs. ink cartridges³, equivalent to about 90 individual ink cartridges⁴

Engineered for reliability — comes with a 2-year limited warranty and permanent printhead designed to last the life of the printer

Compact, space-saving design — and exclusive EcoFit[®] bottles that are auto-start/stop and uniquely keyed for easy filling of each color

Micro Piezo Heat-Free Technology[™] — delivers fast, reliable, sharp text and prints without sacrificing on quality, a fast first page out and low power consumption

Security features — Epson's Solutions Suite of embedded security features helps protect your data

 $\ensuremath{\textbf{Specially engineered inks}}$ — vibrant graphics and pigment black ink for razor-sharp text

Enhanced productivity from your mobile device — the Epson Smart Panel[®] app⁵ transforms your mobile device into a high-performance command center that lets you setup, operate and monitor your printer with ease

Easy connectivity — Wi-Fi®, Wi-Fi Direct®6 and voice-activated printing7

High-quality photo printing - print borderless photos up to 4" x 6"



Replacement ink bottles

1 Based on average monthly document print volumes of about 150 pages.



WorkForce® ST-C2100 Supertank Color MFP

Print

Printing Technology 4-color (CMYK), drop-on-demand MicroPiezo[®] inkjet technology

Printer Language Epson ESC/P®-R Max. Print Resolution 5760 x 1440 optimized dpi Print Speed[†] 10.5 ISO ppm (black), 5.0 ISO ppm (color)

First Page Out Time 16 sec8 First Set Out Time 51 sec8

Auto 2-sided Print⁺ 6 ISO ppm (black), 4 ISO ppm (color) Min. Ink Droplet Size 3 ink droplet sizes, as small as 3 picoliters Monthly Duty Cycle⁹

Monthly: Up to 3,000 pages

Recommended monthly page volume: Up to 600 pages

Mobile Printing and Scanning¹⁰

Epson Connect[™] Solutions¹⁰ Epson Smart Panel App⁵ (iOS[®], Android[™])

Other Apple[®] AirPrint[®], Chrome[™] OS, Android printing, Fire[™] OS printing, Mopria® Print Service

Copy

Copy Speed⁺⁺ 7.7 ISO cpm (black), 3.8 ISO cpm (color) First Copy Out Time⁸ 33 sec Copy Modes Color, Black/White, Draft/Normal Copy Quantity 1 – 20 copies (PC-free) Max. Copy Size 8.5" x 11" (PC-free) Copy Features Reduce and Enlarge (25 - 400%)

Scan

Scanner Type Color flatbed (CIS line sensor) Max. Hardware Resolution 2400 dpi Hardware Resolution 1200 x 2400 dpi Max. Resolution 9600 dpi interpolated Scanner Bit Depth Input: 48-bit color / Output: 24-bit color Scan Bed Size 8 5" x 11 7' Scan Features Scan to Computer

Connectivity

Standard Connectivity Hi-Speed USB Wireless 802.11 b/g/n6 Wi-Fi Directe

All images simulated.

Connectivity (continued)

Operating Systems Windows® 10, Windows 8, 8.1 (32-bit, 64-bit), Windows 7 (32-bit, 64-bit), Windows Server® 2003 – Windows Server 2019¹¹ (32-bit, 64-bit) Mac[®] OS X[®] 10.6 – macOS[®] 10.15.x¹²

Paper Handling

PC-free Paper Support Plain (letter, 8.5" x 14", A4), Photo (4" x 6", 5" x 7", 8" x 10", letter, A4)

Max. Paper Size 8.5" x 47.2'

Paper Sizes 3.5" x 5", 4" x 6", 5" x 7", 8" x 10", 8.5" x 11", 8.5" x 14", A4, A6, half letter, legal, executive

Paper Types Plain paper, Epson Multipurpose Plus Paper. Epson Bright White Premium Paper, Epson Bright White Pro Paper, Value Paper Glossy, Photo Paper Glossy, Premium Photo Paper Glossy, Premium Photo Paper Semi-Gloss, Ultra Premium Photo Paper Glossy, Presentation Paper Matte, Premium Presentation Paper Matte, Premium Presentation Paper Matte Double-Sided, Ultra Premium Presentation Paper Matte, Brochure & Flyer Paper Matte Double-sided

Envelope Types No. 10; plain paper, bond paper, air mail Input Paper Capacity Paper tray: 100 sheets plain paper, 20 sheets photo paper, 10 envelopes

Output Paper Capacity 30 sheets plain paper

General

Display 1.44" color LCD Temperature Operating: 50 ° to 95 °F (10 ° to 35 °C) Storage: -4 ° to 104 °F (-20 ° to 40 °C)

Relative Humidity Operating: 20 – 80% Storage: 5 – 85% (no condensation)

Sound Level

Power: 6.3 B(A)

Pressure: 50 dB(A)

Power Requirements Rated Voltage: AC 100 – 240 V Universal (Automatic) Rated Frequency: 50 – 60 Hz Rated Current: 0.4 – 0.2 A Power Consumption Approx. 12 W ISO 24712 (Standalone copy printing) Approx. 0.3 W (Power Off Mode)

General (continued)

Safety Standards UL60950-1-CAN/CSA-22.2 No. 60950 EMC FCC Part 15 subpart B class B, CAN/CSA-CEI/IEC CISPR 22 class B Weight and Dimensions (W x D x H)

Printing: 14.8" x 22.3" x 10.2 Storage: 14.8" x 13.7" x 7.4" Weight: 11.9 lb

What's in the Box

WorkForce ST-C2100 MFP, manual, power cord, 1x bottles 502 Black (127 mL) and 1x bottle each 502 Cyan, Magenta, Yellow $(70 \text{ ml})^{2}$

Software Available¹³ Epson® printer drivers, Epson ScanSmart

Warranty Standard 2-year limited warranty in the U.S. and Canada

Country of Origin Philippines

Memory¹⁴ 128 MB

Ink

Ink Bottles 4 individual ink bottles (Cyan, Magenta, Yellow and Black)

Replacement Ink Bottles²

502 Black ink bottle (127 mL) vield: 7,500: 502 color (Cyan, Magenta, Yellow) ink bottle (70 mL) yield: 6,000 Epson strongly recommends the use of genuine ink to ensure optimal print quality and performance.

Eco Features

Save up to 50% of your paper supply with auto 2-sided printing ENERGY STAR® qualified RoHS compliant Recyclable product¹⁵ Epson America, Inc. is a SmartWay® Transport Partner¹⁶

Ordering Information

WorkForce ST-C2100	C11CJ63203
Epson Preferred SM Plus Extended Service Plans ¹⁷	
Year 2 Upgrade to Premium	EPPDSKC1U
1-Year Extension - Standard	EPPDSKC1R
1-Year Extension - Premium	EPPDSKC1A

† Black and color print speeds are measured in accordance with ISO/IEC 24734. Actual print times will vary based on factors including system configuration, software, and page complexity. For more information, visit www.epson.com/printspeed | †† Black and color copy speeds are determined in accordance with ISO/IEC 29183. Actual copy times will vary based on factors including system configuration and page complexity. For more information, visit www.epson.com/copyspeed | 1 Based on average monthly document print volumes of about 150 pages. | 2 Included and replacement ink bottle yields based on the ISO/IEC 24712 pattern with Epson's methodology. Actual ink yields will vary considerably for reasons including images printed, print settings, temperature and humidity. Yields may be lower when printing infrequently or predominantly with one ink color. All ink colors are used for printing and printer maintenance, and all colors must be available for printing. For more information, visit www.epson.com/inkinfo | 3 Actual savings and costs will vary considerably based on print tasks, print volumes and usage conditions. Savings and cost per ISO page are based on the cost of replacement ink bottles and the cost of enough standard cartridges to achieve the total page yields of the bottles using the MSRP (USD) and yields for Epson standard-capacity ink cartridges for similarly featured Epson consumer inkjet printers as of May 2021. | 4 Individual cartridges estimate based on print yields of a replacement set of black and color ink bottles as compared to Epson Standard capacity ink cartridges for similarly featured printers as of May 2021. | 5 Requires Epson Smart Panel App download. Data usage fees may apply. | 6 Wi-Fi CERTIFIEDTM; level of performance subject to the range of the router being used. Wi-Fi Direct may require printer software. | 7 Epson Connect account and voice-activated account registration required. See www.epson.com/voice for device compatibility. [8 FPOT is measured on letter-size paper in accordance with ISO/IEC 17629. FSOT is measured on letter-size paper in accordance with ISO/IEC 24735. FCOT is measured on letter-size paper in accordance with ISO/IEC 29183. [9 Monthly duty cycle is the highest duty a user could expect in a month, based on near-constant operation of a device of this kind. It is not recommended that the device be run at this duty. For best device performance, run the device at the recommended monthly page volume. [10 Most features require an Internet connection to the printer, as well as an Internet- and/or email-enabled device. For a list of Epson Connect enabled printers and compatible devices and apps, visit www.epson.com/connect | 11 Only printing and scanning are supported under Windows Server OS. | 12 Some applications and/or functions may not be supported under Mac OS X. | 13 Internet access is required to install OS X drivers and software. | 14 RAM size definition is the total amount of RAM memory capacity inside the device, regardless of memory use. |15 For convenient and reasonable recycling options, visit www.epson.com/recycle | 16 SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency. | 17 See individual service plan for details.

See the latest innovations from Epson Business Solutions at www.epson.com/forbusiness

Better Products for a Better Future" eco.epson.com

Epson America, Inc. 3131 Katella Ave., Los Alamitos, CA 90720





185 Renfrew Drive, Markham, Ontario L3R 6G3

www.epson.com www.epson.ca

Specifications and terms are subject to change without notice. EPSON, Epson ESC/P, Epson ScanSmart, Epson Smart Panel, MicroPiezo and WorkForce are registered trademarks, EPSON Exceed Your Vision is a registered logomark and Better Products for a Better Future and Epson Connect and Micro Piezo Heat-Free Technology are trademarks of Seiko Epson Corporation. EcoFit is a registered trademark and Epson Preferred is a service mark of Epson America, Inc. AirPrint, Apple, Mac, macOS and OS X are trademarks of Apple Inc., registered in the U.S. and other countries. Android and Chrome are trademarks of Google LLC. Windows and Windows Server are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Wi-Fi® and Wi-Fi Direct® are registered trademarks and Wi-Fi CERTIFIED™ is a trademark of Wi-Fi Alliance®. SmartWay is a registered trademark of the U.S. Environmental Protection Agency. All other product and brand names are trademarks and/or registered trademarks of their respective companie Epson disclaims any and all rights in these marks. Copyright 2021 Epson America, Inc. Com-SS-Oct-13 CPD-61820 10/21

SmartWay Transport Partne

Contact: