#### **ProductSheet**

## HP E24mv G4 FHD Conferencing Monitor (169L0AA)

#### **Present Your Best Self**

Make a great impression on video calls on this 23.8-inch full HD conferencing monitor. The integrated, 5MP tiltadjustable pop-up webcam displays a sharp, detailed picture — even in low light — and the built-in speakers and mic produce clear, life-like sound. Everything you need to present your best self on every call. [1]



#### Look Great. Sound Great.

Say goodbye to blurry images or muffled sound on video calls. With speakers and a mic that produce full, rich sound and a 5MP webcam with 25 degrees of tilt adjustability for perfect angles, pop-up action for privacy, and improved Windows Hello support, you'll present your best on every call.

#### **Enhanced Viewing Comfort**

Much of our world operates on screens now, so working long hours in front of a monitor can be tiring and impactful to productivity. HP Eye Ease with TÜV Rheinland Hardware Low Blue Light Certification helps keep you comfortable throughout your day by reducing blue light without the yellow color shift.

#### **Endless Adjustability**

Work effortlessly with 4-way ergonomics that help keep your neck, shoulders, and back comfortable throughout the day. Customize tilt, height, swivel and pivot settings to fit you, your desk, and your needs, and you'll easily see the FHD monitor and 3-sided Micro-Edge 23.8-inch diagonal screen perfectly from virtually any viewing angle.

#### **Featuring**

#### More Ports. More Flexibility.

Packed with ports including HDMI, DisplayPort™, USB-B plus four USB ports. [5]

#### Personalized and Protected

Personalize brightness and color settings or set up security protocols all without the OSD. With HP Display Center installed, you have the control.  $^{[6]}$ 

#### Remote Management Reimagined

HP Display Manager makes remote management of the monitor easy. Simplify deployment, asset tracking, and remotely control monitor settings, like turning the power off.  $^{[7]}$ 

### 3-year Limited Warranty

Get peace of mind with a 3-year warranty.

# **Specifications**

Display size (diagonal)	23.8"
Panel technology	IPS
Display size (diagonal)	60.45 cm (23.8")
Aspect ratio	16:9
Native resolution	FHD (1920 x 1080) <sup>[1]</sup>
Mative resolution	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1680 x
Resolutions supported	1050; 1920 x 1080
Pixel pitch	0.274 mm
Brightness	250 nits <sup>[1]</sup>
Contrast ratio	1000:1
Response time (typical)	5ms GtG (with overdrive) <sup>[1]</sup>
Minimum dimensions (W x D x H)	53.94 x 4.7 x 35.56 cm
	(Without stand.)
Minimum dimensions (W x D x H)	21.23 x 1.85 x 17.78 in (Without stand.)
Dimensions With Stand (W x D x H) 53.94 x 21.6 x 53.07 cm	
Weight	6.5 kg (With stand.)
Weight	14.3 lb
	(With stand.)
Display features	On-screen controls; Low blue light mode; Dual speakers (2W per channel); Anti-glare; IR webcam; Height Adjust/Tilt/Swivel/Pivot
Display Input Type	1 VGA; 1 HDMI 1.4; 1 DisplayPort™ 1.2; 4 USB-A 3.1 Gen 1
Onscreen controls	Brightness; Exit; Information; Management; Menu; Power; Input control; Image; Color
Display colors	Up to 16.7 million colors supported (through FRC technology)
Display scan frequency (horizontal)	30-80 KHz
Display scan frequency (vertical)	50-60 Hz
Camera	Yes, 5MP
Power	100 - 240 VAC 50/60 Hz
Power consumption	50 W (maximum), 28 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% non-condensing
Certifications and compliances	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; cTUVus; EAC; ENERGY STAR®; FCC; GS Mark; ISO 9241-307; KC/KCC; NOM; PSB; SEPA; TCO Certified; TCO Certified Edge; TUV/GS; VCCI; Vietnam MEPS; WEEE; Low blue light; WW application; UAE; Ukraine certificates
Physical security	Security lock-ready <sup>[2]</sup>
Management Software	HP Display Center; HP Display Manager
UPC number	(A2K) 195122022143; (A2N) 195122022136; (ABO) 195122022464; (AB1) 195122022471; (AB2) 195122022488; (AB4) 195122021818; (ABA) 195122021801; (ABB) 195122021795; (ABG) 195122021788; (ABT) 195122021580; (ABU) 195122021597; (ABV) 195122021603; (ABY) 195122021610; (ACJ) 195122021641; (ACQ) 195122021658; (AKL) 195122021665; (ARG) 195122021672; (UUF) 195122021689; (UUZ) 195122021696
What's in the box	Monitor; DisplayPort™ cable; HDMI cable; USB Type-A to B cable; Doc-kit; AC power cord

ProductSheet | HP E24mv G4 FHD Conferencing Monitor (169L0AA)

# **Top Recommended Displays, Accessories and Services**

No Top Recommended Displays, Accessories and Services

#### ProductSheet | HP E24mv G4 FHD Conferencing Monitor (169L0AA)

#### **Messaging Footnotes**

- [1] Based on HP's internal analysis of monitor series with webcams. Most advanced based on physical integration, camera angle tile, Windows Hello IR sensor, minimum 5MP and as privacy pop-up as of 5/28/2021.
- [5] Comes with DisplayPort™, HDMI, USB-B to A cables and Power Cord.
- [6] Host PC requires Windows 10. HP Display Center is available on the Microsoft store.
- [7] HP Display Manager software agent must be running on a web server and host PC. Some limitations may apply to legacy monitors.

#### **Technical Specifications Footnotes**

[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[2] Lock sold separately.

© Copyright 2021 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

DisplayPort<sup>™</sup> is a trademark owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. ENERGY STAR® is a registered mark owned by the U.S. government. EPEAT® is a registered trademark of GREEN ELECTRONICS COUNCIL.

