

3ft (1m) Premium Certified HDMI 2.0 Cable - High Speed Ultra HD 4K 60Hz HDMI Cable with Ethernet - HDR10, ARC - UHD HDMI Video Cord - For UHD Monitors, TVs, Displays - M/M

**Product ID:** HDMMV1M



This 3.3 ft. (1 m) Premium High Speed HDMI 2.0 Certified Cable withstands the daily demands of connecting your HDMI devices. Tested to endure strenuous wear and tear, this durable cable is a must-have for both business and consumer applications.

Experience the latest that HDMI 2.0 has to offer

This high performance 4K cable supports resolutions of up to 4K at 60Hz (3840x2160p) and bandwidths of up to 18Gbps. It also supports HDR10 (High Dynamic Range) and Dolby Vision for higher contrast ratio and vivid colors.

Plus, ARC (Audio Return Channel) has up to 32 uncompressed 5.1 and 7.1 digital audio channels to support DTS-HD Master Audio, DTS:X, Dolby TrueHD, Dolby Atmos for high quality sound.

With high resolutions, increased speeds, sharper images, and crystal-clear audio, you can expect an enhanced video experience. The cable is guaranteed to provide the very best HDMI 4K performance available today. It's the perfect cable for creating the ultimate home theater or for providing lifelike digital signage.

This cable works with all 4K ready devices and is also backward compatible with previous HDMI specifications.

Provide superior connections with Premium High Speed certification

The cable has undergone rigorous compliance testing and is certified by an HDMI Authorized Test Center to ensure it supports the high bandwidth enabled features it promises. An EMI test is also performed to ensure the cable minimizes interference with wireless signals.

Cable Key Features

Aluminum-mylar foil with braided shielding improve EMI protection

Long lasting flexible TPE jacket & strain relief (TPE is non-toxic & halogen free for environmental sustainability)



## Connector Key Features

Corrosion-free gold-plated connectors ensure premium video quality & enhanced reliability

Tested to withstand 10,000+ insertions

The HDMMV1M is backed by StarTech.com's Lifetime Warranty.

## **Certifications, Reports and Compatibility**

## **Applications**

## **Features**

- HIGH PERFORMANCE CABLE: 3.3ft (1m) Premium Certified High Speed HDMI cable with Ethernet supports 4K 60Hz (3840x2160), 18Gbps bandwidth, HDR10, Ultra wide aspect ratio, 32 Ch Audio (5.1/7.1/Dolby TrueHD/Atmos), ARC, BT.2020 colorimetry, 3D video
- PREMIUM HDMI 2.0 CABLE: Ultra HD 4K 60Hz HDMI cable is engineered & built to improve signal integrity; Featuring corrosion free gold-plated connectors encased in die-cast aluminum to prevent signal degradation due to FMI
- DURABLE: Tested to withstand 10,000+ insertions & 600+ bend cycles at 120 angle; Long lasting TPE jacket with molded soft TPE strain relief absorbs stress of frequent bends; TPE is non-toxic, halogen free & RoHS certified for environmental sustainability
- APPLICATIONS: Ideal for home/office & travel, works with computer/laptop/desktop/PC/workstation; UHD HDMI cord to connect your TV/monitor/display/projector; Samsung/Sony/Apple TV/Dell/LG; Works w/ HDMI 2.0 Ultra HD, 1080p Full HD & previous HDMI versions
- SPECS: 3.3 feet (1 meter) HDMI 2.0 Premium Certified HDMI Cable High Speed Cable with Ethernet HDMI Male to Male 6 mm (0.24") Outer Diameter, 30AWG Jacket: TPE EMI Shield: Al-Mylar Foil, Braid StarTech.com Lifetime Warranty

Hardware		
	Warranty	Lifetime
	Active or Passive Adapter	Passive
	Number of Conductors	19
	Connector Plating	Gold
	Cable Jacket Material	TPE - Thermoplastic Elastomers
	Cable Shield Material	Aluminum-Mylar Foil with Braid



**Performance** 

Video Revision HDMI 2.0b

Maximum Data Transfer

Rate

18Gbps

Maximum Cable Length 39.4 in [100 cm]

Maximum Digital

Resolutions

4K 60Hz 3840x2160

Audio Specifications HDMI - 32 Channel Audio

HDMI - 7.1 Channel Audio

HDMI - 5.1 Channel Audio

Connector(s)

Connector A HDMI (19 pin)

Connector B HDMI (19 pin)

**Environmental** 

Operating Temperature 0C to 50C (32F to 122F)

Storage Temperature 0C to 50C (32F to 122F)

Humidity 0%RH ~ 85%RH

Physical Characteristics

Color Gray and Black

Wire Gauge 30 AWG

Cable Length 39.4 in [100 cm]

Cable OD 0.2 in [6 mm]

Product Length 39.4 in [100.0 cm]

Product Width 0.8 in [20.0 mm]

Product Height 0.4 in [11.0 mm]

Weight of Product 0.0 oz [0.0 g]

Packaging Information



Package Length 7.9 in [20.0 cm]

Package Width 8.7 in [22.0 cm]

Package Height 1.2 in [30.0 mm]

Shipping (Package) Weight

3.1 oz [88.0 g]

What's in the Box

Included in Package Premium High Speed HDMI Cable

<sup>\*</sup>Product appearance and specifications are subject to change without notice.