

# Lenovo Legion Y25g-30 66CCGAC1US

## Product

Lenovo Legion Y25g-30

## Machine Type

66CC

## Region

LA, NA

## Display Size

24.5"

## View Area

552.5x319.6 mm

## Panel

In-Plane Switching

## Aspect Ratio

16:9

## Resolution

1920x1080

## Pixel Pitch

0.2829x0.2802 mm

## Dot / Pixel Per Inch

90 dpi

## View Angle (H / V)

178 / 178

## Response Time

2 ms (Esports) / 4 ms (Level 1) / 3 ms (Level 2) / 2 ms (Level 3) / 1 ms (Level 4) / 5 ms (Off mode)

## Color Support

16.7 Million

## Refresh Rate

240 Hz (HDMI 2.0), 360 Hz (DP 1.4)

## Brightness

400 nits

## Contrast Ratio

1000:1

## Color Gamut

99% sRGB

## Curvature

None

## Anti-glare

Yes

## Video Connector

2x HDMI 2.0, 1x DP 1.4

## USB Port

4x USB 3.2 Gen 1 (3x USB Type-A, 1x USB Type-C)

## Network Connectivity

None

## Camera

None

## Microphone

None

## Speakers

2x 3W

## Power Consumption (Typical / Maximum)

30w / 115w

## Power Adapter

External

## Stand

Tilt, Swivel, Pivot, Height Adjust Stand

## Color

Raven Black

## Side Bezel Width

2 mm

## Dimensions with Stand (HxWxD)

509.8x557.3x230.6 mm / 20.07x21.94x9.08 inches

## Weight (Including Stand)

6.1 kg / 13.4 lbs.

## Cables Included

DP cable, USB Type-A to Type-B cable

## Environmental Certification

RoHS

## Ergonomic Certification

TÜV Rheinland Low Blue Light, TÜV Rheinland Flicker Free

## Base Warranty

3-year

## Operating System Support

Support Windows 7, Windows 10

## Sync Technology

NVIDIA G-SYNC, NVIDIA Reflex Latency Analyzer, ULMB

## ThinkCentre M Series Support

None

## Processor

None

## Touchscreen

None

## Controller

None

## Display Ram / Storage / Card Slot

None / None / None

## EAN / UPC / JAN

0195713559218 / 195713559218 / None

## Announce Date

2021-07-30

 [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



Lenovo™

# Legion Y25g-30 Gaming Monitor

## DISPLAY

**Panel Size**  
24.5-inch

**Screen Dimensions**  
552.5 mm x 319.6 mm

**Panel Type**  
3-side NearEdgeless  
In-Plane Switching

**Active Area**  
543.1 mm x 302.6 mm

**Backlight**  
WLED

**Aspect Ratio**  
16:9

**Resolution**  
1920 x 1080

**Pixel Pitch**  
0.2829 mm x 0.2802 mm

**Dot/Pixel Per Inch(DPI/PPI)**  
90

**Viewing Angle (H x V @ CR 10:1)**  
178° / 178°

**Response Time**  
2ms (E-sports)  
4ms (Level 1), 3ms (Level 2),  
2ms (Level 3), 1ms (Level 4),  
5ms (Off)

**Refresh Rate**  
DP 1.4 - 360 Hz  
HDMI 2.0 - 240 Hz

**Brightness (Typical)**  
400 cd/m<sup>2</sup>

**Contrast Ratio (Typical)**  
1000:1

**HDR Decoding**  
Yes

**Dynamic Contrast Ratio (Typical)**  
3M:1

**Color Gamut**  
99% sRGB

**Color Support (Typical)**  
16.7 Million

**Color Depth**  
True 8-bit

## CONNECTIVITY

**Video Signal**  
2 x HDMI 2.0  
1 x DP 1.4

**Audio Signal**  
1 x Audio Combo (3.5 mm)

**USB Hub**  
Yes

**USB Upstream**  
1 x USB3.2 Gen1 Type-B

**USB Downstream**  
4 x USB3.2 Gen1  
(3 x USB Type-A, 1 x USB Type-C)

## MULTI-MEDIA

**Integrated Speakers**  
Yes (2 x 3W)

## SPECIAL FEATURES

**Factory Calibration**  
Yes (Avg. Delta E<2)

**Software**  
Lenovo Artery<sup>4</sup>  
(Lenovo Display Control Center)  
- Brightness & Contrast Adjustment  
- Volume Control  
- Color Tuning  
- Gaming Light Control  
- Show Frame Rate  
- Desktop Partition  
- Sound Device

**Sync Technology**  
NVIDIA® G-SYNC<sup>®1, 2</sup>  
NVIDIA® Reflex Latency Analyzer<sup>3</sup>  
ULMB

**E-sports Mode**  
Yes

**RGB Lighting**  
Yes

## POWER

**Power Consumption (Typ./Max)**  
35W / 115W

**Power Consumption Sleep/Off Mode**  
< 0.5W / < 0.3W

**Power Supply**  
External

**USB Type-C (Downstream) Power Delivery**  
Up to 27W

**Voltage Required**  
AC 100 to 240 V (50-60 Hz)

## MECHANICAL

**Tilt Angle (Front/Back)**  
-5° / 22°

**Swivel Angle (Left/Right)**  
-30° / 30°

**Lift (Max. Range)**  
130 mm

**Pivot**  
-90° / 90°

**VESA Mount Capability**  
Yes (100 x 100 mm)

**Kensington Lock Slot**  
Yes

**Headphone Hook**  
Yes

**Cable Management**  
Yes

**Bezel Color**  
Raven Black

**Bezel Width (Side)**  
2.0 mm

**Bezel Width (Top / Bottom)**  
2.0 / 22.5 mm

## DIMENSION

**Size Packed (D x H x W) (mm/inch)**  
160.0 x 421.0 x 720.0 mm  
6.30 x 16.57 x 28.35 inches

**Size Unpacked w/stand (D x H x W) (mm/inch) (Lowest Position)**  
230.6 x 379.8 x 557.3 mm  
9.08 x 14.95 x 21.94 inches

**Size Unpacked w/stand (D x H x W) (mm/inch) (Highest Position)**  
230.6 x 509.8 x 557.3 mm  
9.08 x 20.07 x 21.94 inches

**Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)**  
57.0 x 333.1 x 557.3 mm  
2.24 x 52.48 x 21.94 inches

**Weight Packed (kg/lb)**  
8.8 kg / 19.4 lbs.

**Weight Unpacked (kg/lb)**  
6.1 kg / 13.4 lbs.

**Weight (Monitor Head Only) (kg/lb)**  
4.1 kg / 8.9 lbs.

## WHAT'S IN THE BOX

Monitor with stand  
1 x Power cable (1.8m)  
1 x DP cable (1.8m)  
1 x USB Type-A to USB Type-B cable (1.8m)  
1 x 120W adapter  
Factory calibration report  
Quick setup guide  
Warranty booklet

## CERTIFICATION

**CCC**  
Yes

**RoHS (EU 2002/95/EC)**  
Yes

**Windows Certification**  
Windows 7, Windows 10

**China Energy Efficiency Standard**  
Tier 2

**TÜV Rheinland Low Blue Light**  
Yes

**TÜV Rheinland Flicker Free**  
Yes



<sup>1</sup> NVIDIA® G-SYNC® requires DisplayPort connectivity. | <sup>2</sup> NVIDIA® G-SYNC® displays are validated for smooth and immersive gameplay. NVIDIA® G-SYNC® eliminates tearing, artifacts, and flicker when used with GeForce® graphics cards.  
<sup>3</sup> Dependent on game type and requires specific mouse models connected directly to the Legion Y25g-30's USB hub. | <sup>4</sup> This software can only be used with Windows 10.  
<sup>5</sup> USB Type-C and USB-C are registered trademarks of USB Implementers Forum.

Depending on variables such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 10 Gbit/s for USB 3.2 Gen2x1 or USB 3.2 Gen1x2; 20 Gbit/s for USB 3.2 Gen2x2.

© 2021 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A. Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

# Lenovo Legion Y25g-30

