



FEATURES

SPECIFICATIONS

Radiator Size	360 mm
Radiator Dimensions (WxDxH)	394 x 120 x 27 mm / 15.5 x 4.7 x 1.06 inches
Radiator Material	Aluminum
Water Cooling Tube Material	Black Rubber + Mesh
Water Cooling Tube Length	400 mm
Number of Fans	3
Fan Dimensions (WxDxH)	120 x 120 x 25 mm / 4.7 x 4.7 x 0.98 inches
Fan Speed	0 ~ 2000 RPM
Fan Air Flow	56.2 CFM
Fan Noise Level	22.7 dBA
Fan Static Pressure	2.21 mm H2O
Fan Bearing	Hydro-Dynamic Bearing
Fan Life Expectancy	50,000 Hours
Fan Rated Current	0.4 A (MAX)
Fan Power Consumption	4.8 W (MAX)
PWM Mode	Yes
Cable Length (PWM Cable)	350 mm / 13.78 inches
Fan Connector	4 pin PWM
Fan Lighting	NA
RGB Connector	NA
Pump Life Expectancy	50,000 Hours
Pump Noise Level	21.2 dBA
Pump Rated Current	0.33A
Pump Power Consumption	4W
Pump Speed	2800 +/-300 RPM (PWM controlled)
Pump Connector	4 pin PWM
Cold Plate Material	Copper
Block Dimensions (WxDxH)	95 x 95 x 83.53 mm
Intel Socket Support	"LGA 1700 / 1200 / 1151 / 1150 / 1155 / 1156 LGA 2066 / 2011-3 / 2011"
AMD Socket Support	"AM4 / AM3+ / AM3 / AM2+ / AM2 / FM2+ / FM2 / FM1 Socket TR4 / sTRX4 / SP3"
Panel Size	2.4"
Panel Type	IPS
Panel Resolution	320 x 240
Panel Color Depth	16 bits
Panel Brightness	500 nits
Interface Connector	USB 2.0 pin header
Power Connector	SATA