ThinkVision E24q-20 62CFGAR1US

Product

ThinkVision E24q-20

Machine Type

62CF

Region

LA, NA

Display Size

23.8"

View Area

526.85x296.4 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

2560x1440

Pixel Pitch

0.2058 x 0.2058 mm

Dot / Pixel Per Inch

123 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode)

Color Support

16.7 Million

Refresh Rate

75 Hz

Brightness

300 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Curvature

None

Anti-glare Yes

Video Connector HDMI, DP

USB Port

None

Camera

None

Microphone

None

Speaker

2x 2W

Power Consumption (Typical / Maximum)

22W / 32W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

475.57x539.80x180.31 mm / 18.72x21.25x7.1 inches

Weight (Including Stand)

5 kg / 11.1 lbs.

Cables Included

HDMI cable

Environmental Certification

Energy Star Certified, TCO 8.0, TCO Edge 2.0, EPEAT Silver, RoHS

Ergonomic Certification

Eyesafe Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland Flicker Free, TÜV Rheinland Eye Comfort

Base Warranty

3-year

Operating System Support

Support Windows 7, Windows 10

Sync Technology

None

Tiny Support / CPU / Platform

None / None / None

Ethernet / Bluetooth / Wireless

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Display Ram / Storage / Card Slot

None / None / None

EAN/UPC/JAN

0195713813549 / 195713813549 / None

Announce Date

2021-06-15

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a



particular purpose.

https://psref.lenovo.com

Visit psref website for the latest version of Product specifications Reference.
© Lenovo, 2021. All rights reserved.



ThinkVision E24q-20

DISPLAY

Panel Size

23.8-inch

Screen Dimensions

534.7 mm x 313.2 mm

Panel Type

3-side NearEdgeless In-Plane Switching

Active Area

526.9 mm x 296.4 mm

Backlight WLED

Aspect Ratio

16:9

Resolution 2560 x 1440

Pixel Pitch

0.2058 mm x 0.2058 mm

Dot/Pixel Per Inch (DPI/PPI) 123

Viewing angle (H x V @ CR 10:1) 178°/178°

Response Time

4ms (Extreme Mode) 6ms (Normal Mode)

Refresh Rate

75 Hz

Brightness (typical)

300 cd/m²

Contrast Ratio (typical)

1000:1

Dynamic Contrast Ratio (typical)

Color Gamut

99% sRGB

Color Support (typical)

16.7 Million

Color Depth 8-bit

Anti-glare

Yes

CONNECTIVITY

Video Signal 1 x HDMI 1.4 1 x DP 1.2

Audio Signal

1 x Audio Out (3.5mm)

MULTI-MEDIA

Integrated Speakers Yes (2 x 2W)

POWER

Power Consumption (typical/max) 22W / 32W

Power Consumption Sleep/Off Mode

< 0.5W

Power Consumption Switch-off Mode

< 0.3W

ENERGY STAR Power Consumption

 (P_{on}/E_{TEC}) 17W / 53kWh

Power Supply

Internal

Voltage Required AC 100 - 240 V (47-63 Hz)

MECHANICAL

Tilt Angle (front/back) -5° / 22°

Swivel Angle (left/right) 360°

Lift (Max range)

155 mm

Pivot -90° / 90°

VESA Mount Capability

Yes (100 x 100 mm)

ThinkCentre Tiny Support* Yes, by Sandwich Mounting Kit

(PN: 4XH0N04098)

Kensington Lock Slot

Bezel Color Raven Black

DIMENSION

Size Packed (D x H x W. mm/inch) 421.0 x 159.0 x 690.0 mm 16.57 x 6.26 x 27.17 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (Lowest Position)

180.3 x 320.6 x 539.8 mm 7.10 x 12.62 x 21.25 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (Highest Position) 180.3 x 475.6 x 539.8 mm

7.10 x 18.72 x 21.25 inches

Size Unpacked w/o Stand (D x H x W, mm/inch) (Head Only)

44.0 x 325.7 x 539.8 mm 1.73 x 12.82 x 21.25 inches

Weight Packed (kg/lb) 7.0 kg / 15.5 lbs.

Weight Unpacked (kg/lb) 5.0 kg / 11.1 lbs.

Weiaht (Monitor Head Only) (kg/lb) 3.3 kg / 7.3 lbs.

WHAT'S IN THE BOX

Monitor with stand 1 x Power cable (1.8m) 1 x HDMI cable (1.8m) Quick setup guide

CERTIFICATION

ENERGY STAR Certification Yes

CCC Yes

TCO 8.0

TCO Edge 2.0

FPFAT Silver

RoHS (EU 2002/95/EC) Yes

Windows Certification Windows 7, Windows 10 China Energy Efficiency Standard

TÜV Rheinland Eye Comfort

TÜV Rheinland Flicker Free

TÜV Low Blue Light (Hardware Solution)

Yes

Eyesafe Display Certification













Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 1; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.2 Gen 2 &

© 2021 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others

^{*} Optional support.











