

6ft (2m) USB C Cable 5Gbps - High Quality USB-C Cable - USB 3.1/3.2 Gen 1 Type-C Cable - 100W (5A) Power Delivery Charging, DP Alt Mode - USB C to C Cord - Charge & Sync

Product ID: USB315CCV2M



This USB 3.2/3.1 Gen1 5Gbps USB-C cable lets you connect your USB Type-C devices for syncing, charging and powering your devices.

The cable is also compatible with Thunderbolt 3 ports, which means you can charge and sync your USB-C mobile devices using your Thunderbolt 3 laptop.

Power your USB-C devices

With up to 5A (100W) of power delivery, you can power a USB-C laptop, such as your Apple MacBook or Microsoft Surface Book. Simply connect the cable to your USB-C laptop and to a USB-C wall charger.

You can use this USB Type-C cable to power your USB-C hard drive from the USB-C port on your laptop.

Deliver 8K video with DisplayPort 1.4 Alt Mode

The cable supports 8K 30Hz video with DisplayPort 1.4 and is backward compatible to connect your docking station or laptop to a monitor that supports 4K or 1080p resolutions.

Charge your mobile devices

When used with devices that support PD 3.0, this cable charges up to 20V and 5A for a maximum of 100W. It can decrease your charge time and make sure your mobile devices are ready, whenever you need them.

The USB315CCV2M from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

Features

- HIGH PERFORMANCE: 6.6ft (2m) USB-C cable supports USB 3.2/3.1 Gen 1 SuperSpeed (5Gbps data transfer); DisplayPort 1.4 Alt mode up to 8K 30Hz; This USB C to C cable supports up to 100W (5A) Power Delivery 3.0 charging; Thunderbolt 3 compatible
- HIGH QUALITY CONSTRUCTION: For home or office, this high quality USB C Cord has been tested to meet USB 3.1/3.2 Gen 2 standards; 32 AWG conductors with Al-Mylar foil (85% Braid coverage) EMI shielding provides superior signal integrity and reliability
- DURABLE DESIGN: USB Type-C cable has been tested to withstand 10000+ insertions & 4000+ bend cycles at 120 angle; Long lasting flexible TPE jacket and strain relief; TPE is non-toxic and halogen free; Compatible with USB 3.0 and earlier versions
- APPLICATIONS: Works w/docking stations/external hard drives; TB3 or USB Type-C laptops MacBook Air/Pro, Surface Book, Lenovo X1 Carbon, Galaxy Book Pro/360; iPad Pro, Samsung Galaxy S20+/S21 Ultra, Pixel 5; USB-C portable monitors Asus ZenScreen/ProArt
- SPECS: 6.6 feet (2 meters) USB 3.2/3.1 Gen 1 5Gbps (USB 3.0) PD 3.0, 20V (max), 5A (max) USB-C Cable Male to Male 0.19" (4.8 mm) Outer Diameter, 32 AWG Jacket: TPE EMI Shield: Al-Mylar Foil, 85% Braid DP 1.4 Alt mode (8K 30Hz) 2-Year warranty

Hardware		
	Warranty	2 Years
	Connector Plating	Nickel
	Cable Jacket Material	TPE - Thermoplastic Elastomers
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance		
	Type and Rate	USB 3.1 Gen 1 - 5 Gbit/s
Connector(s)		
	Connector A	USB Type-C (24 pin) USB 3.0 (5Gbps)
		USB Type-C (24 pin) USB 3.0 (5Gbps)
Power		
	Power Delivery	100W
Physical Characteristics		
	Color	Gray and Black



	Wire Gauge	30/32 AWG
	Cable Length	6.6 ft [2 m]
	Cable OD	0.2 in [4.8 mm]
	Product Length	5.0 in [12.8 cm]
	Product Width	8.7 in [22.0 cm]
	Product Height	0.6 in [14.0 mm]
	Weight of Product	3.5 oz [100.0 g]
Packaging Information		
	Package Length	0.0 in [0.0 mm]
	Package Width	0.0 in [0.0 mm]
	Package Height	0.0 in [0.0 mm]
	Shipping (Package) Weight	0.0 oz [0.0 g]
What's in the Box	Included in Package	2m USB-C 5Gbps cable

^{*}Product appearance and specifications are subject to change without notice.