

## Key **Features**

- Easily extend your content from laptops and mobile devices
- USB-C one-cable solution for audiovisual and power signal transmission
- Flexible display setup work at any angle
- Compact size, light weight, and highly portable
- Endurable one-piece design



## Product **Description**

The ViewSonic VA1655 is a portable 16" Full HD monitor perfect for overcoming one-screen limitations outside the office. Extend the screen from phones, tablets, or laptops for mobile work, one-on-one presentations, or leisure entertainment. The two universal USB Type C connectors provide a one-cable solution for audiovisual and power signal transmission. The adjustable stand and pivot-able display will support your working angles.



DISPLAY

Display Size (in.): 16

Viewable Area (in.): 15.6

Panel Type IPS Technology Resolution: 1920 x 1080

FHD Resolution Type: Static Contrast Ratio: 800:1 (typ) Dynamic Contrast Ratio: 50M:1 LED Light Source:

250 cd/m<sup>2</sup> (typ) Brightness:

Colors: 16.2M

Color Space Support: 8 bit (6 bit + FRC)

Aspect Ratio: Response Time (Typical GTG): 7ms

Viewing Angles: 170º horizontal, 170º vertical

Backlight Life (Hours): 15000 Hrs (Min)

60 Refresh Rate (Hz): Blue Light Filter: Yes

NTSC: 45% size (Typ) sRGB: 64% size (Typ) Color Gamut:

Pixel Size: 0.179 mm (H) x 0.179 mm (V) Surface Treatment: Anti-Glare, Hard Coating (3H)

COMPATIBILITY

PC Resolution (max): 1920x1080 Mac® Resolution (max): 1920x1080

PC Operating System: Windows 10 certified; macOS tested

1920x1080 Mac® Resolution (min):

CONNECTOR

USB 3.2 Type C DisplayPort Alt

mode only

3.5mm Audio Out: Mini HDMI:

Power in: External power adapter

AUDIO

0.8Watts x2 Internal Speakers:

**POWER** 

5.1W Eco Mode (Conserve): Eco Mode (optimized): 6W Consumption (typical): 7W 7.3W Consumption (max): AC N/A N/A Voltage:

Stand-by: 0.3W Power Supply: External

**ADDITIONAL HARDWARE** 

Kensington Lock Slot:

CONTROLS

Physical Controls: Up, Right, Down, Left, Power

Input Select, Audio Adjust, ViewMode, Color Adjust, Manual On Screen Display: Image Adjust, Setup Menu

**OPERATING CONDITIONS** 

32°F to 104°F (0°C to 40°C) Temperature:

Humidity (non-condensing): 20% to 90%

INPUT SIGNAL

mini HDMI (v1.4): 15 ~ 82KHz, Type Frequency Horizontal:

C: 24 ~ 82KHz

mini HDMI (v1.4): 50 ~ 75Hz, Type C: Frequency Vertical:

**VIDEO INPUT** 

TMDS - mini HDMI (v1.4), Micro-Digital Sync:

Packet - Type C

**ERGONOMICS** 

30º / 53º Tilt (Forward/Back):

WEIGHT (IMPERIAL)

1.5 Net (lbs): Net Without Stand (lbs): 1.5 Gross (lbs): 3.7

WEIGHT (METRIC)

0.7 Net (kg): Net Without Stand (kg): 0.7 Gross (kg): 1.7

**DIMENSIONS (IMPERIAL) (WXHXD)** 

Packaging (in.): 17.1 x 15.4 x 3.5 14.1 x 8.9 x 0.7 Physical (in.): Physical Without Stand (in.): 14.1 x 8.9 x 0.7

**DIMENSIONS (METRIC) (WXHXD)** 

434 x 391 x 88 Packaging (mm): 359 x 227 x 17 Physical (mm): Physical Without Stand (mm): 359 x 227 x 17

GENERAL

Regulations:

cTUVus, FCC-B, ICES003, Energy Star 8.0, EPEAT Bronze, CEC, NRCan, NOM, Mexico Energy, CE, NRCan, NOM, Mexico Energy, CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO, UKCA, BSMI, VCCI, PSE

VA1655 x1, mini HDMI to HDMI Cable (v1.4; Male-Male) x1, USB Type-C Cable (Male-Male) x1, Quick Start PACKAGE CONTENTS:

Guide x1. Sleeve case x1

Please dispose of in accordance with Recycle/Disposal: local, state or federal laws

\*Warranty offered may differ from Warranty: market to market

144

Country Of Origin:

Power Management: Energy Star standards, EPEAT