

## PERFORMANCE

### Processor

Intel® Core™ i7-11800H (8C / 16T, 2.3 / 4.6GHz, 24MB)

### Graphics

NVIDIA® T1200 4GB GDDR6

### Chipset

Intel WM590

### Memory

2x 8GB SO-DIMM DDR4-3200 Non-ECC

### Memory Slots

Four DDR4 SO-DIMM slots, dual-channel capable

### Max Memory

Up to 128GB DDR4-3200

### Storage

512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal2

### Storage Support

Up to three drives, 3x M.2 SSD  
• M.2 2280 SSD up to 2TB

### Card Reader

SD Reader

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

### Speakers

Stereo speakers, Dolby® Atmos®

### Camera

IR & 720p with Privacy Shutter

### Microphone

2x, Array

### Battery

Integrated 94Wh

### Max Battery Life

MobileMark® 2018: 9 hr  
JEITA 2.0: 11.5 hr

### Power Adapter

170W Slim Tip (3-pin)

## DESIGN

### Display

15.6" FHD (1920x1080) IPS 500nits Anti-glare, 100% sRGB, Dolby Vision™

### Color Calibrator

No color calibration

### Keyboard

Backlit, English

### Case Color

Black

### Case Material

GFRP 50% (PPS695 + GF 50%, top),  
GFRP 50% (PA + GF 50%, bottom)

### Pen

No Support

### Dimensions (WxDxH)

375.4 x 252.3 x 24.5-31.45 mm (14.24 x 9.67 x 0.96-1.24 inches)

### Weight

2.87 kg (6.32 lbs)

## SOFTWARE

### Operating System

Windows® 11 Pro 64, English

## CONNECTIVITY

### Ethernet

2.5 GbE

### WLAN + Bluetooth®

Intel AX210 11ax, 2x2 + BT5.2

### WWAN

WWAN Upgradable to 4G

### Standard Ports

- 2x USB 3.2 Gen 1 (one Always On)
- 1x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 2x Thunderbolt™ 4 / USB4™ 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort 1.4a)
- 1x SD card reader
- 1x Ethernet (2.5GbE RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)

### Optional Ports (configured)

- 1x HDMI® 2.0 (model with NVIDIA T1200 graphics)
- 1x Nano-SIM card slot (WWAN model)

### Docking

Various docking solutions supported via Thunderbolt or USB-C.

For more compatible docking solutions, please visit .

[Docking for ThinkPad® P15 Gen 2](#)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0

### Fingerprint Reader

Touch Style, Match-on-Chip

### Physical Locks

Kensington® Security Slot (3 x 7 mm)

### Other Security

- IR camera for Windows® Hello
- Camera privacy shutter

## SERVICE

### Base Warranty

3-year, Depot

### Included Upgrade

3Y Premier Support Upgrade from 3Y Courier/Carry-in (5WS0V07092)

## CERTIFICATIONS

### Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0
- RoHS compliant

### Mil-Spec Test

MIL-STD-810H military test passed

### ISV Certifications

Please visit [www.thinkworkstations.com/isv-certifications/](http://www.thinkworkstations.com/isv-certifications/)

## MODEL

**TopSeller** : Yes

**Announce Date** : 2021-12-10

**EAN / UPC / JAN** : 196378084237

**End of Support** : 2028-01-15



## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad 230W AC Adapter (slim tip) - US/CAN/MEX

4X20E75111

Keep a spare ThinkPad 230W AC Adapter at hand to ensure your ThinkPad has a consistent flow of power. Keep one adapter in the office, one at home and another in your carrying case for immediate, convenient access to p...

## Recommended Services

BEST	4Y Lenovo Protect (Premier Support + ADP + KYD + 3Y SBTY + International Upg) (5PS1D67024)
BETTER	3Y Lenovo Protect (ADP + KYD + SBTY + International Upg) (5PS1D67023)
GOOD	3Y Lenovo Support (KYD + SBTY + International Upg) (5PS1D67026)

For a full list of accessories and services, please visit: <https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference