

# ThinkSmart Core for Microsoft Team Rooms 11S30008US

**Product**

ThinkSmart Core Full Room Kit

**Region**

NA

**Country/Region**

USA

**Machine Type**

11S3

**TopSeller**

TopSeller

**Processor**

Intel Core i5-1145G7E (4C / 8T, 1.5 / 4.1GHz, 8MB)

**Graphics**

Integrated Intel Iris Xe Graphics

**Chipset**

Intel SoC Platform

**Memory**

8GB Soldered DDR4-3200

**Storage**

256GB SSD M.2 2280 PCIe 3.0x4 NVMe

**Display**

10.1" Display on ThinkSmart Touch Controller

**Touchscreen**

10-point Multi-touch

**Remote Control**

ThinkSmart Touch Controller

**Camera**

ThinkSmart Cam

**Microphone**

2x Mic on Camera + 4x Mic on ThinkSmart Bar + 2x Satellite Mic

**Speakers**

ThinkSmart Bar (4 Speakers)

**Ethernet**

Integrated 100/1000M

**WLAN + Bluetooth**

Intel AX201 11ax, 2x2 + BT5.0, vPro

**VESA Mount**

Integrated VESA Mount

**Case Color**

Black case with red bottom

**Power Supply**

90W 89% Adapter

**System Management**

Intel vPro

**Operating System**

Windows 10 IoT Enterprise SAC 64, English

**Base Warranty**

3-year, Onsite

**Included Upgrade**

First Year Maintenance (5MS0Z44663), 3Y Premier Support Upgrade from 3Y Onsite (5WS0Y57697)

**EAN / UPC / JAN**

196378829661

**End of Support**

N/A

**Announce Date**

2021-11-16

**Recommended Services****Best**

5Y Premier Support upgrade from 3Y Premier Support (5WS0Z53126)

**Better**

4Y Premier Support upgrade from 3Y Premier Support (5WS0Z53125)

**Notes:****California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

 [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



# ThinkSmart Core for Microsoft Team Rooms Platform Specifications

Product Specifications Reference (PSREF)



ThinkSmart Core Kit Options		ThinkSmart Core Full Room Kit	ThinkSmart Core + Controller Kit	<b>ThinkSmart Controller</b>		
	ThinkSmart Core	1x	1x	Display	<b>10.1" (1280x800)</b> , < 340 nits, 16:10 aspect ratio, Anti-Fingerprint, Anti-Glare, support 30° or 60° placement Supports 10-point touch	
	ThinkSmart Controller	1x	1x	Multi-touch Sensors	IR sensors for motion detection, up to 3 meters distance and 90° angle	
	ThinkSmart Cam	1x	None	Ports	<ul style="list-style-type: none"> <li>• 1x USB-C (connect to compute unit, 10m USB-C cable included)</li> <li>• 1x 3.5mm headphone / mic combo jack,</li> <li>• 1x Kensington Security Slot</li> </ul>	
	ThinkSmart Bar	1x	None	Dimensions	<ul style="list-style-type: none"> <li>• Width: 265.5 mm (10.5 inches)</li> <li>• Height: 168.1 mm (6.6 inches)</li> <li>• Depth: 13 mm (0.5 inches) 83.3 mm (3.3 inches) with the stand</li> </ul>	
	Satellite Microphone	2x (optional)	None	Weight	753.8 g (1.7 lb)	
Color	Raven black case with red bottom			<b>ThinkSmart Cam</b>		
Base Warranty	Some: 3-year Lenovo Premier Support warranty Some: 3-year limited onsite warranty			Image		
<b>Compute System</b>						
Processor	11th Gen Intel® Core™ i5 Processor					
	Processor	Cores / Threads	Frequency Base/Max(GHz)	Cache	Memory Support (Up to)	Integrated Graphics
	Core i5-1145G7E	4 / 8	1.5G / 4.1G	8 MB	DDR4-3200	Intel Iris® Xe Graphics
Memory	8GB DDR4-3200, dual-channel					
Storage	256GB M.2 SSD (2280) / PCIe NVMe, PCIe 3.0 x4					
Chipset	<b>Intel SoC (System on Chip) platform</b>					
Front Ports*	None					
Rear Ports*	<ul style="list-style-type: none"> <li>• 2x USB 3.2 Gen 2 (One for ThinkSmart Bar, one for ThinkSmart Cam)</li> <li>• 1x USB 3.2 Gen1</li> <li>• 1x Thunderbolt™ 4</li> <li>• 1x USB-C 3.2 Gen 1 (connect to ThinkSmart Controller)</li> <li>• 1x HDMI-in</li> <li>• 2x HDMI-out 1.4</li> <li>• 1x Ethernet</li> <li>• 1x power connector</li> </ul>					
	* Depending on many factors, actual data transfer speed may be lower than theoretical speed					
WLAN	11ac wireless, M.2 Card, Intel Wireless-AC 9560 (dual band), Wi-Fi + Bluetooth 5.0 combo adapter, Intel vPro technology support, 2x2					
Bluetooth	Bluetooth 5.0 wireless, integrated in Wi-Fi + Bluetooth combo adapter					
Ethernet	Gigabit ethernet, Intel Ethernet Connection I219-LM (Jacksonville), Wake on LAN®					
Manageability	Intel Active Management Technology 15.0 (Intel AMT 15.0)					
Security chip	Discrete TPM 2.0, TCG Certified					
Security features	<ul style="list-style-type: none"> <li>• Kensington Security Slot, with the integrated cable management, can also secure the cable connection</li> <li>• Power-on, Supervisor, hard disk password</li> <li>• Smart USB Protection</li> </ul>					
Power supply	90 watts adapter, 100V - 240V autosensing, 89% PSU					
Mounting	VESA Mount Kit					
Dimensions	<ul style="list-style-type: none"> <li>• Width: 226 mm (8.9 inches)</li> <li>• Height: 37.5 mm (1.5 inches), 51.7 mm (2 inches) with the clamp unfolded</li> <li>• Depth: 200 mm (7.9 inches)</li> </ul>					
Weight	1.1 kg (2.4 lb)					
Operating System	Windows 10 IoT Enterprise SAC 64 bit					
See footnotes for more detailed information						

# ThinkSmart Core for Microsoft Team Rooms

