

Product data sheet

Specifications



APC Smart-UPS, Line Interactive, 1000VA, Tower, 120V, 8x NEMA 5-15R outlets, SmartConnect Port+SmartSlot, AVR, LCD, TAA

SMT1000CUS

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Other Input Voltage	110 V 125 V
Main Output Voltage	120 V
Other Output Voltage	110 V 125 V
Kw Rating	700 W
Rated power in VA	1000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	8 NEMA 5-15R
Provided equipment	CD with software

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Charge Power (Watts)	99 W rated
Replacement battery	RBC6

Physical

color Black

Input

Efficiency at full load	75...154 V adjustable
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Maximum configurable power in VA	1000 VA
Max Configurable Power (Watts)	700 W
Topology	Line Interactive

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Waveform Type	Sine wave
----------------------	-----------

Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
---	---------------------------------

Conformance

Product Certifications	cULus ENERGY STAR V2.0 (USA)
-------------------------------	---------------------------------

Environmental

Relative Humidity	0...95 %
--------------------------	----------

Storage Relative Humidity	0...95 %
----------------------------------	----------

Ordering and shipping details

GTIN	731304424437
-------------	--------------

Country of origin	US
--------------------------	----

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Number of Units in Package 1	1
-------------------------------------	---

Package 1 Height	13.0 in (33 cm)
-------------------------	-----------------

Package 1 Width	23.2 in (59 cm)
------------------------	-----------------

Package 1 Length	13.0 in (33 cm)
-------------------------	-----------------

Package 1 Weight	49.91 lb(US) (22.64 kg)
-------------------------	-------------------------

Contractual warranty

Warranty	3 Years
-----------------	---------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Environmental Certifications

Energy Star® ENERGY STAR UPS V2.0 (USA)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile [End of Life Information](#)