

Product data sheet

Specifications



APC Smart-UPS, Line Interactive,
1500VA, Rackmount 2U, 120V, 6x
NEMA 5-15R outlets,
SmartConnect Port+SmartSlot,
AVR, LCD, TAA

SMT1500RM2UCUS

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Other Input Voltage	110 V 125 V
Main Output Voltage	120 V
Other Output Voltage	110 V 125 V
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	6 NEMA 5-15R
Provided equipment	CD with software
Range of Product	Smart-UPS

Batteries & Runtime

Efficiency	View Efficiency Graph
Replacement battery	APCRBC159

Physical

color	Black
-------	-------

Input

Efficiency at full load	75...154 V adjustable
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	cULus ENERGY STAR V2.0 (USA)
-------------------------------	---------------------------------

Environmental

Relative Humidity	0...95 %
--------------------------	----------

Storage Relative Humidity	0...95 %
----------------------------------	----------

Ordering and shipping details

GTIN	731304424420
-------------	--------------

Country of origin	US
--------------------------	----

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Number of Units in Package 1	1
-------------------------------------	---

Package 1 Height	9.3 in (23.5 cm)
-------------------------	------------------

Package 1 Width	24.02 in (61 cm)
------------------------	------------------

Package 1 Length	23.2 in (59 cm)
-------------------------	-----------------

Package 1 Weight	70.81 lb(US) (32.12 kg)
-------------------------	-------------------------

Contractual warranty

Warranty	3 Years
-----------------	---------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information Yes

Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Compliant with Exemptions

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile [End of Life Information](#)