

# Product data sheet

Specifications



APC Smart-UPS X, Line Interactive, 750VA, Rack/tower convertible 2U, 120V, 8x 5-15R NEMA, SmartConnect port, Extended runtime, TAA

SMX750CUS

## Overview

Lead time Usually in Stock

## Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	675 W
Rated power in VA	750 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	8 NEMA 5-15R
Provided equipment	CD with software

## Complementary

Software package SmartConnect software for remote power monitoring feature availability varies by terms of use

## Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Battery Charge Power (Watts)	104 W rated

## Physical

color Black

## Input

Efficiency at full load	75...154 V adjustable
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Maximum configurable power in VA	750 VA
Max Configurable Power (Watts)	675 W
Topology	Line Interactive

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

<b>Waveform Type</b>	Sine wave
----------------------	-----------

---

<b>Output Frequency (sync to mains)</b>	50/60 Hz +/- 3 Hz sync to mains
---	---------------------------------

---

## Conformance

---

<b>Product Certifications</b>	cUL Listed ENERGY STAR V2.0 (USA)
-------------------------------	--------------------------------------

---

## Environmental

---

<b>Relative Humidity</b>	0...95 %
--------------------------	----------

---

<b>Storage Relative Humidity</b>	0...95 %
----------------------------------	----------

---

## Communications & Management

---

<b>Communication port support</b>	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
-----------------------------------	--

---

## Ordering and shipping details

---

<b>GTIN</b>	731304424475
-------------	--------------

---

<b>Country of origin</b>	US
--------------------------	----

---

## Packing Units

---

<b>Unit Type of Package 1</b>	PCE
-------------------------------	-----

---

<b>Number of Units in Package 1</b>	1
-------------------------------------	---

---

<b>Package 1 Height</b>	23.2 in (58.9 cm)
-------------------------	-------------------

---

<b>Package 1 Width</b>	24.4 in (62 cm)
------------------------	-----------------

---

<b>Package 1 Length</b>	9.7 in (24.6 cm)
-------------------------	------------------

---

<b>Package 1 Weight</b>	58.4 lb(US) (26.5 kg)
-------------------------	-----------------------

---

## Contractual warranty

---

<b>Warranty</b>	3 Years
-----------------	---------

---

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

 Mercury Free

 Rohs Exemption Information Yes

## Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

## Certifications & Standards

**Reach Regulation** [REACH Declaration](#)

**Eu Rohs Directive** Compliant with Exemptions

**China Rohs Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

**Environmental Disclosure** [Product Environmental Profile](#)

**Weee** The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

**Circularity Profile** [End of Life Information](#)