

Safe-IT Antibacterial Hospital-Grade Power Cord, 5-15P to C13 - Green Dot, 13A, 125V, 16 AWG, Black, 6 ft. (1.8 m)

MODEL NUMBER: P006AB-006-HG







Hospital-grade power cord with antibacterial properties connects your PC or other device with a C14 inlet to a grounded AC outlet.

Features

Hospital-Grade Power Cable is a Safe Solution for Medical Facilities

This Safe-IT[™] hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment with a three-pin C14 inlet. It features a C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient care vicinities. The six-foot (1.8-meter) length allows you flexibility in placing equipment with respect to the power outlet.

Provides Extra Protection Against Certain Bacteria

The connectors and PVC jacket are constructed using an antibacterial material that is effective in inhibiting the growth of Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this cable an ideal solution for medical environments, such as hospitals, laboratories and clinics, and anywhere else that needs extra protection against bacteria.

Designed and Tested to Strict Hospital-Grade Standards

This cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

Specifications

OVERVIEW	
UPC Code	037332266194
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America

Highlights

- Recommended for connecting devices to power outlets outside patient care vicinities
- Made with antibacterial material proven effective in inhibiting the growth of E. coli and staph
- 6 ft. length allows flexibility in placing devices in relationship to AC outlet
- Tested to ANSI/UL 62 and 817 and CAN/CSA C22.2 no. 21 and 49 standards

Package Includes

P006AB-006-HG Antibacterial Hospital-Grade Power Cord, 5-15P to C13, Black, 6 ft. (1.8 m)



	13	
Maximum Input Amps Voltage Compatibility (VAC)	125	
	123	
PHYSICAL		
Plug Color	Black	
Cable Jacket Color	Black	
Connector Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	FT2	
Power Cord Jacket Type	SJT	
Cable Outer Diameter (OD)	0.325"	
Number of Conductors	3	
Wire Gauge (AWG)	16	
Wire Gauge (OD - mm ²)	1.31	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
ENVIRONMENTAL		
Operating Temperature Range	-4 to 221 F (-20 to 105 C)	
Storage Temperature Range	-4 to 140 F (-20 to 60 C)	
Operating Humidity Range	20% TO 80% RH, Non-Condensing	
Storage Humidity Range	20% TO 80% RH, Non-Condensing	
CONNECTIONS		
Side A - Connector 1	NEMA 5-15P	
Side B - Connector 1	IEC-320-C13	
FEATURES & SPECIFICATIONS		
High Voltage	No	
Locking Plug	No	
Antibacterial	Yes	
Angled Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		



Certifications	UL/cUL, RoHS, REACH	
Approvals	UL/CSA	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies