

Lenovo D22e-20 66D2KCC6US

Product

Lenovo D22e-20

Machine Type

66D2

Region

LA, NA

Display Size

21.45"

View Area

478.6x260.2 mm

Panel

VA

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.2490x0.2410 mm

Dot / Pixel Per Inch

103 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode)

Color Support

16.7 Million

Refresh Rate

75 Hz

Brightness

250 nits

Contrast Ratio

3000:1

Color Gamut

72% NTSC

Curvature

None

Anti-glare

Yes

Video Connector

HDMI, VGA

USB Port

None

Camera

None

Microphone

None

Speakers

None

Power Consumption (Typical / Maximum)

15W / 17W

Power Adapter

Integrated

Stand

Tilt Stand

Color

Raven Black

Side Bezel Width

1.8 mm

Dimensions with Stand (HxWxD)

367.4x493.0x209.5 mm / 14.46x19.41x8.25 inches

Weight (Including Stand)

2.6 kg / 5.9 lbs.

Cables Included

HDMI cable

Environmental Certification

Energy Star Certified, EPEAT Gold, RoHS

Ergonomic Certification

TÜV Rheinland Low Blue Light, TÜV Rheinland Flicker Free

Base Warranty

1-year

Operating System Support

Support Windows 10

Sync Technology

AMD FreeSync

Tiny Support / CPU / Platform

Tiny Support, Nano Support / None / None

Ethernet / Bluetooth / Wireless

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Display Ram / Storage / Card Slot

None / None / None

EAN / UPC / JAN

0195890137797 / 195890137797 / None

Announce Date

2021-05-27

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2022. All rights reserved.



Lenovo™

Lenovo D22e-20

DISPLAY

Panel Size
21.45-inch

Screen Dimensions
487.6 mm x 265.9 mm

Panel Type
VA
3-side NearEdgeless

Active Area
478.6 mm x 260.2 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.2490 mm x 0.2410 mm

Pixel Per Inch (DPI/PPI)
103

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
4ms (Extreme Mode)
6ms (Normal Mode)

Refresh Rate
75 Hz²

Brightness (typical)
250 cd/m²

Contrast Ratio (typical)
3000:1

Dynamic Contrast Ratio (typical)
3M:1

Color Gamut
72% NTSC (CIE 1931)

Color Support (typical)
16.7 Million

Color Depth
8-bit

Anti-glare
Yes

CONNECTIVITY

Video Signal
1 x HDMI 1.4
1 x VGA

Audio Signal
1 x Audio Out (3.5 mm)

SPECIAL FEATURES

Sync Technology
AMD FreeSync™¹

POWER

Power Consumption (typical/max)
15W / 17W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-off Mode
< 0.3W

Power Supply
Internal

Voltage Required
AC 100 to 240 V (50-60 Hz)

MECHANICAL

Tilt Angle (front/back)
-5° / 22°

VESA Mount Capability
Yes (100 x 100 mm)

ThinkCentre M Series Tiny support
Yes, by Tiny VESA mount II
(PN: 4XFON03161)

ThinkCentre M Series Nano support
Yes, by Nano VESA mount
(PN: 4XFOV81630)

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (side)
1.8 mm

Bezel Width (top/bottom)
1.8 / 23.59 mm

DIMENSION

Size Packed (D x H x W, mm/inch)
594.0 x 376.0 x 150.0mm /
23.39 x 14.80 x 5.91 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)
209.5 x 367.4 x 493.0mm /
8.25 x 14.47 x 19.41 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)
209.5 x 367.4 x 493.0mm /
8.25 x 14.47 x 19.41 inches

Size Unpacked w/o stand (head Only) (D x H x W) (mm/inch)
52.5 x 292.2 x 493.0mm /
2.07 x 11.51 x 19.41 inches

Weight Packed (kg/lb)
4.1 kg / 9.1 lbs.

Weight Unpacked (kg/lb)
2.6 kg / 5.9 lbs.

Weight (Monitor Head Only) (kg/lb)
2.3 kg / 5.1 lbs.

WHAT'S IN THE BOX

Monitor with stand
1 x Power cable (1.8 m)
1 x HDMI cable (1.8 m)
Quick setup guide

CERTIFICATION

CCC
Yes

RoHS (EU 2002/95/EC)
Yes

Windows Certification
Windows 10

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Low Blue Light
Yes

TÜV Rheinland Flicker Free
Yes

Energy Star® 8.0
Yes

EPEAT™
Gold

¹AMD FreeSync can only work with AMD Radeon series graphic card
²Only for HDMI input

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2021 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.



Lenovo D22e-20

