PN-HY551

Slim and lightweight digital signage displays











- Make an impact with the 55" display in your retail or corporate environments
- Enhanced and true representation of colour shown from wide colour gamut
- Show and hear content easily with integrated 4K USB media player and speakers
- Slim, sleek and elegant design to suit any setting

- Showcase images and video in detail with 4K Ultra HD resolution (3840 x 2160 pixels)
- Continuous display of content during business operating hours 24/7
- Latest HDMI Connectivity for 4K at 60Hz
- Flexible installation in portrait and landscape



Specifications

DISPLAY MODULE DATA

Panel TechnologyTFT LCDNative Resolution (Pixels)3840 x 2160Diagonal Size (inches / cm)55 / 138Aspect Ratio16:9

 Backlight Technology
 W-LED / Full Array

 Brightness (cd/m2)
 500

 Contrast Ratio
 5000 : 1

Contrast Ratio 5000: 1
Display Colours 1,06 Billion
Response Time (grey to grey avg) ms
Viewing Angle (H/V)0 CR > 10 178 / 178

POWER SUPPLY AND OPERATING ENVIRONMENT

Operating Voltage(ACV) / Frequency(Hz)100-240 / 50-60Power Consumption (W) (Operating MAX)150Power Consumption (W) (Standby)0,50Operating Temperature (oC)0 - 40Humidity (%)20 - 80RH

WEIGHTS AND MEASURES

 Bezel Size (L/R) mm
 13,9 / 13,9

 Bezel Size (U/L) mm
 13,9 / 13,9

 Product Dimensions (W/H/D) mm
 1241 x 712,6 x 63,5

 Product Weight Without Stand (Kg)
 18

CONNECTIVITY (AUDIO/VIDEO) INPUT

 HDMI
 3

 VGA
 1

 Audio 3.5mm Jack
 1

Other HDMI2.0 / HDCP 2.2 / CEC

CONNECTIVITY (CONTROL/SERIAL DATA)

 RS232C IN
 1

 LAN Port
 1

 USB
 1

KEY SPECIFICATIONS

24/7 Operation Certified .

Built in Speakers (W) 10W + 10W
Computer Input - Plug and Play
Power Management .

Cabinet Colour Black

SAFETY AND ENVIRONMENT (EUROPE)

CE, CB Report • Mercury Content (mg) 0

INSTALLATION

 Landscape
 •

 Portrait
 •

 Horizontal
 •

 Mounting (VESA/Number of Points/Pitch mm)
 VESA 400 x 400

CONNECTIVITY (AUDIO/VIDEO) OUTPUT

Audio RCA R-L 1

