

Mechanical MX Low Profile Keyboard with RGB lighting and metal housing



Image: G8A-25010LYBDE-2, RGB, black

Design variants can differ from the product illustration

Mechanical MX Low Profile Keyboard with RGB lighting and metal housing

The CHERRY MX 10.0N RGB keyboard provides impressive proof of how flat a premium mechanical keyboard can be. This is enabled using CHERRY MX LOW PROFILE RGB SPEED switches, which are exclusively manufactured in Germany. The overall height of the USB keyboard is just 22 mm. This allows you to type ergonomically and comfortably, even without a palm rest. Although it is elegantly slim, its solid metal construction immediately catches the eye. Even the fold-out foot is made entirely of aluminum. As a special feature, this foot folds in automatically as soon as you lift the keyboard up. The keyboard is stable on the desktop and will not slip regardless of whether the foot is up or not.

Each key contains an RGB LED with up to 16.8 million colors. In addition to pre-programmed effects, you can also choose your own colors or illuminate individual keys. You have the choice between vivid color effects or discrete single-color lighting.

CHERRY MX LOW PROFILE RGB SPEED switches can withstand more than 100 million presses per key. Despite the low profile, you immediately sense the inimitable MX feeling with every keystroke. The switching characteristic is linear, i.e., with no click and without noticeable resistance. The switching point takes effect after actuation of just one millimeter. It is not necessary to push the key all the way down. This not only increases the reaction time, but also ensures that every keystroke is registered. A huge advantage and not just for gamers.

Due to the robust construction, great durability and adjustable illumination, the MX 10.0N RGB is not only suitable for gamers and computer enthusiasts, but also for industrial applications. The compact keyboard is at home anywhere and is a genuine all-rounder!

Mechanical MX Low Profile Keyboard with RGB lighting and metal housing

Advantages

- Original CHERRY MX LOW PROFILE RGB SPEED (made in Germany)
- Over 100 million presses per key guaranteed
- Stable, very flat metal housing
- Innovative metal base for height adjustment
- Removable USB-C to USB-A cable
- RGB lighting with numerous lighting modes and customization options
- Durable key lettering (laser etched & varnished)
- Anti-ghosting and N-key rollover
- 8 megabytes of onboard memory

Technical data

Layout (country or language):

Product dependant, see table "Models"

Housing color:

Product dependant, see table "Models"

Key color:

Product dependant, see table "Models"

Weight (product):

Keyboard with cable:	approx. 854 g
Keyboard without cable:	approx. 812 g

Total weight (with packing):

Approx. 1,066 g

Cable length:

Approx. 160 cm

Storage temperature:

-20 °C to 60 °C

Working temperature:

0 °C to 50 °C

Current consumption:

max. 500 mA

Connection:

USB

Product approvals:

- CE
- KCC
- China RoHS
- Windows hardware compatibility
- UKCA

System requirements:

Windows 7, 8, 10, 11

Delivery Volume:

- CHERRY Keyboard
- Operating Manual

Dimensions:

Keyboard:	approx. 425 x 127x 22 mm
Packing:	approx. 450 x 180 x 30 mm

Keyboard:

- Key Technology: CHERRY MX LOW PROFILE RGB SPEED
- Service life and characteristics depend on switch specification (see www.cherrymx.de).
Lifetime standard key: > 100 million actuations.
- Operating characteristics: Product dependant, see table "Models "
- Labeling technology: Laser
- Number of keys: Product dependant, see table "Models"

Packing unit:

Number of products in the master package: 10

Mechanical MX Low Profile Keyboard with RGB lighting and metal housing

Warranty:

We put a lot of dedication and hard work into the development of our products, and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below.

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

CHERRY MX 10.0N RGB



Mechanical MX Low Profile Keyboard with RGB lighting and metal housing

Versions

Possible country / layout versions

	Product name	Switch characteristics	Layout (country / language)	Lighting	Order number	EAN/UPC-Code	Housing color	Key color	Labeling technology	Number of keys
1	CHERRY MX 10.0N RGB	CHERRY MX LOW PROFILE RGB SPEED	Germany	RGB	G8A-25010LVBDE-2	4025112096488	Black	Black	Laser	105 + 4
2	CHERRY MX 10.0N RGB	CHERRY MX LOW PROFILE RGB SPEED	France	RGB	G8A-25010LVBFR-2	4025112096495	Black	Black	Laser	105 + 4
3	CHERRY MX 10.0N RGB	CHERRY MX LOW PROFILE RGB SPEED	UK	RGB	G8A-25010LVBGB-2	4025112096501	Black	Black	Laser	105 + 4
4	CHERRY MX 10.0N RGB	CHERRY MX LOW PROFILE RGB SPEED	US-International	RGB	G8A-25010LVBEU-2	4025112096518	Black	Black	Laser	104 + 4
5	CHERRY MX 10.0N RGB	CHERRY MX LOW PROFILE RGB SPEED	Pan-Nordic	RGB	G8A-25010LVBPN-2	4025112096525	Black	Black	Laser	105 + 4
6	CHERRY MX 10.0N RGB	CHERRY MX LOW PROFILE RGB SPEED	US-Layout	RGB	G8A-25010LVBUS-2	840183605896 (UPC)	Black	Black	Laser	104 + 4
7	CHERRY MX 10.0N RGB	CHERRY MX LOW PROFILE RGB SPEED	Switzerland	RGB	G8A-25010LVBCH-2	4025112099489	Black	Black	Laser	105 + 4

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.