

# newline TANGO




Connect with USB



Plug & Play Design



1080p Camera



120° Field of View



Integrated Microphone



Digital Noise Reduction

## PLUG, PLAY, **CONNECT** WITH STYLE

Newline Tango brings you simple video connectivity with any device, including your Newline display. Be UC-ready in a flash by adding the 1080p HD camera to any Newline display. Newline Tango works with any video software including Zoom, Meet, Teams, Webex, and more. With an integrated microphone, digital noise reduction, and a wide-angle field of view, be seen and heard from anywhere in the room. Whether you're connecting to your remote students in your classroom or hosting virtual meetings with your team, Newline Tango is here to boost your videoconferencing with style.

# TANGO

<b>Model</b>		<b>TANGO-CAM</b>
<b>Camera</b>		
Sensor	1/2.7", CMOS, total pixel : 2 Mega	
Scanning Mode	Progressive	
Lens Mount	M12	
Lense	focus: f=3.1mm, FOV: 119°	
Minimal Illumination	0.5 Lux @ (F1.8, AGC ON)	
Shutter	1/30s ~ 1/10000s	
Digital Noise Reduction	2D, 3D digital noise reduction	
Backlight Compensation	Yes	
<b>Microphone</b>		
Pickup Range	11.8 ft	
Direction	Omni-directional	
Noise Cancellation	Yes	
Automatic Gain Control	Yes	
<b>USB Specification</b>		
Compatible Operating System	Windows® 7 (1080P and under only), Windows 8.1, Windows 10 or higher; macOS™ 10.10 or higher; Google™ Chromebook™ Version 29.0.1547.70 or higher; Linux (UVC supported)	
Hardware Requirements	2.4 GHz Intel® Core 2 Duo processor or higher; 2 GB RAM or more; USB 2.0 port (USB 3.0 required for 4K)	
Color System/Compression	H.264 / MJPEG / YUY2	
Video Format	1080p@30fps/25fps, 720p@30fps/25fps, 960x540p@30fps/25fps, 640x360p@30fps/25fps	
USB Video Communicaiton Protocol	UVC v1.0	
<b>General Specification</b>		
Input Voltage	5V (USB Power)	
Power Consumption	< 1.4W	
Dimensions	7.6 x 1.8 x 5.3 in	
Net Weight	0.47 lbs	
Operating Temperature	14°F ~ 104°F	
Storage Temperature	-40°F ~ 140°F	
Mounting Options	Panel, desktop or tri-pod	