



USB-C Male to USB-C Male Cable USB 3.2 Gen2 10 Gbps 3A 2m/6.6ft Black

V7USBC10GB-2M

SKU: CB55386

V7 High-Speed USB cables are designed to connect and charge computer peripherals such as digital cameras, printers, scanners, personal media players, external high disk drives, flash drives and network adapters. Capable of 10 Gbps of data transfer speed with 4K resolution and 3A power output. These triple shielded USB cables feature high-grade PVC jacket construction combined with shielded twisted pair data-lines, providing excellent performance. Built for long term use and high performance using quality materials with ISO certified process and backed by our V7 warranty.

- Enhanced connectivity and data transfer for your devices
- Provides up to 3A pass through charging and 10 Gbps data transfer speed
- Hassle free setup, simple plug and play connectivity
- Triple shielding aluminum, mylar foil, braid provides excellent RF and EMI shielding. Corrosion resistant connectors and strain relief for optimal signal transfer and durability.
- Quality manufacturing process in our ISO certified facilities and backed by V7 warranty

General

SKU: CB55386
 Model: V7USBC10GB-2M
 EAN: 0662919114744
 Warranty: 1 year
 Compliance: CE, RoHS, UKCA, WEEE
 Country Of Origin: Vietnam
 Package Type: Polybag

Color

Color: Black

Package Dimensions

Package Dimensions (L/W/H): 6.3 x 8.27 x 0.39 in
 (160 x 210 x 10 mm)
 Shipping Weight: 0.042 kg (0.09 lbs)

Product Dimensions

Product Weight: 0.038 kg (0.08 lbs)

Technical

Cable Jacket: PVC
 Maximum Resolution: 3840 X 2160
 Conductor: Tin Plated Copper
 Cable Length: 2m/6.6ft
 Conductor Size: 30AWG
 Shielding: Aluminum Mylar foil with Braid
 Standard: USB 3.2 Gen 2
 Connectors: USB C
 Frequency: 60 Hz
 Load Capacity (Watts): 60W (20V 3A)
 Peak Current: 3A
 Connector 1: USB-C Male
 Connector 2: USB-C Male
 Data Transfer Rate: 10 Gbps