



msi

BUSINESS PRODUCTIVITY MONITOR

PRO MP241X



SPECIFICATIONS

Compatibility	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
NOTE	HDMI: 1920 x 1080 (Up to 75Hz) D-Sub: 1920 x 1080 (Up to 60Hz)
WEIGHT (NW / GW)	2.85 kg (6.28 lbs) / 4.27 kg (9.41 lbs)
CARTON DIMENSION (W X H X D)	616 x 409 x 125 mm (24.25 x 16.10 x 4.92 inch)
COLOR BIT	8 bits
ADJUSTMENT (TILT)	-5° ~ 15°
POWER INPUT	100~240V, 50~60Hz
POWER TYPE	External Adaptor (12V 2.5A)
VESA MOUNTING	75 x 75 mm
KENSINGTON LOCK	Yes
VIDEO PORTS	1x HDMI (1.4b) 1x D-Sub (VGA)
DIMENSION (W X H X D)	541.79 x 416.61 x 180.8 mm (21.33 x 16.4 x 7.12 inch)
PIXEL PITCH (H X V)	0.2745(H) x 0.2745(V)
DISPLAY COLORS	16.7M
SURFACE TREATMENT	Anti-glare
ACTIVE DISPLAY AREA (MM)	534.04(H) x 307.76(V)
sRGB	105% (CIE 1976)
CONTRAST RATIO	3000:1
ASPECT RATIO	16:9
VIEWING ANGLE	178°(H) / 178°(V)
PANEL TYPE	VA
RESPONSE TIME	8ms
REFRESH RATE	75Hz
PANEL RESOLUTION	1920 x 1080 (FHD)
PANEL SIZE	23.8"
BRIGHTNESS (NITS)	250 cd/m2

FEATURES

- 23.8" Screen Size**
View your applications, spreadsheets and more with a perfect 23.8 inches screen
- Full HD Resolution**
Experience a breathtaking screen clarity that comes with Full HD (1920x1080) resolution
- Anti-Glare Display Design**
An anti-glare display makes viewing the display more pleasant for users and reduces eyestrain for users
- Display Kit Support**
Providing the most convenient tool, the proper color & display mode to you while working with it everyday.
- VESA Mountable**
To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.
- IPS Grade Panel**
Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video

CONNECTIONS



1. 1x HDMI (1.4)
2. 1x D-Sub(VGA)
3. 1x DC Jack
4. 1x Kensington Lock