

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773 869 12

Telephone: 773.869.1234 www.tripplite.com

7-Port USB-A Mini Hub - USB 3.2 Gen 1, International Plug Adapters, Aluminum Housing

MODEL NUMBER: U360-007-AL-INT











USB 3.2 Gen 1 portable hub adds 7 USB-A ports to your PC, laptop, Chromebook, tablet or other USB-enabled device.

Features

USB-A Hub Connects 7 USB Peripherals to Your Computer, Laptop or Tablet

This USB mini hub connects up to seven USB peripherals to your computer, laptop, Ultrabook, Chromebook, tablet or other device with a USB-A port. It expands the potential of your device by connecting peripherals that can help you do your job faster, easier and better, such as a printer, power meter, keyboard/mouse and external hard drives for uploading and downloading important files.

Transfers Data at Fast USB 3.2 Gen 1 Speeds

All seven USB ports transfer images, video and other data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Ideal for Charging Multiple Mobile Devices

The included external power supply provides 5V 3A to be shared among all seven USB ports, which support USB Battery Charging (BC) 1.2. Each port is capable of providing up to 1.5A for fast charging of your phone, tablet, music player and other mobile devices.

Ready to Use Right Out of the Package

The plug-and-play USB hub connects to your computer via its built-in USB cable, saving you the expense and effort of buying and carrying extra cables. It requires no drivers or other software. The included power supply comes with international plug adapters that allow you to connect to almost any AC outlet. The slim aluminum housing fits easily into a pocket, briefcase or laptop bag, so you can set up your workstation anywhere.

Specifications

OVERVIEW	
UPC Code	037332272041

Highlights

- Accepts up to 7 USB peripherals, turning your computer into a mini workstation
- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfer
- BC 1.2 ports provide up to 1.5A for charging smartphones and other mobile devices
- Slim aluminum housing fits easily into backpack or bag for use anywhere
- Plug-and-play operation with no software required for immediate connection

Package Includes

- U360-007-AL-INT 7-Port USB-A Mini Hub
- External power supply with NEMA 1-15P plug (Input: 100–240V, 50/60 Hz, 0.6A; Output: 5V 3A)
- (3) International plug adapters (U.K., Europe, Australia)



CHARGING	
LED Indicators	White (Connection to Power)
USER INTERFACE, ALERTS & CON	
USB Power Delivery (PD) Charging Support	No
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; IEC-320-C14
Power Consumption (Watts)	1.40
DC Barrel Plug	OD: 3.5 x 1.35 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Cord Length (m.)	1.5
External Power Supply Cord Length (ft.)	5
External Power Supply Output Specs (V / A)	5V, 3A
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60Hz, 0.6A
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 5V, 3A
POWER	
Product Length (m.)	0.548
Product Length (ft.)	1.8
Product Length (cm.)	54.86
Product Length (in.)	21.6
Bus Powered	No
Built-In Cable Length (cm)	40
Built-In Cable Length (in.)	15.75
Built-In Cable Length (m)	0.4
Built-In Cable Length (ft.)	1.31
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
INPUT	
Data Ports Details	(7) USB-A - USB 3.2 Gen 1 (5 Gbps)
Data Ports	(7) USB A (FEMALE)
DATA	
Host Connector	USB A (MALE)
Technology	USB
Product Type	Hub



Charging Ports Details	All USB-A ports support BC 1.2 charging, providing 5A to connected devices	
Charging Ports	USB-A: 5V 1.5A (7.5W)	
Charging Ports / Amps	(7) 1.5A	
PHYSICAL		
Material of Construction	Aluminum	
Color	Black	
Cable Jacket Rating	VW-1	
Unit Dimensions (hwd / in.)	0.83 x 6.2 x 1.18	
Unit Dimensions (hwd / cm)	2.1 x 15.74 x 3.0	
Unit Packaging Type	Вох	
Unit Weight (lbs.)	0.53	
Unit Weight (kg)	0.24	
ENVIRONMENTAL		
Operating Temperature Range	32 to 104 F (0 to 40 C)	
Storage Temperature Range	14 to 158 F (-10 to 70 C)	
Relative Humidity	10% to 90% RH, Non-Condensing	
BTUs	4.7 BTU/Hr	
Power Provided to Connected Device(s)	5V 1.5A (7.5W) Output per USB Port	
CONNECTIONS		
Number of Ports	7	
Side A - Connector 1	USB 3.0 A (MALE)	
Side B - Connector 1	(7) USB 3.0 A (FEMALE)	
Connector Plating	Nickel	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)	
Driver Required	No	
UASP Support	No	
Auto MDIX Support	No	
Full Duplex Support	No	
Suspend Mode Support	No	
Remote Wakeup Support	No	
STANDARDS & COMPLIANCE		



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

External Power Supply Certifications	CE; GS; PSE; TUV; UL; WEEE; cUL	
Certification & Compliance	RoHS; REACH; CE (Europe); FCC (USA); WEEE	
WARRANTY		
Product Warranty Period (Worldwide)	1-year limited warranty	

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies