



13.3" LED TV

SC-1310TV



BATTERY DETAILS

Battery Type:	NO BATTERY
Battery Voltage (Volts):	-
Battery Capacity (mAh):	-
Number of Battery Cells:	-
Energy Content (Watt Hours):	-
Weight of Battery (grams):	-

Remote Control: 2x AAA (not included)



PRODUCT DETAILS:

Black Unit UPC: 639131213104
Black Master UPC: 106391312131

Unit Dimensions (in): 12.6 x 8.86 x 1.06
Unit Weight (lbs): 1.88

Giftbox Dimensions (in): 14.0 x 5.5 x 10.75
Giftbox Weight (lbs): 3.95

Master Dimensions (in): 28.25 x 14.75 x 11.5
Master Weight (lbs): 22.25
Master Case QTY: 5

Units per Pallet

48"(L) x 40"(W) x **72"**(H) = 100
48"(L) x 40"(W) x **84"**(H) = 125
48"(L) x 40"(W) x **96"**(H) = 150
48"(L) x 40"(W) x **110"**(H) = 175


Units per Container

20' = 770
40' = 1,540
40'HQ = 1,790
45' = 2,016

Features and specifications, measurements and weight may be subject to change without prior notice

FEATURES & SPECIFICATIONS:

- 13.3" Widescreen LED TV
- Built-in Digital TV Tuner
- VGA Input
- HDMI Input Allows You to Enjoy High Definition Video & Audio
- USB & SD Inputs Compatible Allows You to Play Video & Audio Files from an External Device
- SD Card Reader Compatible, Allows You to Play Video & Audio Files from an SD Card
- Selectable Screen Mode: 16:9
- Resolution: 1280 x 800
- On Screen Display
- AV Input Jack
- Rotary Rod Antenna
- Earphone Jack
- Built-in Speakers
- AC/DC Operation: Watch Your Favorite Shows at Home or on the Go
- Full Function Remote Control
- Peak Brightness: 500cd m2
- Contrast Ratio: 300:1
- Viewing Angle: 165°
- Response Time: 8ms.
- Audio: 2 x 1W
- Maximum Power Consumption: 12W
- Full Compliance with ATSC/NTSC
- Power: AC 100-240V Compatibility/ DC: 12V/1.12A Input for On the Go Use



Accessories: Manual, Remote Control, Power Adapter, DC Car Cord, AV Cables, Antenna

WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information, go to www.P65Warnings.ca.gov

www.supersonicinc.com

01/27/2021