

The Planar® PXN2410 is a 24" Full HD LCD monitor with an ultra-thin bezel design, integrated speakers, multiple inputs and an ergonomic stand. It is a great fit for office or home environments. It uses IPS technology to deliver wide viewing angles with no color shift. It is flicker free and incorporates blue light reduction presets. The LED backlight reduces energy consumption.



24" Full HD LCD monitor

SPECIFICATION	DETAIL
Product Name	PXN2410
Planar Part Number	998-2944-00
Viewable Size	23.8" diagonal (20.75" horizontal x 11.67" vertical)
Aspect Ratio	16:9
Contrast Ratio (typ)	1000:1
Viewing Angle (typ)	178° Horizontal and Vertical
Response Time (typ)	6 ms (GTG)
Brightness (Typical)	250 cd/m ²
Display Type	IPS LCD Active Matrix Flat Panel Display (TFT)
Display Resolution	Full HD 1080P, 1920 x 1080
Tilt Range	-5° to +20°
Palette	16.7 million colors
Pixel Pitch	0.2745 mm
Refresh Rate	48 to 76Hz (60 Hz recommended)
Dimensions (W x H x D)	24.2" x 20.5" x 9.1" (612.84 mm x 519.39 mm x 229.63 mm)
Dimensions without Stand	24.2" x 14.5" x 2.1" (612.84 mm x 367.46 mm x 52.3 mm)
Panel Depth	2.1" (52.3 mm)
Display Weight	10.8 lb/4.9kg (7.0 lb/ 3.145 kg without stand)
Shipping weight	13.3 lb (6.8 kg)
Video Inputs	HDMI, DisplayPort, VGA
HDCP	Yes
Audio Output	Integrated 2W/channel stereo speakers, headphone jack

External Connections	HDMI 19-pin, DisplayPort 20-pin, VGA 15-pin, 3.5 mm audio in, 3.5mm headphone out
Compatibility	PC and Mac® (adapter may be required for Mac)
Power Supply	Internal
Power Consumption (max)	14.7W Typical (<0.5W standby)
Power Requirements	AC 100/240 VAC
Operating Temperature	0° to +40°C (32° to 104°F)
Humidity	10 - 85% RH (non-condensing)
Mount	Built-in 100 mm VESA, back
Product Approvals	cTUVus, CE , FCC-B, RoHS
Recommended Usage	Up to 16 hours per day
Service and Support	3-Year Customer First [™] Warranty featuring FREE 2-Day Advance Replacement (US only). Please see warranty document for more details and for replacement procedures outside the US.
Options / Features	IPS panel, Wide color consistent viewing angle, Discreet branding, Height adjustment: 4.3" (120cmm), Swivel range 60° (30° left, 30° right), Pivot ± 90°, Anti-glare coating ,Multi-language display, On screen display (OSD), Kensington® Security Slot
Blue Light Reduction	Yes
Flicker Free	Yes
In the Box	PXN2410 24" LED LCD Monitor, Power Cord, HDMI Cable, DisplayPort Cable, User's Guide
UPC	8 10689 00989 4

For more information, please visit www.planar.com Specifications are subject to change without notice. Specification Report Date: 5/11/2022 © Copyright 2022 Planar Systems, Inc. All rights reserved