

PERFORMANCE

Processor

Intel® Core™ i5-12400, 6C (6P + 0E) / 12T, P-core 2.5 / 4.4GHz, 18MB

Graphics

Integrated Intel UHD Graphics 730

Chipset

Intel Q670 Chipset

Memory

1x 8GB SO-DIMM DDR4-3200

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Max Memory

Up to 64GB DDR4-3200

Storage

256GB SSD M.2 2280 PCIe® 4.0x4 Value NVMe® Opal

Storage Support

Up to three drives, 2x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 2TB each
- M.2 SSD up to 1TB

Card Reader

None

Optical

DVD±RW

Audio Chip

High Definition (HD) Audio, Realtek® ALC256-NL codec

Speakers

2Wx2

Camera

5.0MP RGBIR

Microphone

2x, Array

Power Supply

180W 90%

DESIGN

Display

21.5" FHD (1920x1080) IPS Anti-glare, Touch

Touchscreen

10-point Multi-touch

Keyboard

USB Calliope Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

Case Color

Black

Stand

UltraFlex V Stand

Mounting

VESA mount

Form Factor

AIO (21.5 inches)

Dimensions (WxDxH)

Lowest in vertical mode: 489 x 216.32 x 358.82 mm (19.25 x 8.52 x 14.13 inches)

Highest in vertical mode: 489 x 216.32 x 443.31 mm (19.25 x 8.52 x 17.45 inches)

Weight

7.985 kg (17.6 lbs)

CONNECTIVITY

Ethernet

Integrated 100/1000M

WLAN + Bluetooth®

Intel 9560 11ac, 2x2 + BT5.0

Rear Ports

- 3x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 2 (support data transfer and 15W charging)
- 1x HDMI® (HDMI in 1.4 / HDMI out 2.1 TMDS combo port)
- 1x DisplayPort™ 1.4
- 1x Ethernet (RJ-45)

Optional Rear Ports (configured)

None

Right Ports

- 2x USB 3.2 Gen 2
- 1x headphone / microphone combo jack (3.5mm)

Monitor Cable

None

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified

Fingerprint Reader

No fingerprint reader

Physical Locks

Kensington® Security Slot, 3 x 7 mm

Chassis Intrusion Switch

None

Other Security

ThinkShutter camera cover

MANAGEABILITY

System Management

Non-vPro

SERVICE

Base Warranty

3-year, Onsite

Included Upgrade

None

CERTIFICATIONS

Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO Certified 9.0
- TCO edge
- RoHS compliant

Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland Low Blue Light
- UL Anti-dust

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation, Contamination by Fluids, Salt Fog)

SOFTWARE

Operating System

Windows® 11 DG Windows 10 Pro 64, English

Bundled Software

None

MODEL

TopSeller : Yes

Announce Date : 2022-04-26

EAN / UPC / JAN : 196380170652

End of Support : 2028-11-12

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Professional Wireless Combo Keyboard & Mouse (US English)

4X30H56796

This sleek and stylish full-size keyboard and mouse combo offers exceptional quality in a modern wireless solution. The slim 3-zone keyboard with number pad has responsive quiet keys and a premium typing experience. O...

Recommended Services

BEST	4Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + International Upg) (5PSON73191)
BETTER	4Y Lenovo Support (Premier Support + Keep Your Drive + International Upg) (5PSON73243)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0U26648)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference