



BUSINESS DEVICES THAT ARE A CLASS APART



The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

ThinkPad T14 Gen 2 (AMD)

Smarter
technology
for all

Lenovo

Enable business productivity and collaboration for your workforce in the new normal – without breaking your IT budget. Powered by the latest AMD Ryzen 5000 Pro series processors, this 14” laptop delivers enterprise-grade computing solutions, comprehensive security features and modern touches. Multiple connectivity options, including USB-C and HDMI, make for seamless multitasking, while Modern Standby allows the device to wake in one second and connect to the internet in the next.



REASONS TO BUY

Display options such as AMD Radeon integrated graphics and 4K UHD Dolby Vision make the device ideal for work as well as off-the-clock entertainment. Plus, the Dolby audio speaker system enhances sound clarity during remote calls and meetings.

On-the-move professionals will appreciate the laptop's Modern Standby feature, which enables it to wake in one second and connect to the internet in the next, reducing time and enhancing efficiency.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

ThinkPad T14 Gen 2 (AMD)

KEY SPECIFICATIONS

Processor	AMD Ryzen™ 3 / 5 / 7 Processor
Operating System	Powered by Windows 10 Pro
Display	14.0" Dolby Vision HDR 400 screen, UHD (3840x2160) IPS, 1500:1 contrast ratio, 100% Adobe RGB gamut, 500 nits 14.0" PrivacyGuard screen, FHD (1920x1080) IPS, 1000:1 contrast ratio, 72% gamut, 500 nits (touch) 14.0" Low Power screen, FHD (1920x1080) IPS, 1200:1 contrast ratio, 72% gamut, 400 nits 14.0" screen, FHD (1920x1080) IPS, 700:1 contrast ratio, 45% gamut, 300 nits (touch) 14.0" screen, FHD (1920x1080) IPS, 700:1 contrast ratio, 45% gamut, 300 nits
Touchscreen	Optional touchscreen on PrivacyGuard FHD or regular FHD model
Graphics	AMD Radeon Graphics in processor
Memory	Up to 48GB DDR4-3200
Storage	One drive, 1x M.2 2280 SSD or 1x M.2 2242 SSD <ul style="list-style-type: none">• M.2 2280 SSD up to 2TB• M.2 2242 SSD up to 128GB
Audio	Stereo speakers, 2W x2, Dolby® Audio™ Dual array microphone, far-field
Battery†	Up to 13.0hrs, 50Wh
Power Adapter	One of the following 45W USB-C (2-pin) 45W USB-C (3-pin) 65W USB-C (2-pin) 65W USB-C (3-pin) 65W USB-C Slim (2-pin) 65W USB-C Slim (3-pin)
Camera	One of the following 720p with Privacy Shutter IR & 720p with Privacy Shutter
Keyboard	6-row, spill-resistant, multimedia Fn keys with Unified Communications controls
Dimensions	329 x 227 x 17.9 mm (12.95 x 8.94 x 0.70 inches)
Weight	From 1.46kg (3.23lb)

GREEN CERTIFICATIONS

EPEAT™ Gold, ENERGY STAR® 8.0

OTHER CERTIFICATIONS

MIL-STD-810H military test passed

Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. † Based on testing with MobileMark 2014. Battery life varies significantly with settings, usage, and other factors. © 2020 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.

CONNECTIVITY

I/O Ports	1x USB 3.2 Gen 1, 1x USB 3.2 Gen 1 (Always On), 2x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4a), 1x HDMI 2.0, 1x microSD card reader, 1x Ethernet (RJ-45), 1x headphone / microphone combo jack (3.5mm), 1x side docking connector, 1x Smart card reader (optional), 1x Nano-SIM card slot (WWAN models)
WLAN + Bluetooth	One of the following Intel AX200 11ax, 2x2 + BT5.2 Mediatek MT7921 11ax, 2x2 + BT5.2 Qualcomm QCNFA765 Wi-Fi 6E, 11ax, 2x2 + BT5.2 RTL8852AE 11ax, 2x2 + BT5.2 Wi-Fi 6 11ax, 2x2 + BT5.2
WWAN	Optional
NFC	Optional
Docking	Compatible with side mechanical dock and USB 3.2 cable dock
SECURITY & PRIVACY	Fingerprint Reader Smart Card Reader IR Camera with Windows Hello ThinkPad PrivacyAlert ThinkPad PrivacyGuard screen Optional touch style fingerprint reader on palm rest, match-on-chip Smart card reader (optional) Kensington® Security Slot

MANAGEABILITY

DASH
Non-DASH

Recommended for this device



Lenovo Powered USB-C Travel Hub

Connects to a PC through a single USB-C cable which also recharges the device

Connect to an external display with HDMI or VGA, and other peripherals with 2x USB ports

Compact 183x100mm (7.2x4") design with integrated cable management



Lenovo 700 Ultraportable Bluetooth Speaker

Just 11mm (0.43") thin and weighing 145g (0.32lb), this ultra-thin Bluetooth speaker delivers 360-degree sound with 2x 2Watt power output

Supports Siri and Google Assistant voice commands for your iOS and Android devices, as well as a dedicated button for taking calls

Fast-charges in 2 hours and lasts for up to 12hours of audio playback or voice calls



Premier Support

Talk directly with advanced technical support agents

Support for software & hardware

Next business day onsite repairs