



USB Dual DisplayLink Docking Station

UDDS2

SKU: 9VB336

Maximize productivity with the UDDS2 from V7. This Universal Docking Station adds displays, USB ports, audio and network connectivity to your computer easily from one included cable. It adds HDMI, DVI, Ethernet, Audio, 2 x USB A 3.2 Gen1 and 4 x USB 2.0 ports. Extend or mirror displays via the HDMI and DVI output (can also connect to a VGA display using the included DVI to VGA adapter). Extend or mirror your HDMI (2560x1440 QHD) and DVI (2048x1152 2K) displays. It's Displaylink certified, with robust high performance connectivity to extend and enhance your workstation productivity with a 2 year warranty.

- Connect your displays and devices to your computer with one USB cable
- Total of 6 USB Ports (2 x USB A 3.2 Gen 1, 4 x USB A 2.0)
- USB Cable and adapter included for connection from USB-C or USB A computer port
- HDMI and DVI Output (includes DVI to VGA Adapter)
- Gigabit Ethernet and 3.5mm audio & microphone ports
- 2 year warranty

General

Sku: 9VB336
 Model: UDDS2
 EAN: 0662919114928
 Warranty: 2 years
 Compliance: CE, FCC, RoHS
 Country Of Origin: China
 Package Type: 4 Color Box
 ASIN: B09S3S7P52
 SAP: 5376143
 Package Includes: Docking Station, USB Cable + USB-C Adapter, DVI to VGA Adapter, Power Supply, Quick Start Guide

Color

Color: Black

Design

Docking Type: USB-C DisplayLink
 Number of Ports: 1 x 3.5 mm Audio Out, 1 x DVI port, 1 x HDMI, 1 x RJ45 Ethernet, 1 x 3.5 mm Audio In (Microphone), 6 x USB
 Material: ABS

Package Dimensions

Package Dimensions (L/W/H): 13.58 x 5.98 x 2.36 in (345 x 152 x 60 mm)
 Shipping Weight: 1.65 lbs (0.75 kg)

Product Dimensions

Product Dim (L/W/H): 8.66 x 3.58 x 1.1 in (220 x 91 x 28 mm)
 Product Weight: 0.62 lbs (0.28 kg)

Technical

Connectivity: USB
 USB Display Type: DisplayLink
 Connectors: 3.5 mm Audio Out, 3.5 mm Audio In (Microphone), DVI, HDMI, RJ45, USB
 System Requirements: Mac OS X v10.6 and above, Windows 11, Windows 10, Windows 7, Windows 8.1, Windows Vista, Windows XP
 Storage Temperature: -10 to 70 C
 Input Voltage: 100-240V AC
 Operating Temperature: 0 to 35 C
 Output Voltage: 5V 1.5A
 Audio Channel: 3.5 mm TRS
 Dock Max Resolution: HDMI 2560x1440 QHD, DVI 2048x1152 2K Full HD