

Accelerate your digital transformation journey

fi-8190

Take on the toughest front-office jobs with this elite scanner. The Fujitsu fi-8190 employs innovative feeding and Clear Image Capture (CIC) technology to deliver industry-leading reliability.



#### **Image Quality**

Clear Image Capture (CIC) technology resets the benchmark for high quality image capture, by combining the reliability and flexibility of Contact Imaging Sensor (CIS) hardware, with an industry-leading, image processor. CIC technology delivers precise, crisp images, and industry-leading OCR accuracy rates while also removing unwanted watermarks and artifacts.

#### **Paper Feeding**

Evolved paper handling with a large 100-page hopper, an all-wheel drive mechanism, and fast 180 images captured per minute, make the fi-8190 one of the easiest and most efficient scanners to operate. The patented Automatic Separation Control uses state of the art technology to sense paper weights and adjusts to consistently separate documents and provide the perfect feed, ensuring documents are safely captured.

#### Reliability

The fi-8190 is built to last and powers up every time you need it regardless of job size. Strong urethane rollers, heavy duty motors, a sturdy frame, and durable consumables combine for a long-lasting scanner that will let your organization capture the volumes of paper from seasonal peaks and heavy backlogs, worry free. Backed by Fujitsu's US-based, legendary solutions architects and support teams.



#### PaperStream IP

Compatible with all major document management software packages, PaperStream IP (PSIP) is a TWAIN/ ISIS® compliant driver that cleansup and optimizes scanned images without any configuration.

### PaperStream Capture

Take advantage of powerful indexing and sorting features, putting the document in the right location for great organization and fast retrieval. Now includes both 2D and 1D barcode support in the box.

## PaperStream Clickscan

Easy to use capture software for any business. Simple scanning interface with 3-steps: scan, select destination, and save.

# Flexible connectivity options

Choose between PaperStream IP Net for flexible, adaptable capture architectures, and PaperStream NX Manager for centralized, serverbased capture.



# The next generation in scanning excellence Fujitsu fi-8190 Image Scanner















#### **Technical Information**

ADF (Automatic Document Feeder) / Manual Feed, Duplex Scanner Type

Scanning Speed\* (A4 Portrait) (Color \*2/ Grayscale\*2/

Simplex: 90 ppm (200/300 dpi) Duplex: 180 ipm (200/300 dpi)

RGB LED x 2 (front x 1, back x 1)

Monochrome\*3 CIS x 2 (front x 1, back x 1) Image Sensor Type

**Optical Resolution** 

Output Resolution\*4 50 to 600 dpi (adjustable by 1 dpi increments)

(Color / Grayscale/ Monochrome)

**Output Format** Color: 24-bit, Grayscale: 8-bit, Monochrome: 1-bit

**Background Colors** White/Black (selectable)

**Document Size** 

**Light Source** 

Maximum\* 8.5 x 14 in. (215.9 x 355.6 mm) 1.9 x 2 in. (48x50 mm) Minimum Long Page Scanning\*7 240 in. (6,096 mm)

Paper Weight (Thickness)

5.3 to 124 lb (20 to 465 g/m<sup>2</sup>)\*8 Paper Booklet 0.276 in. (Less than 7 mm)\* 0.055 in. (1.4 mm) or less\*10 Plastic Card

ADF Capacity\*11 \*12 100 sheets (Letter 20 lb or A4 80 g/m<sup>2</sup>)

Expected Daily Volume\*13 13,000 sheets

Multifeed Detection Overlap detection (Ultrasonic sensor)

Length detection

Image monitoring, Sound detection (iSOP)\*14 **Paper Protection** 

Interface

1 Year Basic Onsite

3.2 Gen 1x1 / USB 2.0 / USB 1.1 **USB** 10BASE-T, 100BASE-TX, 1000BASE-T Ethernet

AC 100V to 240V 50/60Hz **Power Requirements** 

**Power Consumption** 

Operating Mode 30 W or less / 17 W (Eco mode) Sleep Mode 2.0 W or less (LAN) / 1.4 W or less (USB) 0.2 W or less

Auto Standby (Off) Mode

Operating Environment 41 to 95 °F (5 to 35 °C) Temperature Relative Humidity 15 to 80% (non-condensing)

Dimensions\*15

(Width x Depth x Height) 11.8 x 6.7 x 6.4 in. (300 x 170 x 163 mm)

Weight 8.8 lb (4 kg)

Supported Operating

**Environmental Compliance** 

System

Windows® 11, Windows® 10, Windows® 8.1, Windows® 7, Windows Server® 2022, Windows Server® 2019, Windows Server® 2016, Windows Server® 2012 R2, Windows Server® 2012, Windows Server® 2008 R2, macOS, Linux

(Ubuntu)

PaperStream IP Driver (TWAIN/TWAIN x64/ISIS), Included Software / Drivers

ENERGY STAR®, RoHS

WIA Driver\*16, Image Scanner Driver for macOS (ICA)\*16\*17 Image Scanner Driver for Linux (SANE)\*16\*17 PaperStream Capture, PaperStream ClickScan\*17, Software Operation Panel, Error Recovery Guide, ABBYY FineReader for ScanSnap™\*17, Scanner Central Admin, 2D Barcode for PaperStream\*17

Multi image output, Automatic color detection, Blank

**Image Processing** Functions

page detection, Dynamic threshold (iDTC), Advanced DTC, SDTC, Error diffusion, Dither, De-Screen, Emphasis, Dropout color (None/Red/Green/Blue/White/Saturation/ Custom), sRGBoutput, Hole punch removal, Index tab

cropping, Split image, De-Skew, Edge filler, Vertical streaks reduction, Background pattern removal, Cropping, Static

threshold

Included Items ADF paper chute, AC cable, AC adapter, USB cable, Setup

DVD-ROM

Trade Compliant Yes

Additional service coverage durations and response times at fujitsuscannerstore.com/service\_programs Service Programs & Options

1 Year Advance Exchange S8190-AEPWNBD-1 One or year program offers whole-unit, next business day 3 Year Advance Exchange S8190-AEMYNDB-3 replacement for scanner equipment S8190-DEPW5DY-3 Depot Mail-in Repair 3-year scanner contract provides mail-in unit repair that

includes spare parts, labor, and one-way shipping to customer S8190-BAPWNBD-1 One year onsite with a preventative maintenance visit

PaperStream Capture Pro PSCP-DP-0001 PaperStream Capture Pro Departmental software license Fujitsu industry-leading support keeps digital transformation projects on-time and on budget

· U.S. based support

Specialized Teams

Flexible service programs

Consumables Genuine Fujitsu Consumables are available at fujitsuscannerstore.com

Imprinter PA03810-D201 Prints a string of characters on document after a scan Lifetime: approx. 4,000,000 printed characters Lifetime: approx. 200,000 sheets or 1 year Imprinter Ink Cartridge CA00050-0262 Brake Roller PA03810-0001 Pick Roller PA03670-0002 Lifetime: approx. 200,000 sheets or 1 year ScanAid Kit CG01000-302801 Consumable kit with instructions and cleaning supplies Booklet Carrier (1 Piece) PA03810-0020 Supplemental protection for items such as passports Carrier Sheets (5 Pieces) PA03360-0013 Supplemental protection for delicate items









\*1 Actual scanning speeds may vary with data transmission and software processing times. \*2 Indicated speeds are from using IPEC compression. \*3 Indicated speeds are from using IFE CCITT Group 4 compression. \*4. Selectable maximum resolution may vary depending on the length of the scanned document. \*5 Limitations may apply to the size of documents that can be scanned, depending on system environment, when scanning at high resolution (over 600 dpi). \*6 Maximum document width possible for scanning is 240 mm (9.5 ind.). \*7 For use with PaperStream NX Manager, the maximum resolution supported is 400 dpi, with maximum lengths ranging with resolution. Simplex: 1,828.8 mm (72 in.) Below 300 dpj], 355.6 mm (14 in.) Below 400 dpj]. \*8 Thicknesses of up to 128 to 209 gpim" (34 to 56 lb) can be scanned for A8 (52 x Y Am in Z.1 x Z.) indicated thickness is inclusive of Booklet Carrier Sheet thickness when using the Carrier Sheets. \*10 Continuous feeding is supported when scanning up to 10 unembossed cards with thicknesses of 0,76 mm or less. \*11 Maximum capacity depends on paper weight and may vary. \*12 Capable of setting additional documents while scanning, \*13 Numbers are calculated using scanning speeds and typical hours of scanner use, and are not meant to guarantee daily volume or unit untablility. \*14 Intelligent Sonic Paper Protection. \*15 Excludes the ABF paper rote that and stacker the LAPF paper rote that and stacker that and stacker that and stacker that the support to those offered by PaperStream IP may not be available with the Image Scanner Driver for macOS/Linux or WIA Driver. \*17 Refer to the fi Series Support Site for driver/software downloads and full lineup of all supported operating system versions. https://www.fujitsu.com/nl/lobal/support/products/cromputing/nl/cripher/supraction/cripher/supraction/cripher/supraction/cripher/supraction/cripher/supraction/cripher/supraction/cripher/supraction/c com/global/support/products/computing/peripheral/scanners/fi/

\*Replacement units shipped overnight for all requests received by 2 P.M. PST, Monday-Friday

Trademarks
ISIS is a trademark of Open Text. Microsoft, Windows, and Windows Server are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. macOS is a trademark of Apple Inc., registered in the U.S. and other countries. Linux is the registered trademark of Linus Torvalds in the U.S. and other countries. Any other products or company names appearing in this document are the trademarks or registered trademarks of the respective companies.

Safety Precautions

Please carefully read the safety precautions prior to the use of this device and follow the recommended instructions for correct use. Do not place this device in wet, moist, highly humid, dusty or oily areas. Use of this device under such conditions may result in electrical shock, fire or damage to the device. Please use this device within the power ratings listed.

FPU Limited, a Fujitsu company, has determined that this product meets the ENERGY STAR® guidelines for energy efficiency. ENERGY STAR® is a registered trademark of the United States.

Specifications are subject to change without notice.

