

GCS1424TAA4

4-Port Dual View DisplayPort Secure KVM Switch w/Audio



- NIAP-Certified PP4.0
- 4-Port Single View DisplayPort Secure KVM Switch
- Superior 4K UHD Video Resolution
- PP4.0 Certified Remote Port Selector** Support

4-Port Dual View DisplayPort Secure KVM with Audio Protection Profile v4.0

Secure and manage multiple data-sensitive systems from one workstation from internal and external cybersecurity threats with the TAA-compliant IOGEAR 4-Port Dual View DisplayPort Secure KVM with Audio Protection Profile v4.0. Enable authorized users secure access to up to four systems with one keyboard, mouse, up to two 4K @30Hz monitors.

Featuring the latest in Common Criteria and NIAP Protection Profile v4.0 security requirements set for the U.S. government for peripheral sharing switches, the secure KVM switches are built for multiple interfaces and ideal for use in high-security environments that demand rigorous cybersecurity provisions including military and defense, federal agencies, government, utilities, commercial and healthcare applications.

- NIAP-Certified PP4.0
Validated to Protection Profile for Peripheral Sharing Device v4.0
- 4-Port Dual View DisplayPort Secure KVM Switch
One USB console controls 4 secure computers on 2 displays
- Superior 4K UHD Video Resolution

UHD Resolution: 3840 x 2160 @30Hz

- Port Selection via Push-Button and Remote Port Selector** for Enhanced Security
Keyboard restrictions - OSD & hotkey methods are not allowed
- Isolated Channel per Port
Unidirectional data flow restricts data leakage between connected computers
- Active Chassis Intrusion Detection
Compromising the unit's cover renders the switch inoperable
- Tamper-Evident Seals
Visually detect attempts to gain access to switch's internal components

- Tamper-Proof Hardware
Integrated circuits are soldered directly onto the circuit board to hinder component sabotage
- Non-Reprogrammable Firmware
Prevents tampering and attempts to reprogram the switch's firmware
- Clears Keyboard Buffer
Data clears automatically after transmission to switch and resets
- Analog Speaker Support
- Secure audio data input does not convert digital audio to analog audio
- Multiplatform Support
Windows® 2000, Vista, 7, 8, 8.1, 10, 11 Linux, Mac OS X, & Sun
- Rugged Metal Enclosure
Durable, Full Metal Chassis
- Build-In, Internal Power Supply

** Remote Port Selector sold separately



Requirements

Package Contents

Console

- DisplayPort monitors capable of the highest resolution that you will be using on any computer in the installation
- Standard 104-key wired USB keyboard
- Standard 2 or 3 button wired USB mouse
- Speaker (optional)

- 1x GCS1424TAA4
- 1x Power Cord
- 1x User Guide
- 1x Warranty Card

Computers

- 2 x DisplayPort Video output connectors
- A USB Type A port for keyboard and mouse
- A 3.5mm jack Audio port for speaker (Optional)

Operating Systems

- Win 7, 8, 10, 11
- Linux: Kernel2.6+, RedHat v6.0+, SuSE v8.2+
Mandriva(Mandrake) v9.0+
- Unix: AIX v4.3, FreeBSD v3.51+, Sun Solaris v9.0+
- Novell Netware v5.0+Mac OS v9+
- DOS v6.2+

Specifications

Function	GCS1424TAA4
Computer Connections	
Direct	4
Port Selection	Pushbutton or Remote Port Selector
Console Connectors	
Monitor	2 x HDMI 1.4 Female (Black)
Keyboard	1 x USB Type-A Female (Black)
Mouse	1 x USB Type-A Female (Black)
Audio	1 x Mini Stereo 3.5mm Jack Female (Green)
CPU Connectors	
Monitor	8 x DisplayPort 1.2 Female (Black)
Keyboard & Mouse	4 x USB Type-B Female (White)
Audio	4 x Mini Stereo 3.5mm Jack Female (Green)
Switches	
Port Selection	4 x Pushbuttons
Power	1 x Rocker
LEDs	
On Line	4 x Orange
Selected	4 x Orange
Power On	1 x Green
Key Lock	3 x Green (Num Lock, Caps Lock, Scroll Lock)
Console Video	2 x Green (Rear Panel)
Emulation	
Keyboard	USB
Mouse	USB
Video Resolution	Up to 3840 x 2160 @ 30Hz (UHD)
Power	
Amps	1A
Voltage	100 ~240V, 50 ~ 60 Hz
Environment	
Operation Temperature	0 - 50C
Storage Temperature	-20 - 60C
Humidity	0 - 80% RH, Non-condensing
Housing	
Case	Metal

Dimensions	GCS1424TAA4
Unit Package Dimensions	
Height	9.5 in. (24.1 cm)
Length	5.25in. (13.3 cm)
Width	21.25 in. (53.9 cm)
Master Carton	
Height	10.25 in (26.0 cm)
Length	16.75 in. (42.5 cm)
Width	22 in. (55.9 cm)
Master Carton Qty.	3
Weight	
Master Carton Wt.	22.05 lb. (10.0 kg)
Unit Pack Wt.	6.65 lb. (3.0 kg)